



Circuit Diagram



Dimensions: (In.)

■ Specifications:

- Primary voltage: 117VAC 60Hz
- Primary exciting current: 30mA max.
- Secondary voltage: 8VDC $\pm 0.3V$ (no load)
6VDC $\pm 0.3V$ (full load)
- Rated secondary current: 200mA DC 60Hz
- Temperature rise: $<45^{\circ}C$
- Breakdown voltage (hipot): 2000VAC 60Hz for 1 minute
- Coil~coil insulation: 200MQ min. @ 500VDC
- Core size: EI-41
- Core material: hilite core H-23 0.5mm
- Insulation: polyester tape
- Bobbin: nylon 66 13.5 x 16mm
- Impregnation: varnish
- Capacitor: 470mfd x 16V
- Rectifier: IN4001 (2)
- DC plug: 3.5mm male
- AC plug: flat pins
- Cable: 6 ft.
- Lead wire: AWG22

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Xicon:

41AC115