

Plastic-bodied compact limit switches

Combi C2


For confined spaces
With two mounting options
Protection class IP 30
Hinged snap lid




- Compact switches for safety or control applications
- 3 different contact configurations available as slow-action and snap-action
- All normally-closed contacts are positive break
- Two channel safety control possible
- Galvanically isolated terminals, type Zb
- Approvals UL, CSA
- Rectangular cable entries (8.5 x 3.5 mm) for 4 x 1-mm² flexible lead
- 4 screw-type connections (M3,5) with self-lifting clamps
- PBT enclosure, glass-fibre reinforced, self-extinguishing UL 94-V0
- Lid, PC UL 94-V0
- 2 mm contact opening of slow-action system according to EN 81-1 for lift applications



Mounting



a) 2 holes for M4 screws



b) 2 captive M3 nuts for end mounting (depending on type)

Contact configuration

Switching element	Switch function	Switch contact	Designation	Voltage	Continuous current
Slow-action	changeover	1NC/1NO	U1Z	250 V	10 A
Snap-action	changeover	1NC/1NO	SU1Z	250 V	10 A
Slow-action	normally-closed	2NC	A2Z	250 V	10 A
Snap-action	normally-closed	2NC	SA2Z	250 V	10 A
Slow-action	normally-open	2NO	E2	250 V	10 A
Snap-action	normally-open	2NO	SE2	250 V	10 A




Designation
Part number
Switching diagram
⊕ positive break according to IEC 947-5-1 Chap. 3
Za: changeover contact is not galvanically isolated
Zb: changeover contact is galvanically isolated
Slow-action contact/snap-action contact
Gasket inside (iw)/outside (w)

Contact travel mm Tol. ± 0.25 mm	Actuating force N Tol. ± 10%
Switch angle degree Tol. ± 3.5°	Actuating torque Ncm tol. ± 10%
In	Out

Voltage	max.
Continuous current	max.
Making current, acc. to IEC 947-5-1 AC 15/DC 13	
Switching frequency	max.
Mech. operational life – number of switching cycles	
Ambient temperature	min./max.

Approvals
Weight
Delivery: ex-stock/built to order


Further switching functions		
SA2	E2	SE2
		



Dimensions
All dimensions in mm






C2-U1Z	C2-SU1Z	C2-A2Z	C2-U1Z St	C2-SU1Z St	C2-A2Z St	C2-U1Z K	C2-SU1Z K	C2-A2Z K
600.8101.001	600.8351.002	600.8801.003	600.8104.025	600.8354.026	600.8804.027	600.8107.019	600.8357.020	600.8807.021
⊕ Zb	⊕ Zb	⊕ Zb	⊕ Zb	⊕ Zb	⊕ Zb	⊕ Zb	⊕ Zb	⊕ Zb
●/-	-/●	●/-	●/-	-/●	●/-	●/-	-/●	●/-
-/-	-/-	-/-	-/-	-/-	-/-	-/-	-/-	-/-



250 V AC	250 V AC	250 V AC	250 V AC	250 V AC	250 V AC	250 V AC	250 V AC	250 V AC
10 A	10 A	10 A	10 A	10 A	10 A	10 A	10 A	10 A
●	●	●	●	●	●	●	●	●
100/min.	100/min.	100/min.	100/min.	100/min.	100/min.	100/min.	100/min.	100/min.
3 x 10 ⁶	3 x 10 ⁶	3 x 10 ⁶	3 x 10 ⁶	3 x 10 ⁶	3 x 10 ⁶	3 x 10 ⁶	3 x 10 ⁶	3 x 10 ⁶
-30 °C/+80 °C	-30 °C/+80 °C	-30 °C/+80 °C	-30 °C/+80 °C	-30 °C/+80 °C	-30 °C/+80 °C	-30 °C/+80 °C	-30 °C/+80 °C	-30 °C/+80 °C
-22 °F/+176 °F	-22 °F/+176 °F	-22 °F/+176 °F	-22 °F/+176 °F	-22 °F/+176 °F	-22 °F/+176 °F	-22 °F/+176 °F	-22 °F/+176 °F	-22 °F/+176 °F

UL, CSA	UL, CSA	UL, CSA	UL, CSA	UL, CSA	UL, CSA	UL, CSA	UL, CSA	UL, CSA
0.02 kg	0.02 kg	0.02 kg	0.02 kg	0.02 kg	0.02 kg	0.02 kg	0.02 kg	0.02 kg
●/-	●/-	●/-	●/-	●/-	●/-	●/-	●/-	●/-






Designation
Switch part number
Actuator part number
Switching diagram
⊕ positive break according to IEC 947-5-1 Chap. 3
Za: changeover contact is not galvanically isolated
Zb: changeover contact is galvanically isolated
Slow-action contact/snap-action contact
Gasket inside (iw)/outside (w)

C2-U1Z R	C2-SU1Z R	C2-A2Z R	C2-U1Z o. M. + H	C2-SU1Z o. M. + H	C2-A2Z o. M. + H
600.8116.013	600.8366.014	600.8816.015	600.8101.007	600.8351.008	600.8801.009
-	-	-	391.0190.259	391.0190.259	391.0190.259
11-12 23-24	13-14 21-22	11-12 21-22	11-12 23-24	13-14 21-22	11-12 21-22
⊕ Zb	⊕ Zb	⊕ Zb	Zb	Zb	Zb
●/-	-/●	●/-	●/-	-/●	●/-
-/-	-/-	-/-	-/-	-/-	-/-

Contact travel mm Tol. ± 0.25 mm	Actuating force N Tol. ± 10%
Switch angle degree Tol. ± 3.5°	Actuating torque Ncm Tol. ± 10%
On	Off




Voltage	max.
Continuous current	max.
Making current, acc. to IEC 947-5-1 AC 15/DC 13	
Switching frequency	max.
Mech. operational life – number of switching cycles	
Ambient temperature	min./max.

250 V AC	250 V AC	250 V AC	250 V AC	250 V AC	250 V AC
10 A	10 A	10 A	10 A	10 A	10 A
●	●	●	●	●	●
100/min.	100/min.	100/min.	100/min.	100/min.	100/min.
3 x 10 ⁵	3 x 10 ⁵	3 x 10 ⁵	3 x 10 ⁵	3 x 10 ⁵	3 x 10 ⁵
-30 °C/+80 °C	-30 °C/+80 °C	-30 °C/+80 °C	-30 °C/+80 °C	-30 °C/+80 °C	-30 °C/+80 °C
-22 °F/+176 °F	-22 °F/+176 °F	-22 °F/+176 °F	-22 °F/+176 °F	-22 °F/+176 °F	-22 °F/+176 °F

Approvals
Weight
Delivery: ex-stock/built to order

UL, CSA	UL, CSA	UL, CSA	UL, CSA	UL, CSA	UL, CSA
0.02 kg	0.02 kg	0.02 kg	0.03 kg	0.03 kg	0.03 kg
●/-	●/-	●/-	●/-	●/-	●/-

Further switching functions



Dimensions
All dimensions in mm

