0.8 Ω CMOS, 1.8 V to 5.5 V, SPDT/2:1 Mux Mini LFCSP

Data Sheet **ADG852**

FEATURES

0.8 Ω typical on resistance
Less than 1 Ω maximum on resistance at 85°C
1.8 V to 5.5 V single supply
High current carrying capability: 300 mA continuous
Rail-to-rail switching operation
Fast-switching times: <17 ns
Typical power consumption: <0.1 µW
1.30 mm × 1.60 mm, 10-lead mini LFCSP

APPLICATIONS

Cellular phones
PDAs
MP3 players
Power routing
Battery-powered systems
PCMCIA cards
Modems
Audio and video signal routing
Communication systems

FUNCTIONAL BLOCK DIAGRAM



Figure 1.

GENERAL DESCRIPTION

The ADG852 is a low voltage CMOS single-pole, double-throw (SPDT) switch. This device offers ultralow on resistance of less than 1 Ω over the full temperature range. The ADG852 is fully specified for 5.5 V and 3.3 V supply operation.

Each switch conducts equally well in both directions when on, and has an input signal range that extends to the supplies. The ADG852 exhibits break-before-make switching action.

The ADG852 is available in a 1.30 mm × 1.60 mm 10-lead mini LFCSP.

PRODUCT HIGHLIGHTS

1. <1 Ω over full temperature range of −40°C to +85°C.
2. Single 1.8 V to 5.5 V operation.
3. Compatible with 1.8 V CMOS logic.
4. High current handling capability (300 mA continuous current per channel).
5. Low THD + N: 0.08% typical.
6. 1.30 mm × 1.60 mm, 10-lead mini LFCSP.

Rev. B

One Technology Way, P.O. Box 9106, Norwood, MA 02062-9106, U.S.A.
Tel: 781.329.4700 **www.analog.com**
Fax: 781.461.3113

TABLE OF CONTENTS

REVISION HISTORY

5/12—Rev. A to Rev. B

Changes to Ordering Guide ... 13

10/08—Rev. 0 to Rev. A

Change to Title ... 1
Changes to Features Section ... 1
Changes to Product Highlights Section ... 1

8/08—Revision 0: Initial Version

SPECIFICATIONS

V_{DD} = 4.2 V to 5.5 V, GND = 0 V, unless otherwise noted.

Table 1.

Parameter	+25°C	−40°C to +85°C	Unit	Test Conditions/Comments
ANALOG SWITCH				
Analog Signal Range		0 V to V_{DD}	V	
On Resistance, R_{ON}	0.8		Ω typ	V_{DD} = 4.2 V, V_S = 0 V to V_{DD}, I_{DS} = 100 mA; see Figure 16
	0.85	1	Ω max	
On Resistance Match Between Channels, ΔR_{ON}	0.02		Ω typ	V_{DD} = 4.2 V, V_S = 0 V to V_{DD}, I_{DS} = 100 mA
		0.04	Ω max	
On Resistance Flatness, $R_{FLAT (ON)}$	0.17		Ω typ	V_{DD} = 4.2 V, V_S = 0 V to V_{DD}, I_{DS} = 100 mA
		0.23	Ω max	
LEAKAGE CURRENTS				V_{DD} = 5.5 V
Source Off Leakage, I_S (Off)	±10		pA typ	V_S = 0.6 V/4.2 V, V_D = 4.2 V/0.6 V; see Figure 17
Channel On Leakage, I_D, I_S (On)	±30		pA typ	V_S = V_D = 0.6 V or 4.2 V; see Figure 18
DIGITAL INPUTS				
Input High Voltage, V_{INH}		2.0	V min	
Input Low Voltage, V_{INL}		0.8	V max	
Input Current				
I_{INL} or I_{INH}	0.002		μA typ	V_{IN} = V_{GND} or V_{DD}
		0.05	μA max	
C_{IN}, Digital Input Capacitance	2.5		pF typ	
DYNAMIC CHARACTERISTICS[1]				
t_{ON}	17		ns typ	R_L = 50 Ω, C_L = 35 pF
	23	28	ns max	V_S = 3 V/0 V; see Figure 19
t_{OFF}	6		ns typ	R_L = 50 Ω, C_L = 35 pF
	8.5	9.2	ns max	V_S = 3 V; see Figure 19
Break-Before-Make Time Delay, t_{BBM}	14		ns typ	R_L = 50 Ω, C_L = 35 pF
		8	ns min	V_{S1} = V_{S2} = 1.5 V; see Figure 20
Charge Injection	30		pC typ	V_S = 1.5 V, R_S = 0 Ω, C_L = 1 nF; see Figure 21
Off Isolation	−75		dB typ	R_L = 50 Ω, C_L = 5 pF, f = 100 kHz; see Figure 22
Channel-to-Channel Crosstalk	−73		dB typ	R_L = 50 Ω, C_L = 5 pF, f = 100 kHz; see Figure 24
Total Harmonic Distortion, THD + N	0.08		%	R_L = 32 Ω, f = 20 Hz to 20 kHz, V_S = 3.5 V p-p
Insertion Loss	−0.6		dB typ	R_L = 50 Ω, C_L = 5 pF; see Figure 23
−3 dB Bandwidth	100		MHz typ	R_L = 50 Ω, C_L = 5 pF; see Figure 23
C_S (Off)	19.5		pF typ	
C_D, C_S (On)	50		pF typ	
POWER REQUIREMENTS				V_{DD} = 5.5 V
I_{DD}	0.002		μA typ	Digital inputs = 0 V or 5.5 V
		1.0	μA max	

[1] Guaranteed by design, not subject to production test.

V_{DD} = 2.7 V to 3.6 V, GND = 0 V, unless otherwise noted.

Table 2.

Parameter	+25°C	−40°C to +85°C	Unit	Test Conditions/Comments
ANALOG SWITCH				
Analog Signal Range		0 V to V_{DD}	V	
On Resistance, R_{ON}	1.3		Ω typ	V_{DD} = 2.7 V, V_S = 0 V to V_{DD}, I_{DS} = 100 mA; see Figure 16
	1.5	1.7	Ω max	
On Resistance Match Between Channels, ΔR_{ON}	0.03		Ω typ	V_{DD} = 2.7 V, V_S = 0.6 V, I_{DS} = 100 mA
		0.05	Ω max	
On Resistance Flatness, $R_{FLAT (ON)}$	0.48		Ω typ	V_{DD} = 4.2 V, V_S = 0 V to V_{DD}, I_{DS} = 100 mA
		0.66	Ω max	
LEAKAGE CURRENTS				V_{DD} = 3.6 V
Source Off Leakage, I_S (Off)	±10		pA typ	V_S = 0.6 V/3.3 V, V_D = 3.3 V/0.6 V; see Figure 17
Channel On Leakage, I_D, I_S (On)	±30		pA typ	V_S = V_D = 0.6 V or 3.3 V; see Figure 18
DIGITAL INPUTS				
Input High Voltage, V_{INH}		1.35	V min	
Input Low Voltage, V_{INL}		0.7	V max	
Input Current				
I_{INL} or I_{INH}	0.002		μA typ	V_{IN} = V_{GND} or V_{DD}
		0.05	μA max	
C_{IN}, Digital Input Capacitance	4		pF typ	
DYNAMIC CHARACTERISTICS[1]				
t_{ON}	25		ns typ	R_L = 50 Ω, C_L = 35 pF
	37	43	ns max	V_S = 1.5 V/0 V; see Figure 19
t_{OFF}	7		ns typ	R_L = 50 Ω, C_L = 35 pF
	7.4	8	ns max	V_S = 1.5 V; see Figure 19
Break-Before-Make Time Delay, t_{BBM}	22		ns typ	R_L = 50 Ω, C_L = 35 pF
		13	ns min	V_{S1} = V_{S2} = 1 V; see Figure 20
Charge Injection	23		pC typ	V_S = 1.5 V, R_S = 0 V, C_L = 1 nF; see Figure 21
Off Isolation	−75		dB typ	R_L = 50 Ω, C_L = 5 pF, f = 100 kHz; see Figure 22
Channel-to-Channel Crosstalk	−73		dB typ	R_L = 50 Ω, C_L = 5 pF, f = 100 kHz; see Figure 24
Total Harmonic Distortion, THD	0.15		%	R_L = 32 Ω, f = 20 Hz to 20 kHz, V_S = 1.5 V p-p
Insertion Loss	−0.07		dB typ	R_L = 50 Ω, C_L = 5 pF; see Figure 23
−3 dB Bandwidth	100		MHz typ	R_L = 50 Ω, C_L = 5 pF; see Figure 23
C_S (Off)	20		pF typ	
C_D, C_S (On)	52		pF typ	
POWER REQUIREMENTS				V_{DD} = 3.6 V
I_{DD}	0.002		μA typ	Digital inputs = 0 V or 3.6 V
		1.0	μA max	

[1] Guaranteed by design, not subject to production test.

ABSOLUTE MAXIMUM RATINGS

T_A = 25°C, unless otherwise noted.

Table 3.

Parameter	Rating
V_{DD} to GND	−0.3 V to +6 V
Analog Inputs[1]	−0.3 V to V_{DD} + 0.3 V
Digital Inputs[1]	−0.3 V to V_{DD} + 0.3 V or 10 mA, whichever occurs first
Peak Current, S or D Pins	500 mA (pulsed at 1 ms, 10% duty cycle max)
Continuous Current, S or D Pins	300 mA
Operating Temperature Range	−40°C to +85°C
Storage Temperature Range	−65°C to +150°C
Junction Temperature	150°C
Mini LFCSP	
θ_{JA} Thermal Impedance, 3-Layer Board	131.6°C/W
Reflow Soldering, Pb-Free	
Peak Temperature	260(+0/−5)°C
Time at Peak Temperature	10 sec to 40 sec

[1] Overvoltages at the IN, S, or D pins are clamped by internal diodes. Current should be limited to the maximum ratings given.

Stresses above those listed under Absolute Maximum Ratings may cause permanent damage to the device. This is a stress rating only; functional operation of the device at these or any other conditions above those indicated in the operational section of this specification is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

Only one absolute maximum rating can be applied at any one time.

ESD CAUTION

ESD (electrostatic discharge) sensitive device. Charged devices and circuit boards can discharge without detection. Although this product features patented or proprietary protection circuitry, damage may occur on devices subjected to high energy ESD. Therefore, proper ESD precautions should be taken to avoid performance degradation or loss of functionality.

PIN CONFIGURATION AND FUNCTION DESCRIPTION



Figure 2. Pin Configurations

Table 4. Pin Function Descriptions

Pin No.	Mnemonic	Description
1	S1	Source Terminal. Can be an input or output.
2	D	Drain Terminal. Can be an input or output.
3	S2	Source Terminal. Can be an input or output.
4	IN	Logic Control Input.
5, 6	VDD	Most Positive Power Supply Potential.
7, 8, 9	N/C	No Connect.
10	GND	Ground (0 V) Reference.

Table 5. ADG852 Truth Table

Logic	Switch 1	Switch 2
0	Off	On
1	On	Off

TYPICAL PERFORMANCE CHARACTERISTICS



Figure 3. On Resistance vs. V_D (V_S), V_{DD} = 4.2 V to 5.5 V



Figure 6. On Resistance vs. V_D (V_S) for Different Temperatures, V_{DD} = 3.3 V



Figure 4. On Resistance vs. V_D (V_S), V_{DD} = 2.7 V to 3.6 V



Figure 7. Leakage Current vs. Temperature, V_{DD} = 5 V



Figure 5. On Resistance vs. V_D (V_S) for Different Temperatures, V_{DD} = 5 V



Figure 8. Leakage Current vs. Temperature, V_{DD} = 3.3 V



Figure 9. Charge Injection vs. Source Voltage



Figure 10. t_{ON}/t_{OFF} Times vs. Temperature



Figure 11. Bandwidth



Figure 12. Off isolation vs. Frequency



Figure 13. Crosstalk vs. Frequency



Figure 14. Total Harmonic Distortion + Noise (THD+N) vs. Frequency



Figure 15. PSSR vs. Frequency

TEST CIRCUITS



Figure 16. On Resistance



Figure 17. Off Leakage



Figure 18. On Leakage



Figure 19. Switching Times, t_{ON}, t_{OFF}



Figure 20. Break-Before-Make Time Delay, t_{BBM}



Figure 21. Charge Injection



Figure 22. Off Isolation



Figure 24. Channel-to-Channel Crosstalk (S1 toS2)



Figure 23. Bandwidth

TERMINOLOGY

I_{DD}

Positive supply current.

V_D (V_S)

Analog voltage on Terminal D and Terminal S.

R_{ON}

Ohmic resistance between Terminal D and Terminal S.

R_{FLAT} (On)

The difference between the maximum and minimum values of on resistance as measured on the switch.

ΔR_{ON}

On resistance match between any two channels.

I_S (Off)

Source leakage current with the switch off.

I_D (Off)

Drain leakage current with the switch off.

I_D, I_S (On)

Channel leakage current with the switch on.

V_{INL}

Maximum input voltage for Logic 0.

V_{INH}

Minimum input voltage for Logic 1.

I_{INL} (I_{INH})

Input current of the digital input.

C_S (Off)

Off switch source capacitance. Measured with reference to ground.

C_D, C_S (On)

On switch capacitance. Measured with reference to ground.

C_{IN}

Digital input capacitance.

t_{ON}

Delay time between the 50% and 90% points of the digital input and switch on condition.

t_{OFF}

Delay time between the 50% and 90% points of the digital input and switch off condition.

t_{BBM}

On or off time measured between the 80% points of both switches when switching from one to another.

Charge Injection

Measure of the glitch impulse transferred from the digital input to the analog output during on/off switching.

Off Isolation

Measure of unwanted signal coupling through an off switch.

Crosstalk

Measure of unwanted signal that is coupled from one channel to another as a result of parasitic capacitance.

−3 dB Bandwidth

Frequency at which the output is attenuated by 3 dB.

Insertion Loss

The loss due to the on resistance of the switch.

THD + N

Ratio of the harmonics amplitude plus noise of a signal to the fundamental.

OUTLINE DIMENSIONS



Figure 25. 10-Lead Lead Frame Chip Scale Package [LFCSP_UQ]
1.30 mm × 1.60 mm Body, Ultrathin Quad
(CP-10-10)
Dimensions shown in millimeters

ORDERING GUIDE

Model[1]	Temperature Range	Package Description	Package Option	Branding
ADG852BCPZ-REEL7	−40°C to +85°C	10-Lead Lead Frame Chip Scale Package (LFCSP_UQ)	CP-10-10	F

[1]Z = RoHS Compliant Part.

NOTES

NOTES

NOTES

D07461-0-5/12(B)