

Distributed by:

JAMECO[®]
ELECTRONICS

www.Jameco.com ♦ 1-800-831-4242

The content and copyrights of the attached
material are the property of its owner.

Jameco Part Number 1918761

120X120X38 mm

KA1238-1 Series



- **Motor** : Two-pole shaded pole induction motor
- **Frame** : Aluminum Alloy, Painted black
- **Impeller** : Retardant thermoplastic in black color, rated UL94V-0
- **Speed Range** : $\pm 10\%$
- **Impedance protected**

SPECIFICATIONS

Model	Bearing	Nominal Voltage (V)	Frequency (Hz)	Air Flow (CFM)	Static Pressure (inchH ₂ O)	Speed (R.P.M.)	Nominal Current (Amp)	Input Power (Watt)	Noise (dBA)	Weight (g)
KA1238H1B1	Dual Ball	100 - 125	50/60	97/110	0.291/0.339	2600/3000	0.30	29/24	41/45	560
KA1238M1B1			50/60	90/100	0.236/0.276	2400/2700	0.25	19/17	39/42	
KA1238L1B1A			50/60	90/90	0.267/0.214	2450/2450	0.20	14/13	38/38	
KA1238L1B1B			50/60	80/54	0.160/0.130	2100/1500	0.20	11/10	35/27	
KA1238L1B1C			50/60	90/80	0.187/0.140	2400/2100	0.20	17/16	39/35	
KA1238H1S1	Sleeve		50/60	97/110	0.291/0.339	2600/3000	0.30	29/24	41/45	
KA1238M1S1			50/60	90/100	0.236/0.276	2400/2700	0.25	19/17	39/42	
KA1238L1S1A			50/60	90/90	0.267/0.214	2450/2450	0.20	14/13	38/38	
KA1238L1S1B			50/60	80/54	0.160/0.130	2100/1500	0.20	11/10	35/27	
KA1238L1S1C			50/60	90/80	0.187/0.140	2400/2100	0.20	17/16	39/35	
KA1238H2B1	Dual Ball	220 - 240	50/60	97/110	0.291/0.339	2600/3000	0.20	28/24	41/45	
KA1238M2B1			50/60	90/100	0.236/0.276	2400/2700	0.16	16/15	39/42	
KA1238L2B1A			50/60	90/90	0.267/0.214	2450/2450	0.10	14/13	38/38	
KA1238L2B1B			50/60	80/54	0.160/0.130	2100/1500	0.10	11/10	35/27	
KA1238L2B1C			50/60	90/80	0.187/0.140	2400/2100	0.10	17/16	39/35	
KA1238H2S1	Sleeve		50/60	97/110	0.291/0.339	2600/3000	0.20	28/24	41/45	
KA1238M2S1			50/60	90/100	0.236/0.276	2400/2700	0.16	16/15	39/42	
KA1238L2S1A			50/60	90/90	0.267/0.214	2450/2450	0.10	14/13	38/38	
KA1238L2S1B			50/60	80/54	0.160/0.130	2100/1500	0.10	11/10	35/27	
KA1238L2S1C			50/60	90/80	0.187/0.140	2400/2100	0.20	17/16	39/35	

Specifications subject to change without notice

