






NOTES: UNLESS OTHERWISE SPECIFIED;

- 1 CONNECTOR MATERIALS:
HOUSING: GLASS FILLED THERMOPLASTIC,
UL94-V0 COMPLIANT
KEEPER: GLASS FILLED THERMOPLASTIC,
UL94-V0 COMPLIANT
TERMINAL: PHOSPHOR BRONZE ALLOY
- 2 PACKED IN TUBES
- ③ FEATURE MAY OR MAY NOT BE PRESENT DEPENDING UPON THE MOLD TOOL USED TO PRODUCE PRODUCT.
- 4 PRODUCT SPECIFICATION: GS-12-177.
- 5 APPLICATION SPECIFICATION: GS-20-015.
- 6 THE PRODUCTS WHERE THE PART NUMBER ENDS IN 'LF' MEET THE EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
- 7 ALL PRODUCTS WILL WITHSTAND EXPOSURE TO 260°C FOR 60 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW OVEN.
- 8 LOCATION PEGS ARE ONLY EXISTED IN ONE MODULE



Copyright FCI.

rev	ecn no	dr	date
J	V04-1123	TAB	02/03/05
K	V05-0439	VS	07/14/05
L	DG06-0378	KL	09/05/06
M	DG06-0434	Cenh	10/23/06
N	DG06-0534	Cenh	14/12/06
P	DG08-0173	TER	02/07/08
R	N10-0382	Cenh	11/12/10

www.fciconnect.com			surface	tolerance std	projection	MM	
			ANGULAR	LINEAR	size	A4	Scale 4:1
Dr	V. SEBASTIAN	07/14/05	0°	±2°	0.X	± 0.50	ECN N10-0382
Eng	J. VOLSTROF	07/14/05			0.XX	± 0.13	
Chr	J. VOLSTROF	07/14/05			0.XXX	± -	
Appr	J. VOLSTROF	07/14/05	Product family		METRAL	Spec ref	
FCI			title			dwg no	Rev.
			T SERIES R/A RECEPTACLE			SE96847	R
			ASSY, 5 ROW, STB				
			catalog no			CUSTOMER	sheet 1 of 3



OBSELETE


CODE	CONTACT AREA	PERFORMANCE LEVEL
6 or	0.75m Au min over 1.3m Ni min 0.68m PdNi min m Au min over 1.3m Ni min	+0.08 TELCORDIA CD

C

D



I



www.fciconnect.com			surface ☒		tolerance std		projection 		MM 		
			TOLERANCES UNLESS OTHERWISE SPECIFIED								
Dr	V. SEBASTIAN	07/14/05	ANGULAR		LINEAR	0.X	± 0.50	size	A4	Scale 4:1	
Eng	J. VOLSTROF	07/14/05				0.XX	± 0.13				
Chr	J. VOLSTROF	07/14/05	0°	±2°		0.XXX	± -	ECN	N10-0382		
Appr	J. VOLSTROF	07/14/05	Product family			METRAL		Spec ref			
	T SERIES R/A RECEPTACLE ASSY, 5 ROW, STB					dwg no			SE96847		Rev. R
						catalog no			CUSTOMER		sheet 3of 3