



JIANGSU CHANGJIANG ELECTRONICS TECHNOLOGY CO., LTD

SOT-23-3L Encapsulate Three Terminal Voltage Regulator

CJ79L12 Three-terminal negative voltage regulator

FEATURES

Maximum Output current

I_{OM} : 0.1 A

Output voltage


V_O : -12 V

SOT-23-3L

1. GND

2. OUT

3. IN



ABSOLUTE MAXIMUM RATINGS (Operating temperature range applies unless otherwise specified)


Parameter	Symbol	Value	Unlts
Input Voltage	V_i	-35	V
Operating Junction Temperature Range	T_{OPR}	0—+125	°C
Storage Temperature Range	T_{STG}	-55—+150	°C

ELECTRICAL CHARACTERISTICS


($V_i = -19V, I_o = 40mA, 0^\circ C < T_j < 125^\circ C, C_1 = 0.33 \mu F, C_o = 0.1 \mu F$, unless otherwise specified)

Parameter	Symbol	Test conditions	MIN	TYP	MAX	UNIT
Output voltage	V_O	$V_{IN} = -19V, I_o = 40mA$	-11.5	-12.0	-12.5	V
Line Regulation	$V_O - V_{IN}$	$V_{IN} = -14.5 \sim -27V, I_o = 40mA$		50	250	mV
Load Regulation	$V_O - I_o$	$V_{IN} = -19V, I_o = 1 \sim 100mA$		24	100	mV
Quiescent Current	I_Q	$V_{IN} = -19V, I_o = 40mA$			6.5	mA
Ripple Rejection	RR	$V_{IN} = -15V \sim -25V, I_o = 40mA, e_{IN} = 1V_{P-P}, f = 120Hz$	37	42		dB
Output Noise Voltage	V_{NO}	$V_{IN} = -19V, f = 10Hz \sim 100KH, I_o = 40mA$		80		μV

TYPICAL APPLICATION



SOT-23-3L PACKAGE OUTLINE DIMENSIONS



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min	Max	Min	Max
A	1.050	1.250	0.041	0.049
A1	0.000	0.100	0.000	0.004
A2	1.050	1.150	0.041	0.045
b	0.300	0.400	0.012	0.016
c	0.100	0.200	0.004	0.008
D	2.820	3.020	0.111	0.119
E	1.500	1.700	0.059	0.067
E1	2.650	2.950	0.104	0.116
e	0.950TPY		0.037TPY	
e1	1.800	2.000	0.071	0.079
L	0.700REF		0.028REF	
L1	0.300	0.600	0.012	0.024
θ	0°	8°	0°	8°