

# MC74AC257, MC74ACT257

## Quad 2-Input Multiplexer with 3-State Outputs

The MC74AC257/74ACT257 is a quad 2-input multiplexer with 3-state outputs. Four bits of data from two sources can be selected using a Common Data Select input. The four outputs present the selected data in true (noninverted) form. The outputs may be switched to a high impedance state by placing a logic HIGH on the common Output Enable ( $\overline{OE}$ ) input, allowing the outputs to interface directly with bus-oriented systems.

- Multiplexer Expansion by Tying Outputs Together
- Noninverting 3-State Outputs
- Outputs Source/Sink 24 mA
- 'ACT257 Has TTL Compatible Inputs
- These devices are available in Pb-free package(s). Specifications herein apply to both standard and Pb-free devices. Please see our website at [www.onsemi.com](http://www.onsemi.com) for specific Pb-free orderable part numbers, or contact your local ON Semiconductor sales office or representative.





Figure 1. Pinout: 16-Lead Packages Conductors  
(Top View)




ON Semiconductor®


<http://onsemi.com>




DIP-16  
N SUFFIX  
CASE 648



SO-16  
D SUFFIX  
CASE 751B



TSSOP-16  
DT SUFFIX  
CASE 948F



EIAJ-16  
M SUFFIX  
CASE 966

### ORDERING INFORMATION

| Device         | Package  | Shipping         |
|----------------|----------|------------------|
| MC74AC257N     | PDIP-16  | 25 Units/Rail    |
| MC74ACT257N    | PDIP-16  | 25 Units/Rail    |
| MC74AC257D     | SOIC-16  | 48 Units/Rail    |
| MC74ACT257D    | SOIC-16  | 48 Units/Rail    |
| MC74AC257DR2   | SOIC-16  | 2500 Tape & Reel |
| MC74ACT257DR2  | SOIC-16  | 2500 Tape & Reel |
| MC74AC257DT    | TSSOP-16 | 96 Units/Rail    |
| MC74ACT257DT   | TSSOP-16 | 96 Units/Rail    |
| MC74AC257DTR2  | TSSOP-16 | 2500 Tape & Reel |
| MC74ACT257DTR2 | TSSOP-16 | 2500 Tape & Reel |
| MC74ACT257M    | EIAJ-16  | 50 Units/Rail    |
| MC74AC257MEL   | EIAJ-16  | 2000 Tape & Reel |
| MC74ACT257MEL  | EIAJ-16  | 2000 Tape & Reel |

### DEVICE MARKING INFORMATION

See general marking information in the device marking section on page 8 of this data sheet.

# MC74AC257, MC74ACT257

## PIN NAME

| PIN             | FUNCTION                    |
|-----------------|-----------------------------|
| S               | Common Data Select Input    |
| $\overline{OE}$ | 3-State Output Enable Input |
| $I_{0a}-I_{0d}$ | Data Inputs from Source 0   |
| $I_{1a}-I_{1d}$ | Data Inputs from Source 1   |
| $Z_a-Z_d$       | 3-State Multiplexer Outputs |

## TRUTH TABLE

| Output Enable   | Select Input | Data Inputs |       | Outputs |
|-----------------|--------------|-------------|-------|---------|
| $\overline{OE}$ | S            | $I_0$       | $I_1$ | Z       |
| H               | X            | X           | X     | Z       |
| L               | H            | X           | L     | L       |
| L               | H            | X           | H     | H       |
| L               | L            | L           | X     | L       |
| L               | L            | H           | X     | H       |

H = HIGH Voltage Level

L = LOW Voltage Level

X = Immaterial

Z = High Impedance




Figure 2. Logic Symbol

## FUNCTIONAL DESCRIPTION

The MC74AC257/74ACT257 is a quad 2-input multiplexer with 3-state outputs. It selects four bits of data from two sources under control of a Common Data Select input. When the Select input is LOW, the  $I_{0x}$  inputs are selected and when Select is HIGH, the  $I_{1x}$  inputs are selected. The data on the selected inputs appears at the outputs in true (noninverted) form. The device is the logic

implementation of a 4-pole, 2-position switch where the position of the switch is determined by the logic levels supplied to the Select input. The logic equations for the outputs are shown below:

$$Z_a = \overline{OE} \cdot (I_{1a} \cdot S + I_{0a} \cdot \overline{S})$$


$$Z_b = \overline{OE} \cdot (I_{1b} \cdot S + I_{0b} \cdot \overline{S})$$

$$Z_c = \overline{OE} \cdot (I_{1c} \cdot S + I_{0c} \cdot \overline{S})$$

$$Z_d = \overline{OE} \cdot (I_{1d} \cdot S + I_{0d} \cdot \overline{S})$$

When the Output Enable input ( $\overline{OE}$ ) is HIGH, the outputs are forced to a high impedance state. If the outputs are tied together, all but one device must be in the high impedance state to avoid high currents that would exceed the maximum ratings. Designers should ensure the Output Enable signals to 3-state devices whose outputs are tied together are designed so there is no overlap.

# MC74AC257, MC74ACT257



**Figure 3. Logic Diagram**

# MC74AC257, MC74ACT257

## MAXIMUM RATINGS\*

| Symbol    | Parameter                                 | Value                 | Unit |
|-----------|-------------------------------------------|-----------------------|------|
| $V_{CC}$  | DC Supply Voltage (Referenced to GND)     | -0.5 to +7.0          | V    |
| $V_{IN}$  | DC Input Voltage (Referenced to GND)      | -0.5 to $V_{CC}$ +0.5 | V    |
| $V_{OUT}$ | DC Output Voltage (Referenced to GND)     | -0.5 to $V_{CC}$ +0.5 | V    |
| $I_{IN}$  | DC Input Current, per Pin                 | $\pm 20$              | mA   |
| $I_{OUT}$ | DC Output Sink/Source Current, per Pin    | $\pm 50$              | mA   |
| $I_{CC}$  | DC $V_{CC}$ or GND Current per Output Pin | $\pm 50$              | mA   |
| $T_{stg}$ | Storage Temperature                       | -65 to +150           | °C   |

\*Maximum Ratings are those values beyond which damage to the device may occur. Functional operation should be restricted to the Recommended Operating Conditions.

## RECOMMENDED OPERATING CONDITIONS

| Symbol            | Parameter                                                               | Min              | Typ | Max      | Unit |
|-------------------|-------------------------------------------------------------------------|------------------|-----|----------|------|
| $V_{CC}$          | Supply Voltage                                                          | 'AC              | 2.0 | 5.0      | V    |
|                   |                                                                         | 'ACT             | 4.5 | 5.0      |      |
| $V_{IN}, V_{OUT}$ | DC Input Voltage, Output Voltage (Ref. to GND)                          | 0                | -   | $V_{CC}$ | V    |
| $t_r, t_f$        | Input Rise and Fall Time (Note 1)<br>'AC Devices except Schmitt Inputs  | $V_{CC}$ @ 3.0 V | -   | 150      | ns/V |
|                   |                                                                         | $V_{CC}$ @ 4.5 V | -   | 40       |      |
|                   |                                                                         | $V_{CC}$ @ 5.5 V | -   | 25       |      |
| $t_r, t_f$        | Input Rise and Fall Time (Note 2)<br>'ACT Devices except Schmitt Inputs | $V_{CC}$ @ 4.5 V | -   | 10       | ns/V |
|                   |                                                                         | $V_{CC}$ @ 5.5 V | -   | 8.0      |      |
| $T_J$             | Junction Temperature (PDIP)                                             | -                | -   | 140      | °C   |
| $T_A$             | Operating Ambient Temperature Range                                     | -40              | 25  | 85       | °C   |
| $I_{OH}$          | Output Current – High                                                   | -                | -   | -24      | mA   |
| $I_{OL}$          | Output Current – Low                                                    | -                | -   | 24       | mA   |

1.  $V_{in}$  from 30% to 70%  $V_{CC}$ ; see individual Data Sheets for devices that differ from the typical input rise and fall times.
2.  $V_{in}$  from 0.8 V to 2.0 V; see individual Data Sheets for devices that differ from the typical input rise and fall times.

# MC74AC257, MC74ACT257

## DC CHARACTERISTICS

| Symbol           | Parameter                            | V <sub>CC</sub><br>(V) | 74AC                   |                   | 74AC                                  | Unit | Conditions                                                                                                                                  |
|------------------|--------------------------------------|------------------------|------------------------|-------------------|---------------------------------------|------|---------------------------------------------------------------------------------------------------------------------------------------------|
|                  |                                      |                        | T <sub>A</sub> = +25°C |                   | T <sub>A</sub> =<br>–40°C to<br>+85°C |      |                                                                                                                                             |
|                  |                                      |                        | Typ                    | Guaranteed Limits |                                       |      |                                                                                                                                             |
| V <sub>IH</sub>  | Minimum High Level<br>Input Voltage  | 3.0                    | 1.5                    | 2.1               | 2.1                                   | V    | V <sub>OUT</sub> = 0.1 V<br>or V <sub>CC</sub> – 0.1 V                                                                                      |
|                  |                                      | 4.5                    | 2.25                   | 3.15              | 3.15                                  |      |                                                                                                                                             |
|                  |                                      | 5.5                    | 2.75                   | 3.85              | 3.85                                  |      |                                                                                                                                             |
| V <sub>IL</sub>  | Maximum Low Level<br>Input Voltage   | 3.0                    | 1.5                    | 0.9               | 0.9                                   | V    | V <sub>OUT</sub> = 0.1 V<br>or V <sub>CC</sub> – 0.1 V                                                                                      |
|                  |                                      | 4.5                    | 2.25                   | 1.35              | 1.35                                  |      |                                                                                                                                             |
|                  |                                      | 5.5                    | 2.75                   | 1.65              | 1.65                                  |      |                                                                                                                                             |
| V <sub>OH</sub>  | Minimum High Level<br>Output Voltage | 3.0                    | 2.99                   | 2.9               | 2.9                                   | V    | I <sub>OUT</sub> = –50 μA                                                                                                                   |
|                  |                                      | 4.5                    | 4.49                   | 4.4               | 4.4                                   |      |                                                                                                                                             |
|                  |                                      | 5.5                    | 5.49                   | 5.4               | 5.4                                   |      |                                                                                                                                             |
|                  |                                      | 3.0                    | –                      | 2.56              | 2.46                                  | V    | *V <sub>IN</sub> = V <sub>IL</sub> or V <sub>IH</sub><br>–12 mA<br>I <sub>OH</sub> –24 mA<br>–24 mA                                         |
|                  |                                      | 4.5                    | –                      | 3.86              | 3.76                                  |      |                                                                                                                                             |
|                  |                                      | 5.5                    | –                      | 4.86              | 4.76                                  |      |                                                                                                                                             |
| V <sub>OL</sub>  | Maximum Low Level<br>Output Voltage  | 3.0                    | 0.002                  | 0.1               | 0.1                                   | V    | I <sub>OUT</sub> = 50 μA                                                                                                                    |
|                  |                                      | 4.5                    | 0.001                  | 0.1               | 0.1                                   |      |                                                                                                                                             |
|                  |                                      | 5.5                    | 0.001                  | 0.1               | 0.1                                   |      |                                                                                                                                             |
|                  |                                      | 3.0                    | –                      | 0.36              | 0.44                                  | V    | *V <sub>IN</sub> = V <sub>IL</sub> or V <sub>IH</sub><br>12 mA<br>I <sub>OL</sub> 24 mA<br>24 mA                                            |
|                  |                                      | 4.5                    | –                      | 0.36              | 0.44                                  |      |                                                                                                                                             |
|                  |                                      | 5.5                    | –                      | 0.36              | 0.44                                  |      |                                                                                                                                             |
| I <sub>IN</sub>  | Maximum Input<br>Leakage Current     | 5.5                    | –                      | ±0.1              | ±1.0                                  | μA   | V <sub>I</sub> = V <sub>CC</sub> , GND                                                                                                      |
| I <sub>OZ</sub>  | Maximum<br>3–State<br>Current        | 5.5                    | –                      | ±0.5              | ±5.0                                  | μA   | V <sub>I</sub> (OE) = V <sub>IL</sub> , V <sub>IH</sub><br>V <sub>I</sub> = V <sub>CC</sub> , GND<br>V <sub>O</sub> = V <sub>CC</sub> , GND |
| I <sub>OLD</sub> | †Minimum Dynamic<br>Output Current   | 5.5                    | –                      | –                 | 75                                    | mA   | V <sub>OLD</sub> = 1.65 V Max                                                                                                               |
| I <sub>OHD</sub> |                                      | 5.5                    | –                      | –                 | –75                                   | mA   | V <sub>OHD</sub> = 3.85 V Min                                                                                                               |
| I <sub>CC</sub>  | Maximum Quiescent<br>Supply Current  | 5.5                    | –                      | 8.0               | 80                                    | μA   | V <sub>IN</sub> = V <sub>CC</sub> or GND                                                                                                    |

\*All outputs loaded; thresholds on input associated with output under test.

†Maximum test duration 2.0 ms, one output loaded at a time.

NOTE: I<sub>IN</sub> and I<sub>CC</sub> @ 3.0 V are guaranteed to be less than or equal to the respective limit @ 5.5 V V<sub>CC</sub>.

# MC74AC257, MC74ACT257

**AC CHARACTERISTICS** (For Figures and Waveforms – See Section 3 of the ON Semiconductor FACT Data Book, DL138/D)

| Symbol           | Parameter                                             | V <sub>CC</sub> *<br>(V) | 74AC                                             |            |             | 74AC                                                         |              | Unit | Fig. No. |
|------------------|-------------------------------------------------------|--------------------------|--------------------------------------------------|------------|-------------|--------------------------------------------------------------|--------------|------|----------|
|                  |                                                       |                          | T <sub>A</sub> = +25°C<br>C <sub>L</sub> = 50 pF |            |             | T <sub>A</sub> = -40°C<br>to +85°C<br>C <sub>L</sub> = 50 pF |              |      |          |
|                  |                                                       |                          | Min                                              | Typ        | Max         | Min                                                          | Max          |      |          |
| t <sub>PLH</sub> | Propagation Delay<br>I <sub>n</sub> to Z <sub>n</sub> | 3.3<br>5.0               | 1.5<br>1.5                                       | 5.0<br>4.0 | 8.5<br>6.0  | 1.0<br>1.0                                                   | 9.0<br>7.0   | ns   | 3-5      |
| t <sub>PHL</sub> | Propagation Delay<br>I <sub>n</sub> to Z <sub>n</sub> | 3.3<br>5.0               | 1.5<br>1.5                                       | 6.0<br>4.5 | 8.5<br>6.0  | 1.0<br>1.0                                                   | 9.0<br>7.0   | ns   | 3-5      |
| t <sub>PLH</sub> | Propagation Delay<br>S to Z <sub>n</sub>              | 3.3<br>5.0               | 1.5<br>1.5                                       | 7.0<br>5.0 | 10.5<br>7.5 | 1.5<br>1.0                                                   | 11.5<br>8.5  | ns   | 3-6      |
| t <sub>PHL</sub> | Propagation Delay<br>S to Z <sub>n</sub>              | 3.3<br>5.0               | 1.5<br>1.5                                       | 7.5<br>5.5 | 10.5<br>7.5 | 1.5<br>1.0                                                   | 11.5<br>8.5  | ns   | 3-6      |
| t <sub>PZH</sub> | Output Enable Time                                    | 3.3<br>5.0               | 1.5<br>1.5                                       | 6.5<br>5.0 | 9.5<br>7.5  | 1.0<br>1.0                                                   | 10.5<br>8.5  | ns   | 3-7      |
| t <sub>PZL</sub> | Output Enable Time                                    | 3.3<br>5.0               | 1.5<br>1.5                                       | 5.5<br>5.0 | 9.0<br>8.5  | 1.0<br>1.0                                                   | 10.0<br>9.5  | ns   | 3-8      |
| t <sub>PHZ</sub> | Output Disable Time                                   | 3.3<br>5.0               | 1.5<br>1.5                                       | 5.5<br>5.0 | 10.0<br>9.0 | 1.0<br>1.0                                                   | 11.0<br>10.0 | ns   | 3-7      |
| t <sub>PLZ</sub> | Output Disable Time                                   | 3.3<br>5.0               | 1.5<br>1.5                                       | 5.5<br>5.0 | 9.0<br>8.0  | 1.0<br>1.0                                                   | 10.0<br>9.0  | ns   | 3-8      |

\*Voltage Range 3.3 V is 3.3 V ±0.3 V.

\*Voltage Range 5.0 V is 5.0 V ±0.5 V.

# MC74AC257, MC74ACT257

## DC CHARACTERISTICS

| Symbol            | Parameter                              | V <sub>CC</sub><br>(V) | 74ACT                  |                   | 74ACT                                 | Unit | Conditions                                                                                                                                  |
|-------------------|----------------------------------------|------------------------|------------------------|-------------------|---------------------------------------|------|---------------------------------------------------------------------------------------------------------------------------------------------|
|                   |                                        |                        | T <sub>A</sub> = +25°C |                   | T <sub>A</sub> =<br>–40°C to<br>+85°C |      |                                                                                                                                             |
|                   |                                        |                        | Typ                    | Guaranteed Limits |                                       |      |                                                                                                                                             |
| V <sub>IH</sub>   | Minimum High Level<br>Input Voltage    | 4.5<br>5.5             | 1.5<br>1.5             | 2.0<br>2.0        | 2.0<br>2.0                            | V    | V <sub>OUT</sub> = 0.1 V<br>or V <sub>CC</sub> – 0.1 V                                                                                      |
| V <sub>IL</sub>   | Maximum Low Level<br>Input Voltage     | 4.5<br>5.5             | 1.5<br>1.5             | 0.8<br>0.8        | 0.8<br>0.8                            | V    | V <sub>OUT</sub> = 0.1 V<br>or V <sub>CC</sub> – 0.1 V                                                                                      |
| V <sub>OH</sub>   | Minimum High Level<br>Output Voltage   | 4.5<br>5.5             | 4.49<br>5.49           | 4.4<br>5.4        | 4.4<br>5.4                            | V    | I <sub>OUT</sub> = –50 μA                                                                                                                   |
|                   |                                        | 4.5<br>5.5             | –<br>–                 | 3.86<br>4.86      | 3.76<br>4.76                          | V    | *V <sub>IN</sub> = V <sub>IL</sub> or V <sub>IH</sub><br>–24 mA<br>I <sub>OH</sub> –24 mA                                                   |
| V <sub>OL</sub>   | Maximum Low Level<br>Output Voltage    | 4.5<br>5.5             | 0.001<br>0.001         | 0.1<br>0.1        | 0.1<br>0.1                            | V    | I <sub>OUT</sub> = 50 μA                                                                                                                    |
|                   |                                        | 4.5<br>5.5             | –<br>–                 | 0.36<br>0.36      | 0.44<br>0.44                          | V    | *V <sub>IN</sub> = V <sub>IL</sub> or V <sub>IH</sub><br>24 mA<br>I <sub>OL</sub> 24 mA                                                     |
| I <sub>IN</sub>   | Maximum Input<br>Leakage Current       | 5.5                    | –                      | ±0.1              | ±1.0                                  | μA   | V <sub>I</sub> = V <sub>CC</sub> , GND                                                                                                      |
| ΔI <sub>CCT</sub> | Additional Max. I <sub>CC</sub> /Input | 5.5                    | 0.6                    | –                 | 1.5                                   | mA   | V <sub>I</sub> = V <sub>CC</sub> – 2.1 V                                                                                                    |
| I <sub>OZ</sub>   | Maximum<br>3–State<br>Current          | 5.5                    | –                      | ±0.5              | ±5.0                                  | μA   | V <sub>I</sub> (OE) = V <sub>IL</sub> , V <sub>IH</sub><br>V <sub>I</sub> = V <sub>CC</sub> , GND<br>V <sub>O</sub> = V <sub>CC</sub> , GND |
| I <sub>OLD</sub>  | †Minimum Dynamic<br>Output Current     | 5.5                    | –                      | –                 | 75                                    | mA   | V <sub>OLD</sub> = 1.65 V Max                                                                                                               |
| I <sub>OHD</sub>  |                                        | 5.5                    | –                      | –                 | –75                                   | mA   | V <sub>OHD</sub> = 3.85 V Min                                                                                                               |
| I <sub>CC</sub>   | Maximum Quiescent<br>Supply Current    | 5.5                    | –                      | 8.0               | 80                                    | μA   | V <sub>IN</sub> = V <sub>CC</sub> or GND                                                                                                    |

\*All outputs loaded; thresholds on input associated with output under test.

†Maximum test duration 2.0 ms, one output loaded at a time.

# MC74AC257, MC74ACT257

**AC CHARACTERISTICS** (For Figures and Waveforms – See Section 3 of the ON Semiconductor FACT Data Book, DL138/D)


| Symbol           | Parameter                                             | V <sub>CC</sub> *<br>(V) | 74ACT                                            |     |      | 74ACT                                                        |      | Unit | Fig. No. |
|------------------|-------------------------------------------------------|--------------------------|--------------------------------------------------|-----|------|--------------------------------------------------------------|------|------|----------|
|                  |                                                       |                          | T <sub>A</sub> = +25°C<br>C <sub>L</sub> = 50 pF |     |      | T <sub>A</sub> = –40°C<br>to +85°C<br>C <sub>L</sub> = 50 pF |      |      |          |
|                  |                                                       |                          | Min                                              | Typ | Max  | Min                                                          | Max  |      |          |
| t <sub>PLH</sub> | Propagation Delay<br>I <sub>n</sub> to Z <sub>n</sub> | 5.0                      | 1.5                                              | 5.0 | 7.0  | 1.0                                                          | 7.5  | ns   | 3–6      |
| t <sub>PHL</sub> | Propagation Delay<br>I <sub>n</sub> to Z <sub>n</sub> | 5.0                      | 2.0                                              | 6.0 | 7.5  | 1.5                                                          | 8.5  | ns   | 3–6      |
| t <sub>PLH</sub> | Propagation Delay<br>S to Z <sub>n</sub>              | 5.0                      | 2.0                                              | 7.0 | 9.5  | 1.5                                                          | 10.5 | ns   | 3–6      |
| t <sub>PHL</sub> | Propagation Delay<br>S to Z <sub>n</sub>              | 5.0                      | 2.5                                              | 7.0 | 10.5 | 2.0                                                          | 11.5 | ns   | 3–6      |
| t <sub>PZH</sub> | Output Enable Time                                    | 5.0                      | 2.0                                              | 6.0 | 8.0  | 1.5                                                          | 9.0  | ns   | 3–7      |
| t <sub>PZL</sub> | Output Enable Time                                    | 5.0                      | 2.0                                              | 6.0 | 8.0  | 1.5                                                          | 9.0  | ns   | 3–8      |
| t <sub>PHZ</sub> | Output Disable Time                                   | 5.0                      | 2.5                                              | 6.5 | 9.0  | 1.5                                                          | 10.0 | ns   | 3–7      |
| t <sub>PLZ</sub> | Output Disable Time                                   | 5.0                      | 2.0                                              | 6.0 | 7.5  | 1.5                                                          | 8.5  | ns   | 3–8      |

\*Voltage Range 5.0 V is 5.0 V ±0.5 V.

## CAPACITANCE

| Symbol          | Parameter                     | Value<br>Typ | Unit | Test Conditions         |
|-----------------|-------------------------------|--------------|------|-------------------------|
| C <sub>IN</sub> | Input Capacitance             | 4.5          | pF   | V <sub>CC</sub> = 5.0 V |
| C <sub>PD</sub> | Power Dissipation Capacitance | 50           | pF   | V <sub>CC</sub> = 5.0 V |

## MARKING DIAGRAMS




A = Assembly Location  
 WL, L = Wafer Lot  
 YY, Y = Year  
 WW, W = Work Week



# MC74AC257, MC74ACT257

## PACKAGE DIMENSIONS

### PDIP-16 N SUFFIX 16 PIN PLASTIC DIP PACKAGE CASE 648-08 ISSUE R




#### NOTES:

1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
2. CONTROLLING DIMENSION: INCH.
3. DIMENSION L TO CENTER OF LEADS WHEN FORMED PARALLEL.
4. DIMENSION B DOES NOT INCLUDE MOLD FLASH.
5. ROUNDED CORNERS OPTIONAL.

| DIM | INCHES    |       | MILLIMETERS |       |
|-----|-----------|-------|-------------|-------|
|     | MIN       | MAX   | MIN         | MAX   |
| A   | 0.740     | 0.770 | 18.80       | 19.55 |
| B   | 0.250     | 0.270 | 6.35        | 6.85  |
| C   | 0.145     | 0.175 | 3.69        | 4.44  |
| D   | 0.015     | 0.021 | 0.39        | 0.53  |
| F   | 0.040     | 0.70  | 1.02        | 1.77  |
| G   | 0.100 BSC |       | 2.54 BSC    |       |
| H   | 0.050 BSC |       | 1.27 BSC    |       |
| J   | 0.008     | 0.015 | 0.21        | 0.38  |
| K   | 0.110     | 0.130 | 2.80        | 3.30  |
| L   | 0.295     | 0.305 | 7.50        | 7.74  |
| M   | 0°        | 10°   | 0°          | 10°   |
| S   | 0.020     | 0.040 | 0.51        | 1.01  |

### SO-16 D SUFFIX 16 PIN PLASTIC SOIC PACKAGE CASE 751B-05 ISSUE J



#### NOTES:

1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
2. CONTROLLING DIMENSION: MILLIMETER.
3. DIMENSIONS A AND B DO NOT INCLUDE MOLD PROTRUSION.
4. MAXIMUM MOLD PROTRUSION 0.15 (0.006) PER SIDE.
5. DIMENSION D DOES NOT INCLUDE DAMBAR PROTRUSION. ALLOWABLE DAMBAR PROTRUSION SHALL BE 0.127 (0.005) TOTAL IN EXCESS OF THE D DIMENSION AT MAXIMUM MATERIAL CONDITION.

| DIM | MILLIMETERS |       | INCHES    |       |
|-----|-------------|-------|-----------|-------|
|     | MIN         | MAX   | MIN       | MAX   |
| A   | 9.80        | 10.00 | 0.386     | 0.393 |
| B   | 3.80        | 4.00  | 0.150     | 0.157 |
| C   | 1.35        | 1.75  | 0.054     | 0.068 |
| D   | 0.35        | 0.49  | 0.014     | 0.019 |
| F   | 0.40        | 1.25  | 0.016     | 0.049 |
| G   | 1.27 BSC    |       | 0.050 BSC |       |
| J   | 0.19        | 0.25  | 0.008     | 0.009 |
| K   | 0.10        | 0.25  | 0.004     | 0.009 |
| M   | 0°          | 7°    | 0°        | 7°    |
| P   | 5.80        | 6.20  | 0.229     | 0.244 |
| R   | 0.25        | 0.50  | 0.010     | 0.019 |



## **Notes**

## Notes

**ON Semiconductor** and  are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

### PUBLICATION ORDERING INFORMATION

**LITERATURE FULFILLMENT:**

Literature Distribution Center for ON Semiconductor  
P.O. Box 61312, Phoenix, Arizona 85082-1312 USA  
**Phone:** 480-829-7710 or 800-344-3860 Toll Free USA/Canada  
**Fax:** 480-829-7709 or 800-344-3867 Toll Free USA/Canada  
**Email:** [orderlit@onsemi.com](mailto:orderlit@onsemi.com)

**N. American Technical Support:** 800-282-9855 Toll Free  
USA/Canada

**Japan:** ON Semiconductor, Japan Customer Focus Center  
2-9-1 Kamimeguro, Meguro-ku, Tokyo, Japan 153-0051  
**Phone:** 81-3-5773-3850

**ON Semiconductor Website:** <http://onsemi.com>

**Order Literature:** <http://www.onsemi.com/litorder>

For additional information, please contact your  
local Sales Representative.