



TCSD-08-D-02.00-01-N-R

(2.00 mm) .0787"

TCSD SERIES

# TIGER EYE™ IDC SOCKET CABLE

## Mates with:

TMM, TMMH, STMM,  
MMT, TW, MTMM, EHT,  
ETMM (-SR), ZSTMM

## SPECIFICATIONS

For complete specifications  
see [www.samtec.com?TCSD](http://www.samtec.com?TCSD)

### Insulator Material:

Black Glass Filled Polyester

### Contact:

BeCu

### Plating:

Au or Sn over 50µ" (1,27 µm) Ni

### Wire:

28 AWG 7/36 Stranded,

Tinned, Copper with

Gray PVC Insulator

### Current Rating (TCSD/STMM):

2.8 A per pin

(1 pin powered per row)

### Operating Temp Range:

-40°C to +105°C

### Lead Size Accepted:

(0.48 mm) .019" to

(0.53 mm) .021"

### Contact Resistance:

15 mΩ

### Insertion Depth:

(2.87 mm) .113" to

(3.17 mm) .125"

### RoHS Compliant:

Yes

## RECOGNITIONS

For complete scope of  
recognitions see  
[www.samtec.com/quality](http://www.samtec.com/quality)



FILE NO. E111594




## ALSO AVAILABLE (MOQ Required)

- Other sizes
  - Other platings
- Contact Samtec.

## POLARIZING KEY

Specify PK-01-07 for  
polarizing key (Available  
in wheels of six each).  
Also polarizes SMM  
Series socket strips.

**Note:** TCSD Series  
assemblies are non-  
standard, non-returnable.



Specify "XX" as position  
number. Same position  
will be polarized on  
both ends.

Not available with -O, -M,  
-R, -DXX or -BXX

-B "XX"  
= Breakout

Specify "XX" as number of  
conductors to be broken out.

Breakout starts with Number 1  
lead indicated by brown wire or  
red stripe. Shown on top side.

-D "XX"  
= Daisy Chain

2" min. "XX" 1/8"  
Double Row Connectors  
Outer Most (End of assembly)

-RW  
= Reverse Wiring

Blue or black wire  
opposite position #1.

-R  
= Reversed

Requires -DXX


-M  
= Middle Reverse

Requires -DXX

-O  
= Outside Reverse

Requires -DXX

## EJECTOR HEADERS & LOCKING CLIPS



See TMM Series.

See EHT Series.

