





mat'l. code				surface				tolerance				projection				product family							
				ISO 1302 ✓				ISO 406 ISO 1101								QUICKIE							
ltr		ecn		nodr		date		tolerances unless otherwise specified												title			
H		N05-0123		ZC		5/9/05		angles		linear		.XX±.01/.XX±0.3		INCH/MM		HEADER, QUICKIE, SLIM LINE							
J		N07-0151		WG		8/02/07						.XXX±.005/.XXX±0.13				VERTICAL, 4-WALL							
K		ELX-N-012098		J.Z		2012-07-04		±2'				.XXX±.0020/.XXX±0.051		scale 2:1									
								dr		M. CLOUSER		7/11/90				dwg no		sheet 1 of 10		size			
								engr		M. SMYK		7/11/90				88880		A3					
								chr		M. SMYK		8/21/91											
								appd		M. SMYK		8/21/91				type		Product Customer Drawing					
sheet		revision		K		K		K		K		K		K		K		K		K		K	
index		sheet		1		2		3		4		5		6		7		8		9		10	

PRODUCT NUMBER
SEE TABLE

HEADER STYLE



RECOMMENDED BOARD LAYOUT

NOTES:

1. SAME POSITION TOLERANCE APPLIES TO BOTH ENDS OF PINS.
2. MOLDING MATERIAL: GLASS-FILLED POLYESTER, FLAME RETARDANT PER UL 94 V-0, COLOR: BLACK.
3. 1° MAX. DRAFT PERMISSIBLE ON ALL SURFACES.
4. 3 LBS./1.36 KG MIN. TERMINAL PULL-OUT FORCE.
5. TERMINAL MATERIAL: PHOSPHORUS BRONZE.
6. TO DETERMINE DIMENSIONS:
N = NUMBER OF POSITIONS PER ROW
7. SEE 68751 FOR LATCHES.
8. PART NUMBERS WITH "R" FOLLOWING THE PART NUMBER (EXAMPLE 66506-326 R) HAS RETENTION. (ONLY PARTS WITH .105, .120, AND .150 ROUND OR SQUARE TAILS CAN HAVE RETENTION.) LOCATION IS MANUFACTURERS OPTION.
FOR CONNECTORS:
RETENTIVE LEG APPLICABLE TO TAIL LENGTHS .125/3.18 MAX.
5LB/2.3KG MAX INSERTION FORCE AND .25LB/1KG MIN RETENTION FORCE
PER RETENTIVE PIN USING .062/1.57 THICK CIRCUIT BOARD AND RECOMMENDED HOLE PATTERN. RETENTIVE LOCATION AT THE DISCRETION OF THE MANUFACTURER. RETENTION PIN MAY BE SHIFTED TO NEXT POSITION.
9. PART NUMBERS WITH "T" FOLLOWING PART NUMBER (EXAMPLE 66506-068 T IS PACKED IN TUBES.) (CALL PRODUCT MANAGER FOR AVAILABILITY.)
10. MAY BE ORDERED WITH "G" PACK PACKAGING BY ADDING "G" TO DASH NUMBER.
11. UNDER PLATING: 50μ"/1.27μm Ni.
12. ADD "LF" SUFFIX AT THE END OF PART NUMBER FOR LEAD FREE OPTION & PART NUMBERS WITH "LF" SUFFIX ADDED IN THE TABLE ARE LEAD FREE.
13. IF "LF" P/N THE PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATION AS DESCRIBED IN GS-22-008.
14. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 15 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.57mm MINIMUM THICK CIRCUIT BOARD. SEE APPLICATION NOTES/PROCEDURES IF THEY ARE AVAILABLE.
15. "THIS PRODUCT HAS 100% TIN PLATING IN THE INTERFACE AND HAS NOT BEEN TESTED FOR WHISKER GROWTH IN ALL INTERCONNECT ENVIRONMENTS."
16. PLATING OPTIONS:
PERFORMANCE PLATING WILL BE EITHER GOLD OR GXT ON CONTACT OR TAIL, OPTIONALLY TIN ON TAIL.

mat'l. code		surface	tolerance	projection	product family	
		ISO 1302 ✓	ISO 406 ISO 1101		QUICKIE	
l	tr	ec	n	d	date	tolerances unless otherwise specified
K				angles	linear	$XXX \pm .01 / XXX \pm .03$
						$XXX \pm .005 / XXX \pm .013$
				$\pm 2^\circ$		$XXXX \pm .0020 / XXX \pm .051$
		dr	M. CLOUSER	7/11/90		
		engr	M. SMYK	7/11/90		
		chr	M. SMYK	8/21/91		
		appd	M. SMYK	8/21/91	scale 1:1	
sheet	revision					
index	sheet					



FCIconnect.com

Copyright FCI

D

PRODUCT NO. NOTE 8 & 9	SIZE	STYLE	DIM C	DIM J	PIN PLATING	PLASTIC MATERIAL
88880-001	2 X 5	B	. 400/10. 16	. 105/2. 67	30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni	NOTE 2
-002				. 150/3. 81	30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni	
-003				. 675/17. 15	30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni	
-004				. 105/2. 67	150u"/3. 81u TIN	
-005				. 150/3. 81	150u"/3. 81u TIN	
-006	2 X 5	B	. 400/10. 16	. 675/17. 15	150u"/3. 81u TIN	
-007	2 X 10	D	. 900/22. 86	. 105/2. 67	30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni	
-008				. 150/3. 81	30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni	
-009				. 675/17. 15	30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni	
-010				. 105/2. 67	150u"/3. 81u TIN	
-011				. 150/3. 81	150u"/3. 81u TIN	
-012	2 X 10		. 900/22. 86	. 675/17. 15	150u"/3. 81u TIN	
-013	2 X 13		1. 200/30. 48	. 105/2. 67	30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni	
-014				. 150/3. 81	30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni	
-015				. 675/17. 15	30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni	
-016				. 105/2. 67	150u"/3. 81u TIN	
-017				. 150/3. 81	150u"/3. 81u TIN	
-018	2 X 13		1. 200/30. 48	. 675/17. 15	150u"/3. 81u TIN	
-019	2 X 17		1. 600/40. 64	. 105/2. 67	30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni	
-020				. 150/3. 81	30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni	
-021				. 675/17. 15	30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni	
-022				. 105/2. 67	150u"/3. 81u TIN	
-023				. 150/3. 81	150u"/3. 81u TIN	
-024	2 X 17		1. 600/40. 64	. 675/17. 15	150u"/3. 81u TIN	
-025	2 X 20		1. 900/48. 26	. 105/2. 67	30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni	
-026				. 150/3. 81	30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni	
-027				. 675/17. 15	30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni	
-028				. 105/2. 67	150u"/3. 81u TIN	
-029				. 150/3. 81	150u"/3. 81u TIN	
-030	2 X 20		1. 900/48. 26	. 675/17. 15	150u"/3. 81u TIN	
-031	2 X 25		2. 400/60. 96	. 105/2. 67	30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni	
-032				. 150/3. 81	30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni	
-033				. 675/17. 15	30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni	
-034				. 105/2. 67	150u"/3. 81u TIN	
88880-035	2 X 25	D	2. 400/60. 96	. 150/3. 81	150u"/3. 81u TIN	NOTE 2

mat'l. code		surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family QUICKIE	
ltr ecn nchr date		tolerances unless otherwise specified		linear		INCH/MM		title HEADER, QUICKIE, SLIM LINE VERTICAL, 4-WALL	
K		angles		±2'		scale 1:1		dwg no 88880	
		dir		M. CLOUSER		7/11/90		shee 5 of 10 size A3	
		engr		M. SMYK		7/11/90			
		chr		M. SMYK		8/21/91			
		appd		M. SMYK		8/21/91		type Product Customer Drawing	
sheet index		revision sheet							



FCIconnect.com

Copyright FCI

D

PRODUCT NO.	SIZE	STYLE	DIM C	DIM J	PIN PLATING	PLASTIC MATERIAL
88880-036	2 X 25	D	2.400/60.96	.675/17.15	150u"/3.81u TIN	NOTE 2
-037	2 X 7	C	.600/15.24	.105/2.67	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-038				.150/3.81	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-039				.675/17.15	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-040				.105/2.67	150u"/3.81u TIN	
-041				.150/3.81	150u"/3.81u TIN	
-042	2 X 7	C	.600/15.24	.675/17.15	150u"/3.81u TIN	
-043	2 X 8	D	.700/17.78	.105/2.67	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-044				.150/3.81	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-045				.675/17.15	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-046				.105/2.67	150u"/3.81u TIN	
-047				.150/3.81	150u"/3.81u TIN	
-048	2 X 8	D	.700/17.78	.675/17.15	150u"/3.81u TIN	
-049	2 X 5	B	.400/10.16	.150/3.81	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-050	2 X 10	D	.900/22.86			
-051	2 X 13		1.200/30.48			
-052	2 X 17		1.600/40.64			
-053	2 X 20		1.900/48.26			
-054	2 X 25	D	2.400/60.96			
-055	2 X 7	C	.600/15.24			
-056	2 X 8	D	.700/17.78	.150/3.81		
-057	2 X 30		2.900/73.66	.105/2.67		
-058				.150/3.81		
-059				.675/17.15	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-060				.105/2.67	150u"/3.81u TIN	
-061				.150/3.81	150u"/3.81u TIN	
-062				.675/17.15	150u"/3.81u TIN	
-063				.105/2.67	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-064				.150/3.81		
-065	2 X 30	D	2.900/73.66	.675/17.15		
-066	2 X 5	B	.400/10.16	.105/2.67		
-067	2 X 5	B	.400/10.16	.675/17.15		
-068	2 X 7	C	.600/15.24	.105/2.67		
-069	2 X 7	C	.600/15.24	.675/17.15		
88880-070	2 X 8	D	.700/17.78	.105/2.67	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	NOTE 2

mat'l. code		surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family QUICKIE	
ltr ecn nodr date		tolerances unless otherwise specified		linear XX±.01/XX±.03 XX±.005/XX±.013 XX±.0020/XX±.0051		INCH/MM		title HEADER, QUICKIE, SLIM LINE VERTICAL, 4-WALL	
K		angles ±2°		scale 1:1		FCCI		dwg no 88880	
dir M. CLOUSER 7/11/90		engr M. SMYK 7/11/90		chr M. SMYK 8/21/91		appd M. SMYK 8/21/91		shee# of 10 size A3	
sheet index		revision sheet						type Product Customer Drawing	

1

2 3

4

5

6

PRODUCT NO. NOTE 8 & 9	SIZE	STYLE	DIM C	DIM J	PIN PLATING	PLASTIC MATERIAL
88880-071	2 X 8	D	. 700/17. 78	. 675/17. 15	30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni	NOTE 2
-072	2 X 10		. 900/22. 86	. 105/2. 67		
-073	2 X 10		. 900/22. 86	. 675/17. 15		
-074	2 X 13		1. 200/30. 48	. 105/2. 67		
-075	2 X 13		1. 200/30. 48	. 675/17. 15		
-076	2 X 17		1. 600/40. 64	. 105/2. 67		
-077	2 X 17		1. 600/40. 64	. 675/17. 15		
-078	2 X 20		1. 900/48. 26	. 105/2. 67		
-079	2 X 20		1. 900/48. 26	. 675/17. 15		
-080	2 X 25		2. 400/60. 96	. 105/2. 67		
-081	2 X 25	D	2. 400/60. 96	. 675/17. 15	30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni	
-082	2 X 5	B	. 400/10. 16	. 105/2. 67	15u"/0. 38u MIN (NOTE 16) OVER 50u"/1. 27u Ni	
-083	2 X 5	B	. 400/10. 16	. 150/3. 81		
-084	2 X 5	B	. 400/10. 16	. 675/17. 15		
-085	2 X 7	C	. 600/15. 24	. 105/2. 67		
-086	2 X 7	C	. 600/15. 24	. 150/3. 81		
-087	2 X 7	C	. 600/15. 24	. 675/17. 15		
-088	2 X 8	D	. 700/17. 78	. 105/2. 67		
-089	2 X 8		. 700/17. 78	. 150/3. 81		
-090	2 X 8		. 700/17. 78	. 675/17. 15		
-091	2 X 10		. 900/22. 86	. 105/2. 67		
-092	2 X 10		. 900/22. 86	. 150/3. 81		
-093	2 X 10		. 900/22. 86	. 675/17. 15		
-094	2 X 13		1. 200/30. 48	. 105/2. 67		
-095	2 X 13		1. 200/30. 48	. 150/3. 81		
-096	2 X 13		1. 200/30. 48	. 675/17. 15		
-097	2 X 17		1. 600/40. 64	. 105/2. 67		
-098	2 X 17		1. 600/40. 64	. 150/3. 81		
-099	2 X 17		1. 600/40. 64	. 675/17. 15		
-100	2 X 20		1. 900/48. 26	. 105/2. 67		
-101	2 X 20		1. 900/48. 26	. 150/3. 81		
-102	2 X 20		1. 900/48. 26	. 675/17. 15		
-103	2 X 25		2. 400/60. 96	. 105/2. 67		
-104	2 X 25		2. 400/60. 96	. 150/3. 81		
88880-105	2 X 25	D	2. 400/60. 96	. 675/17. 15	15u"/0. 38u MIN (NOTE 16) OVER 50u"/1. 27u Ni	NOTE 2

mat'l. code		surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection ⊕ ↖		product family QUICKIE	
ltr ecn ngr date		tolerances unless otherwise specified		linear		INCH/MM		title HEADER, QUICKIE, SLIM LINE VERTICAL, 4-WALL	
K		angles		±2'		scale 1:1		dwg no 88880	
		dr		M. CLOUSER		7/11/90		shee 5 of 10 size	
		engr		M. SMYK		7/11/90		A3	
		chr		M. SMYK		8/21/91			
		appd		M. SMYK		8/21/91		type Product Customer Drawing	
sheet index		revision sheet							

PRODUCT NO. NOTE 8 & 9	SIZE	STYLE	DIM C	DIM J	PIN PLATING	PLASTIC MATERIAL
88880-106	2 X 30	D	2. 900/73. 66	. 105/2. 67	15u" /0. 38u MIN (NOTE 16) OVER 50u" /1. 27u Ni	NOTE 2
-107	2 X 30	D	2. 900/73. 66	. 150/3. 81	15u" /0. 38u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-108	2 X 30	D	2. 900/73. 66	. 675/17. 15	15u" /0. 38u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-109	2 X 5	B	. 400/10. 16	. 105/2. 67	30u" /0. 76u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-110				. 150/3. 81	30u" /0. 76u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-111				. 675/17. 15	30u" /0. 76u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-112				. 105/2. 67	150u" /3. 81u TIN	
-113				. 150/3. 81	150u" /3. 81u TIN	
-114				. 675/17. 15	150u" /3. 81u TIN	
-115				. 105/2. 67	15u" /0. 38u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-116				. 150/3. 81	15u" /0. 38u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-117				. 675/17. 15	15u" /0. 38u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-118				. 105/2. 67	30u" /0. 76u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-119				. 150/3. 81	30u" /0. 76u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
88880-120	2 X 5	B	. 400/10. 16	. 675/17. 15	30u" /0. 76u MIN (NOTE 16) OVER 50u" /1. 27u Ni	NOTE 2
88880-121	DISCONTINUED					
THRU						
88880-216						
88880-217	2 X 12	D	1. 100/27. 94	. 105/2. 67	15u" /0. 38u MIN (NOTE 16) OVER 50u" /1. 27u Ni	NOTE 2
-218					30u" /0. 76u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-219					30u" /0. 76u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-220				. 105/2. 67	150u" /3. 81u TIN	
-221				. 150/3. 81	15u" /0. 38u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-222					30u" /0. 76u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-223					30u" /0. 76u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-224				. 150/3. 81	150u" /3. 81u TIN	
-225				. 675/17. 15	15u" /0. 38u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-226					30u" /0. 76u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-227					30u" /0. 76u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-228	2 X 12		1. 100/27. 94	. 675/17. 15	150u" /3. 81u TIN	
-229	2 X 15		1. 400/35. 56	. 105/2. 67	15u" /0. 38u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-230					30u" /0. 76u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-231					30u" /0. 76u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-232				. 105/2. 67	150u" /3. 81u TIN	
88880-233	2 X 15	D	1. 400/35. 56	. 150/3. 81	15u" /0. 38u MIN (NOTE 16) OVER 50u" /1. 27u Ni	NOTE 2

mat'l. code		surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family QUICKIE	
ltr ecn nodr date		tolerances unless otherwise specified		linear		INCH/MM		title HEADER, QUICKIE, SLIM LINE VERTICAL, 4-WALL	
K		angles		±2°		scale 1:1		dwg no 88880	
		dir		M. CLOUSER		7/11/90		shee 6 of 10 size	
		engr		M. SMYK		7/11/90		A3	
		chr		M. SMYK		8/21/91			
		appd		M. SMYK		8/21/91		type Product Customer Drawing	
sheet index		revision sheet							



FCIconnect.com

Copyright FCI

PRODUCT NO. NOTE 8 & 9	SIZE	STYLE	DIM C	DIM J	PIN PLATING	PLASTIC MATERIAL
88880-234	2 X 15	D	1. 400/35. 56	. 150/3. 81	30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni	NOTE 2
-235				. 150/3. 81	30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni	
-236				. 150/3. 81	150u"/3. 81u TIN	
-237				. 675/17. 15	15u"/0. 38u MIN (NOTE 16) OVER 50u"/1. 27u Ni	
-238					30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni	
-239					30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni	
-240	2 X 15		1. 400/35. 56	. 675/17. 15	150u"/3. 81u TIN	
-241	2 X 22		2. 100/53. 34	. 105/2. 67	15u"/0. 38u MIN (NOTE 16) OVER 50u"/1. 27u Ni	
-242					30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni	
-243					30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni	
-244				. 105/2. 67	150u"/3. 81u TIN	
-245				. 150/3. 81	15u"/0. 38u MIN (NOTE 16) OVER 50u"/1. 27u Ni	
-246					30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni	
-247					30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni	
-248				. 150/3. 81	150u"/3. 81u TIN	
-249				. 675/17. 15	15u"/0. 38u MIN (NOTE 16) OVER 50u"/1. 27u Ni	
-250					30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni	
-251					30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni	
-252	2 X 22		2. 100/53. 34	. 675/17. 15	150u"/3. 81u TIN	
88880-253	2 X 17	D	1. 600/40. 64	. 105/2. 67	15u"/0. 38u MIN (NOTE 16) OVER 50u"/1. 27u Ni	NOTE 2
88880-254	UNAVAILABLE					
THRU						
88880-279	UNAVAILABLE					
88880-280	2 X 10	D	. 900/22. 86	. 105/2. 67	150u"/3. 81u TIN	NOTE 2
88880-281	UNAVAILABLE					
THRU						
88880-306						

mat'l. code		surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection ⌀ ↖		product family QUICKIE	
ltr ecn nodr date		tolerances unless otherwise specified		linear		INCH/MM		title	
K		angles		XXX-01/XXX-03				HEADER, QUICKIE, SLIM LINE	
		±2°		XXX-005/XXX-013				VERTICAL, 4-WALL	
		dr		M. CLOUSER 7/11/90		scale 1:1		dwg no	
		engr		M. SMYK 7/11/90		FCI		shee 7 of 10 size	
		chr		M. SMYK 8/21/91				88880 A3	
		appd		M. SMYK 8/21/91				type Product Customer Drawing	
sheet index		revision sheet							



Copyright FCI

A

B

C

D

PRODUCT NO. NOTE 8 & 9	SIZE	STYLE	DIM C	DIM J	PIN PLATING	PLASTIC MATERIAL
88880-307	2 X 5	B	. 400/10. 16	. 097/2. 46	30u" /0. 76u MIN (NOTE 16) OVER 50u" /1. 27u Ni	NOTE 2
-308	2 X 5	B	. 400/10. 16			
-309	2 X 7	C	. 600/15. 24			
-310	2 X 8	D	. 700/17. 78			
-311	2 X 10		. 900/22. 86			
-312	2 X 12		1. 100/27. 94			
-313	2 X 13		1. 200/30. 48			
-314	2 X 15		1. 400/35. 56			
-315	2 X 17		1. 600/40. 64			
-316	2 X 20		1. 900/48. 26			
-317	2 X 22		2. 100/53. 34			
-318	2 X 25		2. 400/60. 96			
-319	2 X 30		2. 900/73. 66	. 097/2. 46		
-320	2 X 8		. 700/17. 78	. 105/2. 67		
-321	2 X 25		2. 400/60. 96		30u" /0. 76u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-322	2 X 8		. 700/17. 78		50u" /1. 27u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-323	2 X 17		1. 600/40. 64	. 105/2. 67	50u" /1. 27u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-324	2 X 25		2. 400/60. 96	. 120/3. 05	15u" /0. 38u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-325	2 X 25		2. 400/60. 96	. 150/3. 81	30u" /0. 76u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-326	2 X 10		. 900/22. 86	. 120/3. 05	15u" /0. 38u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-327	2 X 17		1. 600/40. 64	. 120/3. 05	15u" /0. 38u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-328	2 X 25		2. 400/60. 96	. 120/3. 05	15u" /0. 38u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-329	2 X 13		1. 200/30. 48	. 150/3. 81	15u" /0. 38u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-330	2 X 25		2. 400/60. 96		15u" /0. 38u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-331	2 X 30		2. 900/73. 66		15u" /0. 38u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-332	2 X 17		1. 600/40. 64		15u" /0. 38u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-333	2 X 20		1. 900/48. 26	. 150/3. 81	30u" /0. 76u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-334	2 X 10		. 900/22. 86	. 105/2. 67	15u" /0. 38u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-335	2 X 20		1. 900/48. 26	. 105/2. 67	30u" /0. 76u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-336	2 X 22	D	2. 100/53. 34	. 105/2. 67	30u" /0. 76u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-337	2 X 12	D	1. 100/27. 94	. 150/3. 81	15u" /0. 38u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-338	2 X 5	B	. 400/10. 16	. 150/3. 81	15u" /0. 38u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-339	2 X 4	B	. 300/7. 62	. 105/2. 67	15u" /0. 38u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
88880-340	2 X 10	D	. 900/22. 86	. 150/3. 81	30u" /0. 76u MIN (NOTE 16) OVER 50u" /1. 27u Ni	NOTE 2

mat'l. code		surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family QUICKIE	
ltr ecn nodr date		tolerances unless otherwise specified		linear		INCH/MM		title	
K				XXX-01/XXX-03				HEADER, QUICKIE, SLIM LINE	
				XXX-005/XXX-013				VERTICAL, 4-WALL	
				XXX-0020/XXX-0051		scale 1:1		dwg no	
		dr M. CLOUSER 7/11/90						shee 8 of 10 size	
		engr M. SMYK 7/11/90						88880 A3	
		chr M. SMYK 8/21/91						type Product Customer Drawing	
		appd M. SMYK 8/21/91							
sheet index		revision sheet							

A

B

C

D



FCIconnect.com

Copyright FCI

PRODUCT NO.	SIZE	STYLE	DIM C	DIM J	PIN PLATING	PLASTIC MATERIAL
88880-341	2 X 17	D	1.600/40.64	.150/3.81	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	NOTE 2
-342	2 X 10	D	.900/22.86	.150/3.81	15u"/0.38u MIN (NOTE 16) OVER 50u"/1.27u Ni	NOTE 2
-343	2 X 17	D	1.600/40.64	.150/3.81	15u"/0.38u MIN (NOTE 16) OVER 50u"/1.27u Ni	NOTE 2
-344	UNASSIGNED					
-345	2 X 20	D	1.900/48.26	.120/3.05	15u"/0.38u MIN (NOTE 16) OVER 50u"/1.27u Ni	NOTE 2
-346	UNASSIGNED					
-347	UNASSIGNED					
-348	2 X 5	B	.400/10.16	.105/2.67	15u"/0.38u MIN (NOTE 16) OVER 50u"/1.27u Ni	NOTE 2
-349	2 X 7	C	.600/15.24			
-350	2 X 8	D	.700/17.78			
-351	2 X 10		.900/22.86			
-352	2 X 13		1.200/30.48			
-353	2 X 17		1.600/40.64			
-354	2 X 20		1.900/48.26			
-355	2 X 22		2.100/53.34			
-356	2 X 25		2.400/60.96			
-357	2 X 30		2.900/73.66	.105/2.67	15u"/0.38u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-358	2 X 10		.900/22.86	.150/3.81	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-359	2 X 17		1.600/40.64	.150/3.81	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-360	2 X 12	D	1.100/27.94	.295/7.49	15u"/0.38u MIN (NOTE 16) OVER 50u"/1.27u Ni	NOTE 2
-361	UNASSIGNED					
-362	2 X 5	B	.400/10.16	.105/2.67	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	NOTE 2
-363	2 X 8	D	.700/17.78			
-364	2 X 10	D	.900/22.86			
-365	2 X 15	D	1.400/35.56			
-366	2 X 17	D	1.600/40.64	.105/2.67		
-367	2 X 5	B	.400/10.16	.150/3.81		
-368	2 X 17	D	1.600/40.64	.150/3.81		
88880-369	2 X 25	D	2.400/60.96	.150/3.81	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	NOTE 2

mat'l. code				surface ☒ tolerance ☐		projection		product family			
				ISO 1302 ☒ ISO 406 ☐ ISO 1101 ☐				QUICKIE			
l		tr		ec		n		d		r	
K											
				tolerances unless otherwise specified				title			
				angles		linear		INCH/MM		HEADER, QUICKIE, SLIM LINE	
										VERTICAL, 4-WALL	
				±2°				scale 1:1			
				dr		M. CLOUSER		7/11/90		dwg no	
				engr		M. SMYK		7/11/90		sheet 9 of 10	
				chr		M. SMYK		8/21/91		size A3	
				appd		M. SMYK		8/21/91		type Product Customer Drawing	
sheet		revision									
index		sheet									



scale 1:1

dwg no 88880

sheet 9 of 10

A3

type Product Customer Drawing



FCIconnect.com

Copyright FCI

PRODUCT NO.	SIZE	STYLE	DIM C	DIM J	PIN PLATING	PLASTIC MATERIAL	POLARIZED PIN
88880-404	2 X 20	D	1.900/48.26	.120/3.05	15μ/0.38μm MIN (NOTE 16) OVER 50u"/1.27u Ni	NOTE 2	20
↑ -410	2 X 25	↑	2.400/60.96	↑	↑	↑	—
↑ -418	2 X 10	↑	.900/22.86	↑	↑	↑	14
↑ -423	2 X 25	↓	2.400/60.96	↑	↑	↑	25
↑ -426	2 X 17	D	1.600/40.64	↓	↓	↓	3
88880-427	2 X 5	B	.400/10.16	.120/3.05	15μ/0.38μm MIN (NOTE 16) OVER 50u"/1.27u Ni	↓	1
88880-428	2 X 5	B	.400/10.16	.150/3.81	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	NOTE 2	10

mat'l. code			surface	tolerance	projection	product family		
			ISO 1302 ✓	ISO 406 ISO 1101		QUICKIE		
l	tr	ec	n	d		title		
K					INCH/MM	HEADER, QUICKIE, SLIM LINE		
						VERTICAL, 4-WALL		
					scale 1:1	dwg no		
						sheet 10 of 10		
						88880		
						type Product Customer Drawing		
sheet	revision							
index	sheet							