




HONEYWELL PART NUMBER
11SM401-H2
PRODUCT CODE TWY0120

REV	DOCUMENT	CHANGED BY	CHECK
6	0038104	PK 23APR08	ASD



PLASTIC PLUNGER



NOTE -
1 - MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .087 MAX DIA ON .375 ±.002 CENTERS
2 - TERMINALS ARE PLATED FOR SOLDERING
3 - DEAD BREAK CONDITIONS:
A - MAX AMOUNT PERMISSIBLE - - - - - .0002 IN.

RELEASE NO.	SR - 12207
REPLACES	-

CHARACTERISTICS		ELECTRICAL DATA			DESIGN UNITS: INCH TOLERANCES UNLESS NOTED: NO PLACE X ± ONE PLACE .X ± TWO PLACE .XX ± THREE PLACE .XXX ± FOUR PLACE .XXXX ± ANGLES ± THIRD ANGLE PROJECTION 			DRAWN	VK	27 NOV 07		Honeywell						
OPERATING FORCE — — — 31/2 OZ MAX		CONTACT ARRANGEMENT SPDT						CHECK	RJ	27 NOV 07								
RELEASE FORCE— — — — 1 OZ MIN		30 VOLTS DC RATING			0.030 0.015 0.005			THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.				TITLE SWITCH - BASIC						
DIFFERENTIAL TRAVEL— — — .001 MAX			SEA LEVEL	50,000 FT														
OVERTRAVEL — — — — — .005 MIN		INDUCTIVE	3 AMP	2.5 AMP		INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY								SIZE	TYPE	DRAWING NAME		REV
	RESISTIVE	5 AMP	5 AMP		B									I	11SM401-H2		6	
					RASTER								SCALE	-	WEIGHT .006 LB MAX	SHEET 1 OF 1		