



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
E	B		B	ECR-05-013423	13DEC05	JMS	FWK
			C	ECO-11-010168	17MAY2011	TITAN	MARTIN

NOTES:


- 1 PACK IN ACCORDANCE WITH AMP SPEC 107-3275
- 2 100 TRAY PACK IN ACCORDANCE WITH AMP SPEC 107-3275
- 3 Au PLATING
- 4 Ni PLATING
- 5 Sn PLATING

- 6 ELECTRICAL CHARACTERISTICS
FREQUENCY RANGE: DC – 1 GHz
NOMINAL IMPEDANCE: 75 Ohms
INSULATION RESISTANCE: 5000 MOhms Min.
WORKING VOLTAGE: 500 Volts RMS at Sea Level
DIELECTRIC WITHSTAND VOLTAGE: 1500 Volts RMS Max
CONTACT RESISTANCE: 1.50 mOhms Max
CENTRE CONTACT: 1.0 mOhms Max
OUTER CONTACT: 1.5 MAX. @0.3 GHz
VSWR @ xGHz: 0.5 dB MAX. @0.3 GHZ
INSERTION LOSS xdb:
- 7 MECHANICAL CHARATERISTICS
DURABILITY: 500 MATINGS
- 8 ENVIRONMENTAL CHARACTERISTICS
OPERATING TEMPERATURE: -40 to +60 DegC



MOUNTING HOLE

		1	1	BRASS	3	CENTER CONTACT	7
		1	1	ABS		BODY II	6
		1	1	BRASS	5	GROUNDING TAB	5
		1	1	BRASS	4	BODY I	4
		1	1	BRASS	4	WASHER	3
		1	1	BRASS	4	NUT	2
		1	1	STEEL	4	WASHER	1
		6--0	1--0	MATERIAL		DESCRIPTION	ITEM
		6	1				
QUANTITY PER ASSY				PARTS LIST			

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.SANDWELL CHK S.PARLOW APVD F.WHEELER-KING PRODUCT SPEC — APPLICATION SPEC — WEIGHT —	14JUN06 14JUN06 14JUN06 —	 TE Connectivity			
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	NAME BNC INSULATED BULKHEAD JACK FRONT MOUNT 75 OHM —			RESTRICTED TO —		
	0 PLC ± — 1 PLC ± 0.2 2 PLC ± 0.1 3 PLC ± 0.05 4 PLC ± — ANGLES ± 5°						
MATERIAL SEE TABLE	FINISH SEE TABLE	SIZE A3			CAGE CODE 00779	DRAWING NO C-1478048	REV C
CUSTOMER DRAWING					SCALE NTS	SHEET 1 OF 1	REV C