


NOTES:

1. MATERIALS AND FINISH:
BODY: BRASS, GOLD PLATED
CONTACT: BRASS, GOLD PLATED
CAP: BRASS, GOLD PLATED
INSULATOR: PTFE, NATURAL
2. ELECTRICAL:
A. IMPEDANCE: 50 OHM
B. FREQUENCY RANGE: DC - 6 GHZ
C. DIELECTRIC WITHSTANDING VOLTAGE: 500 VRMS. MIN.
3. PHYSICAL:
A. OPERATING TEMPERATURE = -65°C TO +165°C
B. DURABILITY = 500 MATING CYCLES MINIMUM
4. USE ASSEMBLY INSTRUCTIONS 349-50602.
5. SOLDER CENTER AND OUTER CONDUCTOR.



THIRD ANGLE PROJ.

REVISIONS

REV	DESCRIPTION	DATE	ECO	APPR
A	OFFICIAL ENG. RELEASE TO MFG.	06-06-95	40641	GT/RV
B	REDRAWN ON PRO/E, SEE E.C.O. FOR DETAILS	6/5/96	41376	BCG
C	BODY WAS CHANGED	3/23/09	47451	CPM
D	BODY WAS CHANGED	31-Mar-11	48431	SH



CABLE STRIPPING DIMENSIONS



SCALE 6.000

CUSTOMER OUTLINE DRAWING

ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE: <0.5mm ± 0.05mm 0.5 - 6mm ± 0.1mm 6 - 30mm ± 0.2mm 30 - 120mm ± 0.3mm ANGLES ± 1°	MATERIAL	DRAWN T.DENG	DATE 29-Mar-11	TITLE MICROMATE (MALE) RIGHT ANGLE FOR .086 S/R CABLE	Amphenol RF www.amphenolrf.com	
		ENGINEER R. VACCARO	DATE 18-May-95		DRAWING NO. 908-43400	
		APPROVED S.HSIEH	DATE 31-Mar-11		ITEM NO. 908-43400	
		REFERENCE MOTOROLA EAR 964678-0 615X-1320-300 GEN# ASSYM2.MMCX CONFIGURATION LEVEL:	CAD FILE	SCALE: 12.0:1.0	SHEET 2 OF 2	PART NO.908-43400
		FINISH		DWG SIZE B	REV D	