





LOC	DIST	REVISIONS			
CM	0	P	LTR	DESCRIPTION	DATE
		D		REVISED PER 0G3B-0237-05	9/21/05



1. 0.00076 [.000030] MIN GOLD IN LOCALIZED GOLD PLATE AREA AND 0.00254 [.000100] MIN BRIGHT TIN-LEAD IN LOCALIZED TIN-LEAD PLATE AREA OVER 0.0013 [.000050] MIN NICKEL.
2. WIRE RANGE: 0.12 – 0.4MM² (26–22 AWG).
3. INSULATION RANGE: 1.19–1.75[.047–.069] DIA.
4. DIMENSIONS IN BRACKETS ARE IN INCHES.
5. 0.00076 [.000030] MIN GOLD IN LOCALIZED GOLD PLATE AREA AND 0.00254 [.000100] MIN MATTE TIN IN LOCALIZED TIN PLATE AREA OVER 0.0013 [.000050] MIN NICKEL.



SECTION A-A
SCALE 20:1



SECTION B-B
SCALE 20:1

$\triangle 5$	0.25[.010] BRASS	1-794226-0
$\triangle 1$	0.25[.010] BRASS	794226-3
PRE-TIN	0.25[.010] BRASS	794226-1
FINISH	MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. VESTAL 1-15-97	tyco Electronics Tyco Electronics Corporation Harrisburg, PA 17105-3608			
DIMENSIONS: mm [INCHES]		CHK R. SWING 1-15-97				
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD -	NAME		
	0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.15 [.006] 4 PLC ± - ANGLES ± - FINISH		PRODUCT SPEC -	PIN, LOOSE PIECE, MINI UNIVERSAL MATE-N-LOK 2		
	SEE TABLE		APPLICATION SPEC -	SIZE A2	CAGE CODE 00779	DRAWING NO C=794226
MATERIAL SEE TABLE		SEE TABLE	WEIGHT -	RESTRICTED TO -		
CUSTOMER DRAWING				SCALE 10:1	SHEET 1 of 1	REV D