


AUTOMOTIVE SEALS & CAVITY PLUGS



✓ Active

TE CONNECTIVITY (TE)

MQS SINGLE-WIRE SEAL FOR 4MM

AMP | MQS

963142-1

TE Internal Number: 963142-1

EU RoHS Compliant

EU ELV Compliant

Cable Insulation Diameter 2.4 mm [.094 in]

Seal Type Single Wire Seal (SWS)

Cavity Diameter 4 mm [.157 in]

Material Silicone

Resistance to Hydrocarbons POOR

 **PRODUCT DRAWING**
English

 **3D PDF**

DOCUMENTATION

Product Drawings

MQS Tabellenzeichnung Buchsenkontakt TABLE SOCKET CONTACT

PDF

English

Micro Quadlok System Einzeldichtung Kammerdurchmesser 4.0

PDF

English

CAD Files

3D PDF

PDF

3D

Customer View Model

2D_DXF.ZIP

English

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

Product Specifications

Application Specification

Application Specification For MQS Contact System With SINGLE WIRE SEAL

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Seal Type Single Wire Seal (SWS)

Body Features

Material Silicone

Color Black

Dimensions

Cavity Diameter 4 mm [.157 in]

Cable Insulation Diameter 2.4 mm [.094 in]

Usage Conditions

Operating Temperature Range -40 – 130 °C [-40 – 266 °F]

Industry Standards

UL Flammability Rating None

Other

Resistance to Hydrocarbons POOR

Shore A Hardness 50

Lubricant Content Yes

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance

PDF
