

# Customer Information Sheet

DRAWING No.: M22-6023042

SHEET 2 OF 2




IF IN DOUBT - ASK

(C)

NOT TO SCALE

THIRD ANGLE PROJECTION

ALL DIMENSIONS IN mm



## SPECIFICATION:

### MATERIALS:

MOULDING = NYLON 6T, UL94V-0 BLACK

CONTACTS = BRASS

FINISH (OVER NICKEL):

GOLD ON CONTACT AREA, 100% TIN ON TAILS

### ELECTRICAL:

CONTACT RESISTANCE = 30mΩ MAX.

INSULATION RESISTANCE = 5000MΩ MIN.

CURRENT RATING = 1A MAX

VOLTAGE RATING = 250V AC

VOLTAGE PROOF = 800V AC FOR ONE MINUTE

### ENVIRONMENTAL:


TEMPERATURE RANGE = -55° TO +105°C

PACKING:

TUBE

## NOTES:

- ALL TOLERANCES ARE ±0.20 UNLESS OTHERWISE STATED.



## ORDER CODE:

M22-6023042

No. OF CONTACTS PER ROW: 30

FINISH: 42 = SELECTIVE GOLD + 100% TIN

|                |           |          |        |
|----------------|-----------|----------|--------|
| MSP            | 8         | 25.04.17 | 20391  |
| NAME           | ISS.      | DATE     | C/NOTE |
| APPROVED:      | M.PERREN  |          |        |
| CHECKED:       | S.BENNETT |          |        |
| DRAWN:         | D.BECK    |          |        |
| CUSTOMER REF.: |           |          |        |
| ASSEMBLY DRG:  |           |          |        |

# HARWIN

www.harwin.com  
technical@harwin.com

THIS DRAWING AND ANY INFORMATION OR DESCRIPTIVE MATTER SET OUT HEREON ARE CONFIDENTIAL AND COPYRIGHT PROPERTY OF THE HARWIN GROUP AND MUST NOT BE DISCLOSED, LOANED, COPIED OR USED FOR MANUFACTURING, TENDERING OR FOR ANY OTHER PURPOSE WITHOUT THEIR WRITTEN PERMISSION.

## TOLERANCES

X = ±1mm  
X.X = ±0.50mm  
X.XX = ±0.10mm  
X.XXX = ±0.01mm

ANGLES = ±5°

UNLESS STATED

## MATERIAL:

SEE ABOVE

FINISH: SEE ABOVE

S/AREA:

mm<sup>2</sup>

## TITLE:

PCI04 PLUS  
POST HEADER

DRAWING NUMBER:

M22-6023042

SHT

2 OF 2