






PANDUIT PART NO. SEE NOTES	D I M E N S I O N S			RECOMMENDED HOLE DIA. IN. (mm)	RECOMMENDED PANEL SIZE IN. (mm)	WEIGHT LBS./ 100 PCS. (g)
	"A"	"B"	"C"			
THMSP20- ---	0.19 [4.8]	0.47 [11.9]	0.65 [16.5]	0.244 - 0.283 [6.20 - 7.20]	0.024 - 0.160 (0.61 - 4.1)	0.238 (105)
THMSP25- ---	0.26 [6.6]	0.54 [13.7]	0.72 [18.3]		0.024 - 0.230 (0.61 - 5.8)	0.254 (115)
THMSP20F- ---	0.19 [4.8]	0.47 [11.9]	0.65 [16.5]		0.024 - 0.160 (0.61 - 4.1)	0.238 (105)
THMSP25F- ---	0.26 [6.6]	0.54 [13.7]	0.72 [18.3]		0.024 - 0.230 (0.61 - 5.8)	0.254 (115)

NOTES:

- SEE PART NUMBER SUFFIX DESIGNATIONS ON CURRENT PRICE SHEET FOR PACKAGE SIZE, PART COLOR AND PART MATERIAL.
- SUFFIX 'F' AFTER PART SIZE INDICATES ABSENCE OF TAB WHERE SHOWN. (I.E. THMSC60F).
- MATERIAL TABLE

-39	NYLON 6.6	HEAT STABILIZED	NATURAL
-30	NYLON 6.6	HEAT STABILIZED	BLACK
-639	NYLON 6	HEAT STABILIZED	NATURAL
-630	NYLON 6	HEAT STABILIZED	BLACK



DIMENSIONS IN BRACKETS ARE METRIC [mm]

CAD FILENAME/LAYERS

GB0303BB_PB_THMSP_08

PANDUIT

CORP.

TINLEY PARK, ILLINOIS

THMSP, THMSPF
TIE HARNESS MOUNTUNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:(.X) ±0.05 [1.3] (.XXX) ±0.010 [0.25]
(.XX) ±0.02 [0.5] ANGLES ± 5°

UNLESS OTHERWISE SPECIFIED,

ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

8	12-21-06	TMSA		ADDED NOTE 3 MATERIAL TABLE	GB0303BB	8			
7	06/29/01	LGG		UPDATED DIM FOR WEB & ADDED REF.	GB0303BB	7			
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP	Q.C.

DRAWN BY TNT

MAT'L:

SCALE

NONE

DATE 11/24/92

SEE NOTE 3

DRAWING NO.

GB0303BB

DWG
A
SIZE

CHK'D