

LT-Series

Toggle Switches

The LT-Series illuminated toggle switches feature up to a three-color lighting sequence from a single lamp. These lighted toggles contain neoprene bushing seals for dust and moisture protection and provide a simple way to dress-up most any Marine or Transportation industry panel. A variety of circuits and terminations are available.



Carling Technologies®

Innovative Designs. Powerful Solutions.

Innovative Designs. Powerful Solutions.

Carling Technologies, Inc.
60 Johnson Avenue • Plainville, CT 06062-1177
Phone: (860) 793-9281 • Fax: (860) 793-9231
Email: sales@carlingtech.com • www.carlingtech.com

Dielectric Strength

1000V - live to dead metal parts

Electrical Life

50,000 cycles - maintained

25,000 cycles - momentary

Mechanical Life

100,000 cycles

Operating Temperature

32°F to 185°F (0°C to 85°C)

LT-1561 - 1 30 - 012

1
Base Part Number

2 Actuator Style

3 Lighting Sequence

4 Lamp Voltage

**1 BASE PART NUMBER: SERIES/POLES/ILLUMINATION/
CIRCUITRY/RATING/TERMINATION⁵**

10A 250VAC, 15A 125VAC, 3/4 HP 125-250VAC, 15A 15-28VDC

Single Pole	Solder Lug	.250 Tab	QC	.187 Tab	QC	Wire Leads
On-None-Off	LT-1510	LT-1511		LT-1514		LT-1515
On-None-(Off)	LT-1520	LT-1521		LT-1524		LT-1525
(On)-None-Off	LT-1530	LT-1531		LT-1534		LT-1535
On-None-On	LT-1540	LT-1541		LT-1544		LT-1545
On-None-(On)	LT-1550	LT-1551		LT-1554		LT-1555
On-Off-On	LT-1560	LT-1561		LT-1564		LT-1565
On-Off-(On)	LT-1570	LT-1571		LT-1574		LT-1575
(On)-Off-(On)	LT-1580	LT-1581		LT-1584		LT-1585
Double Pole	Solder Lug	.250 Tab	QC	.187 Tab	QC	Wire Leads
On-None-Off	LT-2510	LT-2511		LT-2514		LT-2515
On-None-(Off)	LT-2520	LT-2521		LT-2524		LT-2525
(On)-None-Off	LT-2530	LT-2531		LT-2534		LT-2535
On-None-On	LT-2540	LT-2541		LT-2544		LT-2545
On-None-(On)	LT-2550	LT-2551		LT-2554		LT-2555
On-Off-On	LT-2560	LT-2561		LT-2564		LT-2565
On-Off-(On)	LT-2570	LT-2571		LT-2574		LT-2575
(On)-Off-(On)	LT-2580	LT-2581		LT-2584		LT-2585

2 ACTUATOR STYLE

Paddle¹

1 Clear Paddle
4 Solid Color Paddle

Snapkap Style²



5 Bright Chrome
6 Satin Chrome
7 Black Molded

3 LIGHTING SEQUENCE^{3,4}

	position 1	position 2	position 3
01	red	red	red
02	amber	amber	amber
03	green	green	green
10	red	---	none
11	red	clear	red
12	red	clear	amber
13	red	clear	green
14	red	clear	blue
15	red	clear	clear
20	amber	---	none
21	amber	clear	red
22	amber	clear	amber
23	amber	clear	green
24	amber	clear	blue
25	amber	clear	clear
30	green	---	none
31	green	clear	red
32	green	clear	amber
33	green	clear	green
34	green	clear	blue
35	green	clear	clear
40	blue	---	none
41	blue	clear	red
42	blue	clear	amber
43	blue	clear	green
44	blue	clear	blue
45	blue	clear	clear
50	clear	---	none
51	clear	clear	red
52	clear	clear	amber
53	clear	clear	green
54	clear	clear	blue
55	clear	clear	clear

4 LAMP VOLTAGE⁴

incandescent		neon	
006	6 volt	125N	125 volt neon
012	12 volt	250N	250 volt neon
018	18 volt		
024	24 volt		



*Manufacturer reserves the right to change product specification without prior notice.

REV_SW_LT_0912