

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL INTERNATIONAL RIGHTS RESERVED.






LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AF	50		K1	REDRAWN PER ECR-08-032847	09FEB09	HMR	JR
			K2	REVISED PER ECO-09-020932	08SEP09	KK	AEG

- 1

CRIMP DONE IN APPLICATOR
- 2

GOLD ON AREA MARKED .000015 - .000020 THK. WITH NICKEL OVER ENTIRE PART .000080 THK.
- 3

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



3	SUPERSEDED		OBSOLETE	GOLD/NICKEL	24-20	.043-.073	62358-5	
		REVERSE REELED	1	BRIGHT TIN/LEAD OVER NICKEL	24-20	.043-.073	62358-4	
		1	OBSOLETE				62358-3	
					TIN	24-20	.043-.073	62358-1
					FINISH	WIRE AWG	INSULATION RANGE	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RAGHAVENDRA 09FEB09		 Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: INCHES		CHK JEFF RUTH 09FEB09			
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD DON DECKER 09FEB09		NAME PIN .080 DIAMETER
			PRODUCT SPEC —		
			APPLICATION SPEC —		
			SIZE		
			CAGE CODE		
MATERIAL BRASS		FINISH SEE TABLE		DRAWING NO A2 00779 C=62358	
		WEIGHT —		RESTRICTED TO —	
CUSTOMER DRAWING				SCALE 7:1 SHEET 1 of 1 REV K2	