


REV. W

DO NOT SCALE
FROM THIS PRINT

DIMENSIONS ARE IN INCHES		UNLESS OTHERWISE NOTED	TOLERANCES ARE:	TITLE:	DWG NO:
ONE PLACE DECIMALS $\pm .1$	THREE PLACE DECIMALS $\pm .005$		ANGLES $\pm 2^\circ$	DUAL ROW .050 x .050 STRIP ASSEMBLY	FLE-1XX-XX-XX-DV-X
TWO PLACE DECIMALS $\pm .01$	FOUR PLACE DECIMALS $\pm .0020$				SHEET 1 OF 2



NOTES:

1. MINIMUM PUSHOUT FORCE: .5 lb.
2. COPLANARITY; POS -2 THRU -26: .004
POS -27 THRU -75: .006
3. $\odot$ REPRESENTS A CRITICAL DIMENSION.
4. PACKAGE POSITIONS -05 THRU -75 IN TUBES; LAYER PACKAGE POSITIONS -02 THRU -04.
5. FOR EVERY FINISHED PART, ONE POSITION WILL BE LOST WHEN CUTTING BODY TO LENGTH.
6. BURR ALLOWANCE: .003 [.08] MAX.
7. CUT FLASH TO BE .010 [.25] MAX WITH NO FLASH ALLOWED IN HOLES OR EXTENDING BELOW LEADS.

PROPRIETARY NOTE

THIS DOCUMENT CONTAINS INFORMATION CONFIDENTIAL AND PROPRIETARY TO SAMTEC INC. AND SHALL NOT BE REPRODUCED OR TRANSMITTED TO OTHER DOCUMENTS OR DISCLOSED TO OTHERS OR USED FOR ANY PURPOSE, OTHER THAN THAT FOR WHICH IT WAS OBTAINED WITHOUT THE EXPRESSED WRITTEN CONSENT OF SAMTEC INC.

PLOT SCALE: .175/ DIMSCALE: .200

samtec

520 PARK EAST BLVD. NEW ALBANY, INDIANA 47150
PHONE (812) 944-6733 P.O. BOX 1147
CODE 55322

MADE BY:

D PURVIS 11-05-96

FLE-1XX-XX-XX-DV-X

SHEET 1 OF 2