




Helitrim® Model 56 trimming potentiometers provide:

- Thin, 0.195" width housing.
- One watt power rating at 85°C.
- Voltage adjustability within 0.01%.
- Standard resistance values from 10 to 2 megohms.
- Sealing for protection under environmental stresses.
- Rugged cermet resistance element.
- ± 100 ppm/°C maximum unit tempco.
- 22 Adjustment turns.

SPECIFICATIONS

General

Ambient temperature range, °C	-65 to 150
Resistance element	cermet
Adjustment turns, nominal	22
Sealing	meets immersion test of MIL-R-22097
Tempco	± 100 ppm/°C*
*Guaranteed maximum over the ambient temperature range of -65° to 150°C (100Ω to 2 megΩ)	

Model 56

1-1/4" (31,750 mm) Rectangular 22-Turn Cermet

Electrical

Range of std. resistance values, ohms	10 to 2M
Standard resistance tolerance	50Ω thru 2MΩ, $\pm 10\%$ other values, $\pm 20\%$
Input voltage, maximum	300V DC/RMS but not to exceed power rating.
Slider current, maximum	100 mA or within power rating, whichever is less.
Power rating, watts	1.0 at 85°C, derating to 0 at 150°C
End resistance, maximum	4Ω
Actual electrical travel, turns	22 ± 5
Dielectric strength	900V RMS
Insulation resistance	1,000MΩ
Resolution	essentially infinite
Contact resistance variation	3Ω or 3% of R_T , whichever is greater.

Mechanical

Stops	clutch action, both ends
Starting torque, maximum	5 oz-in. (0,035 N·m)
Weight, nominal	0.1 oz. (2,83 gm)
Terminal strength	2 lb. (0,91 kgm) pull & bend
Mounting screw torque, maximum	2 lb-in. (0,23 N·m)

Standard Resistance Values, Ohms


10	100	1K	10K	100K	1M
20	200	2K	20K	200K	2M
50	500	5K	50K	500K	—

Environmental


(Model 56 trimming potentiometers meet or exceed the following environmental requirements of MIL-R-22097.)

Environment (Para. No.)	Severity
Thermal shock (4.6.8)	-65° to 125°C
Moisture resistance (4.6.10)	10 days at 80-98% RH
Shock (4.6.11)	100 g's
Vibration (4.6.12)	20 g's; 10 to 2,000 Hz
Salt spray (4.6.13)	96 hrs.
Effects of soldering (4.6.14)	3 sec. at 350°C
Life, at 0.75 watt (4.6.15)	1,000 hrs. at 85°C
Low temp. operation (4.6.16)	-55°
High temp. exposure (4.6.17)	250 hrs. at 150°C
Rotational life (4.6.18)	200 cycles
Solderability (4.6.20)	5 sec. at 230°C
Immersion (4.6.21)	85°C water
Dielectric strength (4.6.5.2)	70,000 ft. (21 336m); 350V

MODEL 56P



MODEL 56L



CIRCUIT DIAGRAM

