General Specifications

Electrical Capacity (Resistive Load)

Switching Rating: 100mA @ 5V DC
Nonswitching Rating: 100mA @ 50V DC

Other Ratings

Contact Resistance: 100 milliohms maximum; 30 milliohms maximum for contact point
Insulation Resistance: 1,000 megohms minimum @ 250V DC
Dielectric Strength: 250V AC minimum for 1 minute minimum
Mechanical Life: 10,000 detent operations minimum
Electrical Life: 10,000 detent operations minimum
Notes: A detent operation is one actuator position operation or stepping.
A cycle is one 360° rotation. 10,000 detent operations equal 625 cycles for hexadecimal devices or 1,000 cycles for decimal devices.
Nominal Operating Torque: Metal Shaft: 0.009Nm for decimal devices; 0.011Nm for hexadecimal devices
All other Actuator types: 0.008Nm for decimal devices; 0.01Nm for hexadecimal devices
Contact Timing: Nonshorting

Materials & Finishes

Actuators: Screwdriver and Plastic Shaft - Glass fiber reinforced polyamide (UL94V-0);
Dial - Polyoxymethylene; Metal Shaft - Brass with nickel plating
Bushing : Brass with nickel plating (for Metal Shaft model)
Outer Case: Glass fiber reinforced PBT (for Metal Shaft model)
Housing & Base: Glass fiber reinforced polyamide (UL94V-0)
Movable Contacts: Copper alloy with gold plating
Stationary Contacts: Phosphor bronze with gold plating
Terminals: Phosphor bronze with gold plating
Terminal Cover: Polyamide (Right angle model only)
Bracket: Phospher bronze with tin plating (for Metal Shaft model)

Environmental Data

Operating Temperature Range: –25°C through +85°C (–13°F through +185°F)
Humidity: 90 ~ 95% humidity for 240 hours @ 40°C (104°F)
Vibration: 10 ~ 55Hz with peak-to-peak amplitude of 1.5mm traversing the frequency range & returning in 5 minutes; 3 right angled directions for 2 hours
Shock: 50G (490m/s²) acceleration (tested in 6 right angled directions, with 5 shocks in each direction)

Processing

Soldering: Wave Soldering Recommended. See Profile A in Supplement section.
Manual Soldering: See Profile A in Supplement section.
Note: During soldering process, set the switch to the following position:
FR01FR10P, FR01FR16P, FR01KR10P, FR01KR16P, FR01SR10P, FR01SR16P,
FR01AR10PB, FR01AR16PB, FR01AR10HB, FR01AR16HB: 0 position;
FR01FC10P, FR01KC10P, FR01FC10H, FR01KC10H,
FR01SC10P, FR01AC10PB, FR01AC10HB: 7 position;
FR01FC16P, FR01KC16P, FR01FC16H, FR01KC16H,
FR01SC16P, FR01AC16PB, FR01AC16HB: F position
Cleaning: These devices are not process sealed. Hand clean locally using alcohol based solution.
Custom process sealed version available; contact factory.

Standards & Certifications

Flammability Standards: UL94V-0 rated actuator, housing and base
The FR01 Series rotaries have not been tested for UL recognition or CSA certification.
These switches are designed for use in a low-voltage, low-current circuit.
When used as intended, the results do not produce hazardous energy.

Distinctive Characteristics

Compact dimensions and low profile allow high density mounting and close stacking of PC boards.

Highly visible legends and choice of screwdriver, shaft or dial actuators with arrow position indication provide trouble-free code setting. Knob actuator also available.



Real or complement code setting identified by color-keyed actuator.

Detent mechanism gives crisp, positive action for accurate switch setting.

Crimped terminals ensure secure PC mounting and prevent dislodging during soldering.

Cam activated movable contact and gold contacts assure contact reliability and continuity.

Surface mount model with screwdriver actuation available and shown in the surface mount section.

Contact factory for custom models with .200" (5.08mm) terminal spacing.

Actual Size



TYPICAL SWITCH ORDERING EXAMPLE

FR | 01 | K | R | 16 | P | [ ] — | S

Mounting

01	Through-hole

Actuation

F	Screwdriver
K	Plastic Shaft
S	Dial (for Straight Terminals only)
*A	Metal Shaft (for Optional Knobs)

*Must be used with Bracket

Circuits

R	Real Coded (Orange Actuator)
C	Complement Coded (Yellow Actuator)

Color not applicable to Actuator A

Positions

10	Decimal
16	Hexadecimal

PC Terminals

P	Straight
H	Right Angle

Bracket

No Code	No Bracket
*B	With Bracket

*For Actuator A only

Packaging

S	Stick-Tubes: FR01F, FR01K, FR01S 50 Pieces/Stick FR01A 25 Pieces/Stick

DESCRIPTION FOR TYPICAL ORDERING EXAMPLE

FR01KR16P-S



MOUNTING

01 **Through-hole**

ACTUATION

F **Screwdriver**

Adjusted with a flat tipped screwdriver



Actuators are fully rotational either clockwise or counterclockwise.
Actuator Colors: Orange for real coded devices; Yellow for complement coded devices.

AT4180
Optional Snap-on Knob

Polyamide

Black knob with transparent flange



Install knob before mounting on PCB for right angle type; it should not be removed once mounted. When mounting, align slit in knob with arrowhead on actuator.

ACTUATION

K **Plastic Shaft**

Adjusted by hand or with flat tipped screwdriver



S **Dial**

Adjusted by hand or with flat tipped screwdriver



A **Metal Shaft**

Knob options illustrated below with color choices



Actuators are fully rotational and operate either clockwise or counterclockwise.
Colors for Actuators K and S: Orange for real coded devices; Yellow for complement coded devices

Mounting hardware is available if needed for models with Actuator A:
Hexagon Nut AT513M, Locking Ring AT515M, and Lockwasher AT509; all are shown in the Accessories and Hardware section.

OPTIONAL KNOBS FOR METAL SHAFT

AT433
Plain Black

Material:
Polyacetal

Color:
Black



AT4103 Small
Color Tipped

Polyester Base:
Black

Polyamide Tip Colors:
A, B, C, E, F, G, H



AT4104 Large
Color Tipped

Polyester Base:
Black

Polyamide Tip Colors:
A, B, C, E, F, G, H



Knob Orientation: When installed with shaft flat rotated 180° from bushing flat as shown in "Typical Switch Dimensions," white line on cap points to Actuator Position 0 noted in truth tables below.

Color Codes: **A** Black **B** White **C** Red **E** Yellow **F** Green **G** Blue **H** Gray

TRUTH TABLES (CIRCUITS & POSITIONS)

Terminal No. (Output)	Actuator Position (● = ON)	10 Decimal										16 Hexadecimal															
		0	1	2	3	4	5	6	7	8	9	0	1	2	3	4	5	6	7	8	9	A	B	C	D	E	F
R **Real Coded** Model Numbers: FR01FR, FR01KR, FR01SR, FR01AR	1		●		●		●		●		●		●		●		●		●		●		●		●		●
	2			●	●			●	●					●	●			●	●			●	●			●	●
	4					●	●	●	●							●	●	●	●					●	●	●	●
	8									●	●									●	●	●	●	●	●	●	●
C **Complement Coded** Model Numbers: FR01FC, FR01KC FR01SC, FR01AC	1	●		●		●		●		●		●		●		●		●		●		●		●		●	
	2	●	●			●	●			●	●	●	●			●	●			●	●			●	●		
	4	●	●	●	●					●	●	●	●	●	●					●	●	●	●				
	8	●	●	●	●	●	●	●	●			●	●	●	●	●	●	●	●								

Terminal numbers are actually on the switch.
Above sequence shown for clockwise rotation.

TYPICAL SWITCH DIMENSIONS

P Straight PC • Screwdriver











FR01FC10P Decimal Hexadecimal

H Right Angle PC • Screwdriver











FR01FR10H Decimal Hexadecimal

P Straight PC • Plastic Shaft











FR01KR16P Decimal Hexadecimal

H Right Angle PC • Plastic Shaft













FR01KC16H Decimal Hexadecimal

TYPICAL SWITCH DIMENSIONS

Straight PC • Dial P



Decimal Hexadecimal

FR01SR10P

Straight PC • Metal Shaft P



Shown in Position 0 with shaft flat rotated 180° from bushing flat

FR01AR10PB

Right Angle PC • Metal Shaft H



Shown in Position 0 with shaft flat rotated 180° from bushing flat

FR01AC16HB

PACKAGING

S

Stick-Tube

FR01F, FR01K & FR01S
Each stick-tube contains 50 switches.
Switches must be ordered in 50-piece increments.

FR01A
Each stick-tube contains 25 switches.
Switches must be ordered in 25-piece increments.

Note: Transport and storage temperatures should not exceed 50°C (122°F). Store stick tubes on flat surface.

FR01F with Screwdriver Actuation & Straight PC



FR01K with Plastic Shaft & Right Angle PC



FR01S with Dial Actuation & Straight PC



FR01A with Metal Shaft & Straight PC



FR01A with Metal Shaft & Right Angle PC