



THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO CW INDUSTRIES INCORPORATED AND ITS AFFILIATES. IT MAY NOT BE DISCLOSED TO ANYONE, OTHER THAN CW INDUSTRIES PERSONNEL, WITHOUT WRITTEN AUTHORIZATION FROM CW INDUSTRIES INCORPORATED, SOUTHAMPTON, PENNSYLVANIA USA.

Rating		20A 12VDC 10A 24VDC		Mounting Hole		Circuit Diagram
Configured For		12VDC 14V				
Contact Resistance		50m ohm Max.				
Insulation Resistance		DC 500V 100M ohm Min.				
Dielectric Strength		AC 1500V 1 minute				
Operation Temperature		-20°~85°				
Switch Function		3P SPST ON-OFF Lamp Dependent				
Lamp Type		Bulb 12VDC 14V				

Thickness(mm)	X(mm)	Y(mm)
0.75~1.25	21.2+0.1	36.6 ^{+0.2} ₋₀
1.25~2.0		36.8 ^{+0.2} ₋₀
2.0~3.0		37.0 ^{+0.2} ₋₀







*** MATERIAL:**

Frame: Nylon#66, Black

Actuator: Nylon#66 with 33%GF, Black

Lens: PC, Red

Water proof and dust proof to fit IP-56



RoHS Compliant

2	Added Configured for to rating, Dependent to function & Lamp Type. 1/23/12.
1	Removed AC Rating marks and added DC Rating marks.8/23/10

CW INDUSTRIES
Southampton, Pa. 18966
Tel 215.355.7080/www.cwind.com

Date Drawn: 5/27/10

Rev. 2

Unit: mm

Checked By: *G. Guld*

Title: **ROCKER SWITCH**

CW P/N: **GRB260A401BBRN1**