






PRODUCT NUMBER NOTE 6	AWG RANGE	SPRING MATERIAL	SPRING PLATING	TERMINAL MATERIAL	TERMINAL PLATING
87027-001	22-26	.13/.005 THK BeCu HEAT TREATED	TIN	.25/.010 THK BRASS 1/4 HARD BRASS	Cu UNDERPLATE REFLOWED 60/40 TIN-LEAD OVERPLATE
87027-001LF	22-26	.13/.005 THK BeCu HEAT TREATED	TIN	.25/.010 THK BRASS 1/4 HARD BRASS	HOT DIPPED TIN

NOTE 7



NOTES:

- PART TO MATE WITH .025 ±.002/.64 ±.05 SQUARE PIN.
- APPLICABLE SPECIFICATIONS:
 - BUS-12-067 PRODUCT SPECIFICATION.
 - TA-75 CRIMP METHODS FOR USE IN MINI LATCH HOUSING.
 - TA-146 FOR DISCRETE TERMINAL USE.
- PART TO BE LUBRICATED TO FACILITATE CRIMPING.
- MAX BURR ANY EDGE .0032/.081.
- MEASURED OVER .280/7.11 REF LENGTH.
- PART NUMBERS WITH AN LF SUFFIX MEET EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
- THIS PRODUCT HAS 100% TIN PLATING IN THE INTERFACE AND HAS NOT BEEN TESTED FOR WHISKER GROWTH IN ALL INTERCONNECT ENVIRONMENTS.

mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY		A FCI www.fciconnect.com	
ltr	ecn no	dr	date	linear	.XX ±.01/.X±.3	projection		title	
C	V61318	EPK	9/25/96		.XXX ±.005/.XX±.13			MINI PVT™ RECEPT. CTW	
D	V05-0472	HTB	5/16/05		.XXX ±.0020/.XXX±.051			SHORT WIRE BARREL w/INSUL. BARREL	
E	V05-0530	HTB	5/31/05	angles	0° ±2°			product family PV TERMINAL	code
				dr	R. SEIPLE 12/15/88	INCH/MM		size	213
				enr	H. SUNDY 6/29/89			dwg no	sheet
				chr	H. SUNDY 12/15/88	scale		A	87027
				appd	H. SUNDY 6/29/98	3:1			1 of 1
sheet index	revision	E							
	sheet	1							

cage code
22526

ACAD

PDM: Rev:E

STATUS:Released

Printed: Mar 07, 2006