




Anwendung / Application



8S Seriell RS-232 Erweiterungs-Metall-Box für EX-47000 / EX-47005

Beschreibung

Das EX-47020 Erweiterungs-I/O-Modul stellt acht Serielle RS-232 High Performance UART 16C950 Ausgänge zur Verfügung. Er ist entwickelt worden um acht weitere Serielle Ausgänge an der EX-47000 oder EX-47005 zu erweitern. Mit dem Modul wird eine Wandbefestigung und auch ein Din-Rail Kit mitgeliefert. Es benötigt kein zusätzliches Netzteil mehr.

Merkmale

- Schnittstelle: RS-232 V.24 mit FIFO 16C950 und 128Byte Buffer
- I/O Adressen und Interrupt wird vom System BIOS vergeben mit Interrupt Sharing
- Daten Bits: 5, 6, 7, 8, 9 / Stop Bits: 1, 1.5, 2 / Parity: none, even, odd, space, mark
- Signale: TxD, RxD, RTS, CTS, DTR, DSR, DCD, GND
- TXD und RXD LED Anzeige für jeden Port
- Bietet DC Strom über den 9 Pin Seriellen Ausgang
- Metall Box mit Wandbefestigung oder Din-Rail Kit für einen 19" Schrank
- Erweitert die EX-47000 oder EX-47005 mit 8 weiteren Seriellen RS-232 Ports

Spezifikationen

- | | |
|-------------------------------|---|
| • Chip-Set: | Oxford OXPCle958 |
| • Datentransfer-Rate: | 50 Baud bis 921.6KBaud |
| • Anschlüsse: | 8 x 9 Pin D-SUB Seriell Stecker
1 x Verschraubbarer Netzteil-Anschluss |
| • Hardwaresysteme: | EX-47000 oder EX-47005 |
| • Treiber: | 2000/XP(32 & 64bit)/Vista(32 & 64bit)/CE(4.2 & 5.0)
Server(2003 & 2008)/Linux(2.4.x & 2.6.x) |
| • Betriebstemperatur : | 0° bis 55° Celsius |
| • Lagertemperatur: | -40° bis 75° Celsius |
| • Luftfeuchtigkeit: | 5% bis 95% |
| • Abmessung: | 171 x 93 x 38 mm |
| • Gewicht: | 1000g |
| • Lieferumfang: | EX-47020, Wandbefestigung, Din-Rail-Kit, Handbuch |



8S Serial RS-232 Expansion-Metal box for EX-47000 / EX-47005

Description

The EX-47020 Expansion I/O module provides 8 high performance 16C950-type UART compatible RS-232 serial ports. It is designed for EX-47000 or EX-47005 to provide eight additional instant COM ports. We provides Wall Mounting and Din-Rail Mounting Kit.

Feature

- Interface: RS-232 V.24 with FIFO 16C950 and 128Byte Buffer
- I/O addresses and Interrupt are set from the System BIOS with Interrupt Sharing
- Data Bits: 5, 6, 7, 8, 9 / Stop Bits: 1, 1.5, 2 / Parity: none, even, odd, space, mark
- Signal: TxD, RxD, RTS, CTS, DTR, DSR, DCD, GND
- TXD and RXD Activity LED Indicators for each Port
- Provides DC Power over Serial DB9 Connectors
- Metal Module Box with Wall Mounting and Din-Rail Mounting Kit
- Expand the EX-47000 or EX-47005 with other 8 Serial RS-232 ports

Specification

- | | |
|----------------------------------|---|
| • Chip-Set: | Oxford OXPCle958 |
| • Data transfer rate: | 50 Baud up to 921.6KBaud |
| • Connectors: | 8 x 9 pin D-SUB serial male
1 x Power Supply connector with Screw Lock |
| • Hardware system: | EX-47000 or EX-47005 |
| • Driver: | 2000/XP(32 & 64bit)/Vista(32 & 64bit)/CE(4.2 & 5.0)
Server(2003 & 2008)/Linux(2.4.x & 2.6.x) |
| • Operating Temperature : | 32° up to 131° Fahrenheit |
| • Storage Temperature: | -40° up to 167° Fahrenheit |
| • Humidity: | 5% to 95% |
| • Size: | 171 x 93 x 38 mm |
| • Weight: | 1000g |
| • Packaging contents: | EX-47020, Wall Mounting and Din-Rail Kit, Manual |

Operating System (OS)

Geprüft / Approved

Verpackung / Packaging

