



Specification Status: RELEASED

Max Electrical Rating at 20°C

Operating Voltage: 250V_{DC}

Interrupt Current: 3A_{RMS}

Fault Voltage: 600V_{RMS}



Lead Material: Tin plated brass

Configuration: Two PPTC devices per
TSM600 part

Case Material: Nylon Resin (UL94 V-0)
1000V dielectric rating

Marking:

 Raychem Logo
 TSM600 — Part Identification
 — Lot Identification

Terminal Description:

T1 = Tip In T4 = Tip Out

R2 = Ring In R3 = Ring Out

**Not to be used for new designs.
For new designs please use TSM600-250F**




TABLE I. DIMENSIONS:

	A MIN	A MAX	B MIN	B MAX	C MIN	C MAX	D MIN	D MAX	E MIN	E MAX	F MIN	F MAX	G MIN	G MAX
mm:	17.0	17.6	11.2	11.7	10.4	11.2	4.8	5.2	2.5	2.8	0.6	1.0	2.2	3.1
in:	(0.671)	(0.691)	(0.440)	(0.460)	(0.410)	(0.440)	(0.187)	(0.203)	(0.099)	(0.111)	(0.022)	(0.038)	(0.087)	(0.122)

TABLE II. PERFORMANCE RATINGS @ 20°C (unless otherwise noted):

IHOLD (A)		RESISTANCE (Ω)** @ 20°C			TIME TO TRIP @ 3 A (Seconds)		OPERATING TEMPERATURE (°C)		Tripped state Power Dissipation @ 250V (Watts) TYPICAL	
20°C	60°C	R MIN	R TYP	R ₁ MAX*	TYP	MAX	MIN	MAX		
0.250	0.140	1.0	3.5	7.0	0.8	6	-40	85	2	

* Maximum device resistance, measured 1-hour post reflow or post trip.

** Resistance per PPTC device.

Additional Ratings @ 20°C

Resistance Matched:

0.5 Ohm measured 24 hours after
reflow installation

Storage Temperature: -40° to 85° C

Line Balance:

0.5 Ohm, 59 dB @ 4 kHz minimum***

Storage Humidity: Per IPC/JEDEC J-STD-020A Level 2a

***Tested in accordance with IEEE 455 with a device having a series longitudinal balance value of at least 60dB

Agency Recognition:

UL, CSA

Reference Documents:

PS300

Precedence:

This specification takes precedence over documents referenced herein.

Effectivity:

Reference documents shall be the issue in effect on the date of invitation for bid.