

SN54LV245A, SN74LV245A OCTAL BUS TRANSCEIVERS WITH 3-STATE OUTPUTS

SCLS382C – SEPTEMBER 1997 – REVISED JUNE 1998

- **EPIC™** (Enhanced-Performance Implanted CMOS) Process
- Typical V_{OLP} (Output Ground Bounce) < 0.8 V at V_{CC} , $T_A = 25^\circ\text{C}$
- Typical V_{OHV} (Output V_{OH} Undershoot) > 2 V at V_{CC} , $T_A = 25^\circ\text{C}$
- Latch-Up Performance Exceeds 250 mA Per JESD 17
- ESD Protection Exceeds 2000 V Per MIL-STD-883, Method 3015; Exceeds 200 V Using Machine Model ($C = 200$ pF, $R = 0$)
- Package Options Include Plastic Small-Outline (DW, NS), Shrink Small-Outline (DB), Thin Very Small-Outline (DGV), and Thin Shrink Small-Outline (PW) Packages, Ceramic Flat (W) Packages, Chip Carriers (FK), and DIPs (J)

description


These octal bus transceivers are designed for 2-V to 5.5-V V_{CC} operation.

The 'LV245A devices are designed for asynchronous communication between data buses. The device transmits data from the A bus to the B bus or from the B bus to the A bus, depending on the logic level at the direction-control (DIR) input. The output-enable ($\overline{OE}$) input can be used to disable the device so the buses are effectively isolated.


To ensure the high-impedance state during power up or power down, $\overline{OE}$ should be tied to V_{CC} through a pullup resistor; the minimum value of the resistor is determined by the current-sinking capability of the driver.

The SN54LV245A is characterized for operation over the full military temperature range of -55°C to 125°C . The SN74LV245A is characterized for operation from -40°C to 85°C .

SN54LV245A . . . J OR W PACKAGE
SN74LV245A . . . DB, DGV, DW, NS, OR PW PACKAGE
(TOP VIEW)



SN54LV245A . . . FK PACKAGE
(TOP VIEW)



FUNCTION TABLE

INPUTS		OPERATION
$\overline{OE}$	DIR	
L	L	B data to A bus
L	H	A data to B bus
H	X	Isolation



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

EPIC is a trademark of Texas Instruments Incorporated.

UNLESS OTHERWISE NOTED this document contains PRODUCTION DATA information current as of publication date. Products conform to specifications per the terms of Texas Instruments standard warranty. Production processing does not necessarily include testing of all parameters.


**TEXAS
INSTRUMENTS**

POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

Copyright © 1998, Texas Instruments Incorporated


SCLS382C – SEPTEMBER 1997 – REVISED JUNE 1998

95



[†] This symbol is in accordance with ANSI/IEEE Std 91-1984 and IEC Publication 617-12.

“...and the



SCLS382C – SEPTEMBER 1997 – REVISED JUNE 1998

Supply voltage range, V_{CC}		-0.5 V to 7 V
Input voltage range, V_I : Except I/O ports (see Note 1)		-0.5 V to 7 V
I/O ports (see Notes 1 and 2)		-0.5 V to $V_{CC} + 0.5$ V
Output voltage range applied in the high or low state, V_O (see Notes 1 and 2)		-0.5 V to $V_{CC} + 0.5$ V
Output voltage range applied in high-impedance or power-off state, V_O (see Note 1)		-0.5 V to 7 V
Input clamp current, I_{IK} ($V_I < 0$)		-20 mA
Output clamp current, I_{OK} ($V_O < 0$ or $V_O > V_{CC}$)		± 50 mA
Continuous output current, I_O ($V_O = 0$ to V_{CC})		± 35 mA
Continuous current through V_{CC} or GND		± 70 mA
Package thermal impedance, θ_{JA} (see Note 3): DB package		115°C/W
DGV package		146°C/W
DW package		97°C/W
NS package		100°C/W
PW package		128°C/W
Storage temperature range, T_{sta}		-65°C to 150°C

NOTES:

1. The input and output voltage ratings may be exceeded if the input and output current ratings are observed.
2. This value is limited to 7 V maximum.
3. The package thermal impedance is calculated in accordance with JEDEC 51.

SN54LV245A, SN74LV245A

OCTAL BUS TRANSCEIVERS

WITH 3-STATE OUTPUTS

SCLS382C – SEPTEMBER 1997 – REVISED JUNE 1998

recommended operating conditions (see Note 4)

			SN54LV245A		SN74LV245A		UNIT
			MIN	MAX	MIN	MAX	
V _{CC}	Supply voltage		2	5.5	2	5.5	V
V _{IH}	High-level input voltage	V _{CC} = 2 V	1.5		1.5		V
		V _{CC} = 2.3 V to 2.7 V	V _{CC} × 0.7		V _{CC} × 0.7		
		V _{CC} = 3 V to 3.6 V	V _{CC} × 0.7		V _{CC} × 0.7		
		V _{CC} = 4.5 V to 5.5 V	V _{CC} × 0.7		V _{CC} × 0.7		
V _{IL}	Low-level input voltage	V _{CC} = 2 V	0.5		0.5		V
		V _{CC} = 2.3 V to 2.7 V	V _{CC} × 0.3		V _{CC} × 0.3		
		V _{CC} = 3 V to 3.6 V	V _{CC} × 0.3		V _{CC} × 0.3		
		V _{CC} = 4.5 V to 5.5 V	V _{CC} × 0.3		V _{CC} × 0.3		
V _I	Input voltage		0	5.5	0	5.5	V
V _O	Output voltage	High or low state	0	V _{CC}	0	V _{CC}	V
		3-state	0	5.5	0	5.5	
I _{OH}	High-level output current	V _{CC} = 2 V	−50		−50		μA
		V _{CC} = 2.3 V to 2.7 V	−2		−2		mA
		V _{CC} = 3 V to 3.6 V	−8		−8		
		V _{CC} = 4.5 V to 5.5 V	−16		−16		
I _{OL}	Low-level output current	V _{CC} = 2 V	50		50		μA
		V _{CC} = 2.3 V to 2.7 V	2		2		mA
		V _{CC} = 3 V to 3.6 V	8		8		
		V _{CC} = 4.5 V to 5.5 V	16		16		
Δt/Δv	Input transition rise or fall rate	V _{CC} = 2.3 V to 2.7 V	0	200	0	200	ns/V
		V _{CC} = 3 V to 3.6 V	0	100	0	100	
		V _{CC} = 4.5 V to 5.5 V	0	20	0	20	
T _A	Operating free-air temperature		−55	125	−40	85	°C

NOTE 4: All unused inputs of the device must be held at V_{CC} or GND to ensure proper device operation. Refer to the TI application report, *Implications of Slow or Floating CMOS Inputs*, literature number SCBA004.

SN54LV245A, SN74LV245A OCTAL BUS TRANSCEIVERS WITH 3-STATE OUTPUTS

SCLS382C – SEPTEMBER 1997 – REVISED JUNE 1998

electrical characteristics over recommended operating free-air temperature range (unless otherwise noted)

PARAMETER		TEST CONDITIONS	V _{CC}	SN54LV245A			SN74LV245A			UNIT
				MIN	TYP	MAX	MIN	TYP	MAX	
V _{OH}		I _{OH} = −50 μA	2 V to 5.5 V	V _{CC} −0.1			V _{CC} −0.1			V
		I _{OH} = −2 mA	2.3 V	2			2			
		I _{OH} = −8 mA	3 V	2.48			2.48			
		I _{OH} = −16 mA	4.5 V	3.8			3.8			
V _{OL}		I _{OL} = 50 μA	2 V to 5.5 V	0.1			0.1			V
		I _{OL} = 2 mA	2.3 V	0.4			0.4			
		I _{OL} = 8 mA	3 V	0.44			0.44			
		I _{OL} = 16 mA	4.5 V	0.55			0.55			
I _I		V _I = V _{CC} or GND	5.5 V	±1			±1			μA
I _{OZ}		V _O = V _{CC} or GND	5.5 V	±5			±5			μA
I _{CC}		V _I = V _{CC} or GND, I _O = 0	5.5 V	20			20			μA
I _{off}		V _I or V _O = 0 to 5.5 V	0 V	5			5			μA
C _i	Control inputs	V _I = V _{CC} or GND	3.3 V	2.4			2.4			pF
			5 V	2.4			2.4			
C _{io}	A or B port	V _O = V _{CC} or GND	3.3 V	5.4			5.4			pF
			5 V	5.4			5.4			

switching characteristics over recommended operating free-air temperature range,
V_{CC} = 2.5 V ± 0.2 V (unless otherwise noted) (see Figure 1)

PARAMETER	FROM (INPUT)	TO (OUTPUT)	LOAD CAPACITANCE	T _A = 25°C			SN54LV245A		SN74LV245A		UNIT
				MIN	TYP	MAX	MIN	MAX	MIN	MAX	
t _{pd} *	A or B	B or A	C _L = 15 pF	8.3	13		1	15	1	15	ns
t _{en} *	$\overline{\text{OE}}$	A or B		11.8	19.9		1	22	1	22	
t _{dis} *	$\overline{\text{OE}}$	A or B		11.8	18.1		1	20	1	20	
t _{pd}	A or B	B or A	C _L = 50 pF	11.2	15.9		1	18	1	18	ns
t _{en}	$\overline{\text{OE}}$	A or B		14.1	22.7		1	26	1	26	
t _{dis}	$\overline{\text{OE}}$	A or B		17.6	23.1		1	25	1	25	
t _{sk(o)} †				2						2	

* On products compliant to MIL-PRF-38535, this parameter is not production tested.

† Skew between any two outputs of the same package switching in the same direction

PRODUCT PREVIEW information concerns products in the formative or design phase of development. Characteristic data and other specifications are design goals. Texas Instruments reserves the right to change or discontinue these products without notice.



POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

SN54LV245A, SN74LV245A

OCTAL BUS TRANSCEIVERS

WITH 3-STATE OUTPUTS

SCLS382C – SEPTEMBER 1997 – REVISED JUNE 1998

switching characteristics over recommended operating free-air temperature range,
 $V_{CC} = 3.3 \text{ V} \pm 0.3 \text{ V}$ (unless otherwise noted) (see Figure 1)

PARAMETER	FROM (INPUT)	TO (OUTPUT)	LOAD CAPACITANCE	$T_A = 25^\circ\text{C}$			SN54LV245A		SN74LV245A		UNIT
				MIN	TYP	MAX	MIN	MAX	MIN	MAX	
t_{pd}^*	A or B	B or A	$C_L = 15 \text{ pF}$	5.9	8.4		1	10	1	10	ns
t_{en}^*	$\overline{OE}$	A or B		8.2	13.2		1	15.5	1	15.5	
t_{dis}^*	$\overline{OE}$	A or B		9.6	16.5		1	19.5	1	19.5	
t_{pd}	A or B	B or A	$C_L = 50 \text{ pF}$	7.9	11.9		1	13.5	1	13.5	ns
t_{en}	$\overline{OE}$	A or B		9.9	16.7		1	19	1	19	
t_{dis}	$\overline{OE}$	A or B		13.9	19.8		1	22	1	22	
$t_{sk(o)}^\dagger$					1.5					1.5	

* On products compliant to MIL-PRF-38535, this parameter is not production tested.

† Skew between any two outputs of the same package switching in the same direction

switching characteristics over recommended operating free-air temperature range,
 $V_{CC} = 5 \text{ V} \pm 0.5 \text{ V}$ (unless otherwise noted) (see Figure 1)

PARAMETER	FROM (INPUT)	TO (OUTPUT)	LOAD CAPACITANCE	$T_A = 25^\circ\text{C}$			SN54LV245A		SN74LV245A		UNIT
				MIN	TYP	MAX	MIN	MAX	MIN	MAX	
t_{pd}^*	A or B	B or A	$C_L = 15 \text{ pF}$	4.3	5.5		1	6.5	1	6.5	ns
t_{en}^*	$\overline{OE}$	A or B		5.7	8.5		1	10.6	1	10	
t_{dis}^*	$\overline{OE}$	A or B		7.8	12.8		1	14.7	1	14.2	
t_{pd}	A or B	B or A	$C_L = 50 \text{ pF}$	5.6	7.5		1	8.5	1	8.5	ns
t_{en}	$\overline{OE}$	A or B		7	10.6		1	12	1	12	
t_{dis}	$\overline{OE}$	A or B		10.9	14.7		1	16	1	16	
$t_{sk(o)}^\dagger$					1					1	

* On products compliant to MIL-PRF-38535, this parameter is not production tested.

† Skew between any two outputs of the same package switching in the same direction

noise characteristics, $V_{CC} = 3.3 \text{ V}$, $C_L = 50 \text{ pF}$, $T_A = 25^\circ\text{C}$ (see Note 5)

PARAMETER		SN74LV245A			UNIT
		MIN	TYP	MAX	
$V_{OL(P)}$	Quiet output, maximum dynamic V_{OL}		0.45		V
$V_{OL(V)}$	Quiet output, minimum dynamic V_{OL}		-0.45		V
$V_{OH(V)}$	Quiet output, minimum dynamic V_{OH}		2.94		V
$V_{IH(D)}$	High-level dynamic input voltage		2.31		V
$V_{IL(D)}$	Low-level dynamic input voltage			0.99	V

NOTE 5: Characteristics are for surface-mount packages only.

operating characteristics, $T_A = 25^\circ\text{C}$


PARAMETER		TEST CONDITIONS		V_{CC}	TYP	UNIT
C_{pd}	Power dissipation capacitance	Outputs enabled	$C_L = 50 \text{ pF}$, $f = 10 \text{ MHz}$	3.3 V	20	pF
				5 V	25	

PRODUCT PREVIEW information concerns products in the formative or design phase of development. Characteristic data and other specifications are design goals. Texas Instruments reserves the right to change or discontinue these products without notice.



POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

PARAMETER MEASUREMENT INFORMATION



- NOTES: A. C_L includes probe and jig capacitance.
- B. Waveform 1 is for an output with internal conditions such that the output is low except when disabled by the output control. Waveform 2 is for an output with internal conditions such that the output is high except when disabled by the output control.
- C. All input pulses are supplied by generators having the following characteristics: $PRR \leq 1\text{ MHz}$, $Z_O = 50\ \Omega$, $t_r \leq 3\text{ ns}$, $t_f \leq 3\text{ ns}$.
- D. The outputs are measured one at a time with one input transition per measurement.
- E. t_{PLZ} and t_{PHZ} are the same as t_{dis} .
- F. t_{pZL} and t_{pZH} are the same as t_{en} .
- G. t_{pHL} and t_{pLH} are the same as t_{pd} .

Figure 1. Load Circuit and Voltage Waveforms

IMPORTANT NOTICE

Texas Instruments and its subsidiaries (TI) reserve the right to make changes to their products or to discontinue any product or service without notice, and advise customers to obtain the latest version of relevant information to verify, before placing orders, that information being relied on is current and complete. All products are sold subject to the terms and conditions of sale supplied at the time of order acknowledgement, including those pertaining to warranty, patent infringement, and limitation of liability.

TI warrants performance of its semiconductor products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are utilized to the extent TI deems necessary to support this warranty. Specific testing of all parameters of each device is not necessarily performed, except those mandated by government requirements.

CERTAIN APPLICATIONS USING SEMICONDUCTOR PRODUCTS MAY INVOLVE POTENTIAL RISKS OF DEATH, PERSONAL INJURY, OR SEVERE PROPERTY OR ENVIRONMENTAL DAMAGE ("CRITICAL APPLICATIONS"). TI SEMICONDUCTOR PRODUCTS ARE NOT DESIGNED, AUTHORIZED, OR WARRANTED TO BE SUITABLE FOR USE IN LIFE-SUPPORT DEVICES OR SYSTEMS OR OTHER CRITICAL APPLICATIONS. INCLUSION OF TI PRODUCTS IN SUCH APPLICATIONS IS UNDERSTOOD TO BE FULLY AT THE CUSTOMER'S RISK.

In order to minimize risks associated with the customer's applications, adequate design and operating safeguards must be provided by the customer to minimize inherent or procedural hazards.

TI assumes no liability for applications assistance or customer product design. TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right of TI covering or relating to any combination, machine, or process in which such semiconductor products or services might be or are used. TI's publication of information regarding any third party's products or services does not constitute TI's approval, warranty or endorsement thereof.