



Full metal top and side entry hoods
with different screw options

Identification	No. of contacts	Part No.	Drawing	Dimensions in mm																														
40° side entry hood with internal grounding block	9 15 25	61 03 001 . 013 61 03 001 . 014 61 03 001 . 015		internal grounding block <table border="1"> <tr> <th>No. of contacts</th> <th>A</th> <th>B</th> <th>C</th> <th>D</th> </tr> <tr> <td>9</td> <td>31.0</td> <td>25.0</td> <td>35.0</td> <td>15.0</td> </tr> <tr> <td>15</td> <td>39.3</td> <td>33.3</td> <td>35.0</td> <td>15.0</td> </tr> <tr> <td>25</td> <td>53.0</td> <td>47.0</td> <td>35.0</td> <td>15.0</td> </tr> </table>	No. of contacts	A	B	C	D	9	31.0	25.0	35.0	15.0	15	39.3	33.3	35.0	15.0	25	53.0	47.0	35.0	15.0										
No. of contacts	A	B	C	D																														
9	31.0	25.0	35.0	15.0																														
15	39.3	33.3	35.0	15.0																														
25	53.0	47.0	35.0	15.0																														
without internal grounding block	9	61 03 001 . 013 010																																
Top/side entry hood with internal grounding block	9 15 25 37 50	61 03 001 . 010 61 03 001 . 016 61 03 001 . 017 ¹⁾ 61 03 001 . 018 ¹⁾ 61 03 001 . 019 ¹⁾		 <table border="1"> <tr> <th>No. of contacts</th> <th>A</th> <th>B</th> <th>C</th> <th>D</th> </tr> <tr> <td>9</td> <td>31.0</td> <td>25.0</td> <td>38.0</td> <td>15.0</td> </tr> <tr> <td>15</td> <td>39.5</td> <td>33.3</td> <td>35.0</td> <td>15.0</td> </tr> <tr> <td>25</td> <td>53.0</td> <td>47.0</td> <td>43.0</td> <td>15.0</td> </tr> <tr> <td>37</td> <td>69.5</td> <td>63.5</td> <td>43.0</td> <td>15.0</td> </tr> <tr> <td>50</td> <td>67.2</td> <td>61.6</td> <td>43.0</td> <td>17.8</td> </tr> </table>	No. of contacts	A	B	C	D	9	31.0	25.0	38.0	15.0	15	39.5	33.3	35.0	15.0	25	53.0	47.0	43.0	15.0	37	69.5	63.5	43.0	15.0	50	67.2	61.6	43.0	17.8
No. of contacts	A	B	C	D																														
9	31.0	25.0	38.0	15.0																														
15	39.5	33.3	35.0	15.0																														
25	53.0	47.0	43.0	15.0																														
37	69.5	63.5	43.0	15.0																														
50	67.2	61.6	43.0	17.8																														
without internal grounding block	9	61 03 001 . 010 010																																
Please insert digit for screw option																																		
Knurled screw, thread 4-40 UNC ▶ 0																																		
Hexagonal screw, thread M3 ▶ 1																																		
Hexagonal screw, thread 4-40 UNC ▶ 2																																		
Knurled screw, thread M3 ▶ 3																																		
Top entry hood for InduCom 9																																		
Hexagonal screw, thread 4-40 UNC	9	66 67 009 0346																																
Hexagonal screw, thread M3	9	66 67 009 0347																																

¹⁾ Part No. contains two blanking pieces

Operating temperature for all hoods on this page: -20 °C ... +90 °C