

ISSUE 12; July 2016

### Description

- Standard 7 x 5mm crystal oscillator
- Ceramic package with a seam sealed metal lid, hermetically sealed
- Stock parts are available
- Fast Make capability: CFPP-73 series programmable oscillators are the nearest equivalent fast make model



### Frequency Parameters

- Frequency: 500.0kHz to 157.0MHz
- Frequency Stability:  $\pm 20.00\text{ppm}$  to  $\pm 100.00\text{ppm}$
- Ageing:  $\pm 3\text{ppm}$  per year max

### Electrical Parameters

- Supply Voltage:  $3.3\text{V} \pm 10\%$

### Operating Temperature Ranges

- 0 to  $70^{\circ}\text{C}$
- $-40$  to  $85^{\circ}\text{C}$

### Output Details

- Output Compatibility: HCMOS

| Drive Capability    |          |
|---------------------|----------|
| 0.5MHz to 50.0MHz   | 50pF max |
| 50.0MHz to 80.0MHz  | 30pF max |
| 80.0MHz to 157.0MHz | 15pF max |

### Output Control

- Logic '1' ( $>70\%$  VS) to pad 1 enables oscillator output
- Logic '0' ( $<30\%$  VS) to pad 1 disables oscillator output; the oscillator output goes to the high impedance state
- No connection to pad 1 enables oscillator output
- Standby Current:  $10\mu\text{A}$  max

### Noise Parameters

- Phase Noise @125MHz (typical):
  - 10Hz -54dBc
  - 100Hz -92dBc
  - 1kHz -130dBc
  - 10kHz -149dBc
  - 100kHz -159dBc
  - 1MHz -163dBc
- RMS Phase Jitter @125MHz: 52fs typical

### Environmental Parameters


- Shock: MIL-STD-202, Method 213, Condition E
- Vibration: MIL-STD-883, Method 2007, Condition A
- Storage Temperature Range:  $-55$  to  $125^{\circ}\text{C}$

### Compliance


- RoHS Status (2011/65/EU): Compliant
- REACH Status: Compliant
- MSL Rating (JDEC-STD-033): Not Applicable



### Outline (mm)



### Test Circuit



\* Inclusive of jigging and equipment capacitance

### Sales Office Contact Details:

UK: +44 (0)1460 270200  
Germany: 0800 1808 443


France: 0800 901 383  
USA: +1.760.318.2824

Email: [info@iqdfrequencyproducts.com](mailto:info@iqdfrequencyproducts.com)  
Web: [www.iqdfrequencyproducts.com](http://www.iqdfrequencyproducts.com)


### Packaging Details

- Pack Style: Bulk Loose in bulk pack  
Pack Size: 100
- Pack Style: Cutt In tape, cut from a reel  
Pack Size: 1
- Pack Style: Reel Tape & reel in accordance with EIA-481-D  
Pack Size: 1,000

### Wave Form



### Phase Noise / Jitter



### Electrical Specification - maximum limiting values 3.3V ±10%

| Frequency Min | Frequency Max | Temperature Range    | Stability (Min) | Current Draw | Rise and Fall Time | Duty Cycle     |
|---------------|---------------|----------------------|-----------------|--------------|--------------------|----------------|
|               |               | °C                   | ppm             | mA           | ns                 | %              |
| 500.0kHz      | 19.999999MHz  | 0 to 70<br>-40 to 85 | ±20.0<br>±25.0  | 7<br>7       | 10<br>10           | 45/55<br>45/55 |
| 20.0MHz       | 31.999999MHz  | 0 to 70<br>-40 to 85 | ±20.0<br>±25.0  | 12<br>12     | 10<br>10           | 45/55<br>45/55 |
| 32.0MHz       | 49.999999MHz  | 0 to 70<br>-40 to 85 | ±20.0<br>±25.0  | 20<br>20     | 10<br>10           | 45/55<br>45/55 |
| 50.0MHz       | 79.999999MHz  | 0 to 70<br>-40 to 85 | ±20.0<br>±25.0  | 25<br>25     | 8<br>8             | 45/55<br>45/55 |
| 80.0MHz       | 99.999999MHz  | 0 to 70<br>-40 to 85 | ±20.0<br>±25.0  | 30<br>30     | 5<br>5             | 45/55<br>45/55 |
| 100.0MHz      | 157.0MHz      | 0 to 70<br>-40 to 85 | ±20.0<br>±25.0  | 40<br>40     | 4<br>4             | 45/55<br>45/55 |

This document was correct at the time of printing; please contact your local sales office for the latest version.  
[Click to view latest version on our website.](#)

### Sales Office Contact Details:

UK: +44 (0)1460 270200  
 Germany: 0800 1808 443

France: 0800 901 383  
 USA: +1.760.318.2824

Email: [info@iqdfrequencyproducts.com](mailto:info@iqdfrequencyproducts.com)  
 Web: [www.iqdfrequencyproducts.com](http://www.iqdfrequencyproducts.com)