







- 1
- PARTS COMPLY TO AMP SOLDERABILITY SPECIFICATION 109-11-3.
- 2
- CONTACT IS PLATED OVERALL WITH 0.00127 [.000050] NICKEL, THEN 0.00076 [.000030] GOLD OVER CONTACT LENGTH INDICATED AND MATTE TIN LEAD ON SOLDER TAIL END.
- 3
- CIRCUIT IDENTIFICATION CHARACTERS ARE ADJACENT TO THE INDICATED CAVITIES, BUT LOCATION AND ORIENTATION MAY DIFFER FROM PRINT.
- 4
- DIMENSIONS IN BRACKETS ARE IN INCHES.
- 5
- DRAIN HOLES LOCATED AS SHOWN. OPTIONAL CONSTRUCTION - ALL DRAIN HOLES LOCATED 90° AS SHOWN IN DETAIL A.
- 6
- CONTACT IS PLATED OVERALL WITH 0.00127 [.000050] NICKEL, THEN 0.00076 [.000030] GOLD OVER CONTACT LENGTH INDICATED AND MATTE TIN ON SOLDER TAIL END.
- 7
- SUPERSEDED BY 350584-4



3-DIMENSIONAL MODEL
NTS



PHOSPHOR BRONZE, GOLD	NYLON,UL94-V-2,NATURAL	350584-4
PHOSPHOR BRONZE, GOLD	NYLON,UL94-V-2,NATURAL	350584-2
PHOSPHOR BRONZE, PRE-TIN	NYLON,UL94-V-2,NATURAL	350584-1
PIN CONTACT MATERIAL AND FINISH	HOUSING MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.	DWN B. LEWIS CHK R. SWING APVD M. TRULL	8-25-98 8-25-98 8-25-98
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	NAME
0 PLC ± -	1 PLC ± -	PRODUCT SPEC
2 PLC ± -	3 PLC ± 0.13 [.005]	APPLICATION SPEC
4 PLC ± -	ANGLES ± ± 0°30'	SIZE
MATERIAL SEE TABLE	FINISH SEE TABLE	WEIGHT —
CUSTOMER DRAWING		SCALE 5:1
SHEET 1 OF 1		REV V1

TE Connectivity	PIN HEADER ASSEMBLY, 4 CIRCUIT UNIVERSAL MATE-N-LOK™	RESTRICTED TO
-----------------	--	---------------