

5320FL Multi-Conductor - Commercial Applications - 2 Conductors Cabled



For more Information
please call

1-800-Belden1



General Description:

Fire Alarm Cable, Riser-FPLR, 2-18 AWG solid bare copper conductors with polyolefin insulation, Overall Beldfoil® shield, PVC jacket with ripcord

Usage (Overall)

Suitable Applications:

Fire Protection, Alarm, Signal, Monitor/Detection, Audio Circuits, Control Circuits, Initiating Circuits, Notification Circuits

Physical Characteristics (Overall)

Conductor

AWG:

# Conductors	AWG	Stranding	Conductor Material
2	18	Solid	BC - Bare Copper

Total Number of Conductors:

2

Insulation

Insulation Material:

Insulation Material	Wall Thickness (mm)
PP - Polypropylene	0.178

Outer Shield

Outer Shield Material:

Outer Shield Trade Name	Outer Shield Material	Coverage (%)
Beldfoil®	Aluminum Foil-Polyester Tape	100

Outer Shield Drain Wire AWG:

AWG	Stranding	Drain Wire Conductor Material
24	Solid	TC - Tinned Copper

Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (mm)
PVC - Polyvinyl Chloride	0.432

Outer Jacket Ripcord:

Yes

Overall Cable

Overall Cabling Lay Length & Direction:

Length (mm)	Direction	Twists (twist/m)
69.850	Left Hand	14.436

Overall Cabling Color Code Chart:

Number	Color
1	Black
2	Red

Overall Nominal Diameter:

3.734 mm

Mechanical Characteristics (Overall)

Operating Temperature Range: -20°C To +75°C

UL Temperature Rating: 75°C

Bulk Cable Weight: 29.764 Kg/Km

Max. Recommended Pulling Tension: 236.644 N

Min. Bend Radius/Minor Axis: 38.100 mm

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification: FPLR

NEC Articles: 760

METRIC MEASUREMENT VERSION

5320FL Multi-Conductor - Commercial Applications - 2 Conductors Cabled

EU Directive 2011/65/EU (ROHS II):	Yes
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Flame Test

UL Flame Test:	UL1666 Vertical Shaft
CSA Flame Test:	FT4

Plenum/Non-Plenum

Plenum Number:	6320FL
----------------	--------

Electrical Characteristics (Overall)

Nom. Inductance:

Inductance (µH/m)
0.492

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/m)
180.455

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/m)
324.819

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)
20.9984

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/km)
58.730

Max. Operating Voltage - UL:

Voltage
300 V RMS

Max. Recommended Current:

Description	Current
10C Temperature Rise	5 Amps per conductor @ 25°C

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
5320FL D15U1000	305 MT	8.165 KG	BLUE		2 #18 PP FS FRPVC
5320FL D15I1000	305 MT	8.165 KG	BLUE	C	2 #18 PP FS FRPVC
5320FL 002U1000	305 MT	8.165 KG	RED		2 #18 PP FS FRPVC
5320FL 002U500	152 MT	4.309 KG	RED		2 #18 PP FS FRPVC
5320FL 002I1000	305 MT	8.165 KG	RED	C	2 #18 PP FS FRPVC
5320FL 003C500	152 MT	3.629 KG	ORANGE		2 #18 PP FS FRPVC
5320FL 004C500	152 MT	3.629 KG	YELLOW		2 #18 PP FS FRPVC
5320FL 004I1000	305 MT	8.165 KG	YELLOW		2 #18 PP FS FRPVC
5320FL 007I1000	305 MT	8.165 KG	VIOLET		2 #18 PP FS FRPVC

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 3 Revision Date: 08-20-2013

© 2014 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

METRIC MEASUREMENT VERSION

5320FL Multi-Conductor - Commercial Applications - 2 Conductors Cabled

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.