

SS3 Series

Controlled Avalanche Power Diodes




Features:

- For surface mounted application.
- Metal to silicon rectifier, majority carrier conduction.
- Low forward voltage drop.
- Easy pick and place.
- High surge current capability.
- Epitaxial construction
- High temperature soldering: 260°C/10 seconds at terminals.

Mechanical Data:

Case	: Moulded plastic.
Terminals	: Solder plated.
Polarity	: Indicated by cathode band.

SMC/DO-214AB



Dimensions : Inches (Millimetres)

Maximum Ratings and Electrical Characteristics

Rating at 25°C ambient temperature unless otherwise specified. Single phase, half wave, 60Hz, resistive or inductive load. For capacitive load, derate current by 20%.

Type Number	Symbol	SS34	SS36	Unit
Maximum recurrent peak reverse voltage	V _{RRM}	40	60	V
Maximum RMS voltage	V _{RMS}	28	42	
Maximum DC blocking voltage	V _{DC}	40	60	
Maximum average forward rectified current at T _L (See Figure 1)	I _(AV)	3.0		A
Peak forward surge current, 8.3ms single half sine-wave superimposed on rated load (JEDEC method)	I _{FSM}	100		
Maximum Instantaneous forward voltage (Note 1) at 3.0A	V _F	0.5	0.75	V
Maximum DC reverse current at T _A = 25°C at rated DC blocking voltage at T _A = 100°C	I _R	0.5		mA
		20	10.0	
Typical thermal resistance (Note 2)	R _{θJL}	17		°C/W
	R _{θJA}	55		
Operating temperature range	T _J	-55 to +125	-55 to +150	°C
Storage temperature range	T _{STG}	-55 to +150		

Notes:

1. Pulse test with $PW = 300\mu\text{sec}$, 1% duty cycle.
2. Measured on PC Board with 0.6 x 0.6" (16 x 16mm) copper pad areas.

Ratings and Characteristic Curves

Figure 1 Maximum Forward Current Derating Curve




Figure 2 Maximum Non-Repetitive Forward Surge Current




Figure 3 Typical Forward Characteristics




Figure 4 Typical Reverse Characteristics




Figure 5 Typical Junction Capacitance





Figure 6 Typical Transient Thermal Impedance



SS3 Series

Controlled Avalanche Power Diodes



Specifications

I_F (AV) (A)	T_C (°C)	V_{RRM} (V)	V_{FM} maximum (V)	I_{RM} maximum (mA)	Package	Part Number
3	105	40	0.5	0.5	DO-214AB (SMC)	SS34
		60	0.75			SS36

SS3 Series

Controlled Avalanche Power Diodes



Notes:

International Sales Offices:



AUSTRALIA – Farnell InOne

Tel No: ++ 61 2 9645 8888
Fax No: ++ 61 2 9644 7898



FINLAND – Farnell InOne

Tel No: ++ 358 9 560 7780
Fax No: ++ 358 9 345 5411



NETHERLANDS – Farnell InOne

Tel No: ++ 31 30 241 7373
Fax No: ++ 31 30 241 7333



SWITZERLAND – Farnell InOne

Tel No: ++ 41 1 204 64 64
Fax No: ++ 41 1 204 64 54



AUSTRIA – Farnell InOne

Tel No: ++ 43 662 2180 680
Fax No: ++ 43 662 2180 670



FRANCE – Farnell InOne

Tel No: ++ 33 474 68 99 99
Fax No: ++ 33 474 68 99 90



NEW ZEALAND – Farnell InOne

Tel No: ++ 64 9 357 0646
Fax No: ++ 64 9 357 0656



UK – Farnell InOne

Tel No: ++ 44 8701 200 200
Fax No: ++ 44 8701 200 201



BELGIUM – Farnell InOne

Tel No: ++ 32 3 475 2810
Fax No: ++ 32 3 227 3648



GERMANY – Farnell InOne

Tel No: ++ 49 89 61 39 39 39
Fax No: ++ 49 89 613 59 01



NORWAY – Farnell InOne

Tel No: ++ 45 44 53 66 66
Fax No: ++ 45 44 53 66 02



UK – BuckHickman InOne

++ 44 8450 510 150
++ 44 8450 510 130



BRAZIL – Farnell-Newark InOne

Tel No: ++ 55 11 4066 9400
Fax No: ++ 55 11 4066 9410



HONG KONG – Farnell-Newark InOne

Tel No: ++ 852 2268 9888
Fax No: ++ 852 2268 9899



PORTUGAL – Farnell InOne

Tel No: ++ 34 93 475 8804
Fax No: ++ 34 93 474 5288



UK – CPC

++ 44 8701 202 530
++ 44 8701 202 531



CHINA – Farnell-Newark InOne

Tel No: ++86 10 6238 5152
Fax No: ++86 10 6238 5022



IRELAND – Farnell InOne

Tel No: ++ 353 1 830 9277
Fax No: ++ 353 1 830 9016



SINGAPORE – Farnell-Newark InOne

Tel No: ++ 65 6788 0200
Fax No: ++ 65 6788 0300



EXPORT – Farnell InOne

Tel No: ++ 44 8701 200 208
Fax No: ++ 44 8701 200 209

For enquiries from all other markets



DENMARK – Farnell InOne

Tel No: ++ 45 44 53 66 44
Fax No: ++ 45 44 53 66 06



ITALY – Farnell InOne

Tel No: ++ 39 02 93 995 200
Fax No: ++ 39 02 93 995 300



SPAIN – Farnell InOne

Tel No: ++ 34 93 475 8805
Fax No: ++ 34 93 474 5107



ESTONIA – Farnell InOne

Tel No: ++ 358 9 560 7780
Fax No: ++ 358 9 345 5411



MALAYSIA – Farnell-Newark InOne

Tel No: ++ 60 3 7873 8000
Fax No: ++ 60 3 7873 7000



SWEDEN – Farnell InOne

Tel No: ++ 46 8 730 50 00
Fax No: ++ 46 8 83 52 62

<http://www.farnellinone.com>

<http://www.buckhickmaninone.com>

<http://www.cpc.co.uk>

Disclaimer This data sheet and its contents (the "Information") belong to the Premier Farnell Group (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2004.

