


SPECIFICATIONS		
SILIKROME®	GRADE	
	COMMERCIAL	MILITARY
Material	Silicone Rubber ASTM D 1418	Silicone Rubber conforming to A-A-59588 Class II GR 50
Temperature Range	-112°F to +400°F (-80°C to +204°C)	-160°F to +450°F (-106°C to +260°C)
	-112°F to +575°F (-80°C to +302°C)	
Shelf Life	25 Years (minimum)	
Resistant to	Salt spray, sunlight, ozone, cleaning solutions, and most acids	
Physical Characteristics	Flexible, non-breakable, re-usable. Acts as shock mount. Protects against shattering. Easy to mount.	



UNLESS OTHERWISE SPECIFIED, TOLERANCES ARE ±.010 FOR DECIMALS

SECTION AA

C	REDRAWN and MAT'L CHANGED				S. GOK	05.28.09	
B	CAD COMPUTER GENERATED					01.10.03	
A	CHANGE DIMENSIONS TO DECIMALS				NKS	01.05.67	
REV.	DESCRIPTION				DATE		
MAXIMUM AND MINIMUM MEASUREMENTS ARE STATED DIRECTLY ON EACH DIMENSION.		TITLE:	SILIKROMES® COLORED FILTERS FOR INCANDESCENT T-1 3/4 LAMPS		ENG.	S. GOK	05.28.09
					DWN.	ED	09.26.62
					CHKD.	J. CELLA	05.28.09
MAT'L: SEE ABOVE			APM-HEXSEAL CORPORATION		SCALE	DWG. NO.	1813/1
COLOR: SPECIFY					10 : 1		

THIS DRAWING COVERS PROPRIETARY ITEM AND IS THE PROPERTY OF THE APM-HEXSEAL CORPORATION.
THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE WRITTEN APPROVAL OF AN OFFICER OF THE APM-HEXSEAL CORPORATION.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[APM HEXSEAL:](#)

[1813/1](#) [1813/1 A2 C](#) [1813/1 B12-4 C](#) [1813/1 LW17-14 C](#) [1813/1 G1 C](#) [1813/1 Y3-3](#) [1813/1 R 2 C](#)