LinCMOS™ PRECISION QUAD OPERATIONAL AMPLIFIERS

Check for Samples: TLC27M4, TLC27M4A, TLC27M4B, TLC27M4Y, TLC27M9

FEATURES

- **Trimmed Offset Voltage**
  - **TLC27M9 . . . 900 µV Max at T_A = 25°C, V_{DD} = 5 V**
- **Input Offset Voltage Drift . . . Typically 0.1 µV/Month, Including the First 30 Days**
- **Wide Range of Supply Voltages Over Specified Temperature Range:**
  - **0°C to 70°C . . . 3 V to 16 V**
  - **–40°C to 85°C . . . 4 V to 16 V**
  - **–55°C to 125°C . . . 4 V to 16 V**
- **Single-Supply Operation**
- **Common-Mode Input Voltage Range Extends Below the Negative Rail (C-Suffix, I-Suffix Types)**
- **Low Noise . . . Typically 32 nV/$\sqrt{\text{Hz}}$ at f = 1 kHz**
- **Low Power . . . Typically 2.1 mW at T_A = 25°C, V_{DD} = 5 V**
- **Output Voltage Range Includes Negative Rail**
- **High Input Impedance . . . 10^{12} Ω Typ**
- **ESD-Protection Circuitry**
- **Small-Outline Package Option Also Available in Tape and Reel**
- **Designed-In Latch-Up Immunity**

D, J, N, OR PW PACKAGE
(TOP VIEW)



FK PACKAGE
(TOP VIEW)



NC – No internal connection

DESCRIPTION

The TLC27M4 and TLC27M9 quad operational amplifiers combine a wide range of input offset voltage grades with low offset voltage drift, high input impedance, low noise, and speeds comparable to that of general-purpose bipolar devices. These devices use Texas Instruments silicon-gate LinCMOS™ technology, which provides offset voltage stability far exceeding the stability available with conventional metal-gate processes.

The extremely high input impedance, low bias currents, make these cost-effective devices ideal for applications that have previously been reserved for general-purpose bipolar products, but with only a fraction of the power consumption.

DISTRIBUTION OF TLC27M9
INPUT OFFSET VOLTAGE



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

LinCMOS is a trademark of Texas Instruments Incorporated.

PRODUCTION DATA information is current as of publication date. Products conform to specifications per the terms of the Texas Instruments standard warranty. Production processing does not necessarily include testing of all parameters.

Copyright © 1987–2012, Texas Instruments Incorporated

Four offset voltage grades are available (C-suffix and I-suffix types), ranging from the low-cost TLC27M4 (10 mV) to the high-precision TLC27M9 (900 µV). These advantages, in combination with good common-mode rejection and supply voltage rejection, make these devices a good choice for new state-of-the-art designs as well as for upgrading existing designs.

In general, many features associated with bipolar technology are available on LinCMOS™ operational amplifiers, without the power penalties of bipolar technology. General applications such as transducer interfacing, analog calculations, amplifier blocks, active filters, and signal buffering are easily designed with the TLC27M4 and TLC27M9. The devices also exhibit low voltage single-supply operation, and low power consumption, making them ideally suited for remote and inaccessible battery-powered applications. The common-mode input voltage range includes the negative rail.

A wide range of packaging options is available, including small-outline and chip-carrier versions for high-density system applications.

The device inputs and outputs are designed to withstand −100-mA surge currents without sustaining latch-up.

The TLC27M4 and TLC27M9 incorporate internal ESD-protection circuits that prevent functional failures at voltages up to 2000 V as tested under MIL-STD-883C, Method 3015; however, care should be exercised in handling these devices, as exposure to ESD may result in the degradation of the device parametric performance.

The C-suffix devices are characterized for operation from 0°C to 70°C. The I-suffix devices are characterized for operation from –40°C to 85°C. The M-suffix devices are characterized for operation over the full military temperature range of –55°C to 125°C.

AVAILABLE OPTIONS

T_A	V_{IO}max AT 25°C	PACKAGE					CHIP FORM (Y)
		SMALL OUTLINE (D)(1)	CHIP CARRIER (FK)	CERAMIC DIP (J)	PLASTIC DIP (N)	TSSOP (PW)(1)	
0°C to 70°C	900 µV	TLC27M9CD	—	—	TLC27M9CN	—	—
	2 mV	TLC27M4BCD	—	—	TLC27M4BCN	—	—
	5 mV	TLC27M4ACD	—	—	TLC27M4ACN	—	—
	10 mV	TLC27M4CD	—	—	TLC27M4CN	TLC27M4CPW	TLC27M4Y
–40°C to 85°C	900 µV	TLC27M9ID	—	—	TLC27M9IN	—	—
	2 mV	TLC27M4BID	—	—	TLC27M4BIN	—	—
	5 mV	TLC27M4AID	—	—	TLC27M4AIN	—	—
	10 mV	TLC27M4ID	—	—	TLC27M4IN	TLC27M41PW	—
–55°C to 125°C	900 µV	TLC27M9MD	TLC27M9MFK	TLC27M9MJ	TLC27M9MN	—	—
	10 mV	TLC27M4MD	TLC27M4MFK	TLC27M4MJ	TLC27M4MN	—	—

(1) The D and PW package is available taped and reeled. Add R suffix to the device type (e.g., TLC279CDR).

Copyright © 1987–2012, Texas Instruments Incorporated

EQUIVALENT SCHEMATIC (EACH AMPLIFIER)



Copyright © 1987–2012, Texas Instruments Incorporated

TLC27M4Y chip information

This chip, when properly assembled, displays characteristics similar to the TLC27M4C. Thermal compression or ultrasonic bonding may be used on the doped-aluminum bonding pads. Chips may be mounted with conductive epoxy or a gold-silicon preform.



Copyright © 1987–2012, Texas Instruments Incorporated

ABSOLUTE MAXIMUM RATINGS

over operating free-air temperature range (unless otherwise noted)(1)

		VALUE	UNIT
Supply voltage, V_{DD}(2)		18	V
Differential input voltage, V_{ID}(3)		±VDD	
Input voltage range, V_I (any input)		–0.3 V to V_{DD}	
Input current, I_I		±5	mA
Output current, I_O (each output)		±30	mA
Total current into V_{DD}		45	mA
Total current out of GND		45	mA
Duration of short-circuit current at (or below) 25°C(4)		unlimited	
Continuous total dissipation		See Dissipation Rating Table	
Operating free-air temperature, T_A	C suffix	0 to 70	°C
	I suffix	–40 to 85	°C
	M suffix	–55 to 125	°C
Storage temperature range		–65 to 150	°C
Case temperature for 60 seconds: FK package		260	°C
Lead temperature 1,6 mm (1/16 inch) from case for 10 seconds: D, N, or PW package		260	°C
Lead temperature 1,6 mm (1/16 inch) from case for 60 seconds: J package		300	°C

(1) Stresses beyond those listed under “absolute maximum ratings” may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under “recommended operating conditions” is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.
(2) All voltage values, except differential voltages, are with respect to network ground.
(3) Differential voltages are at IN+ with respect to IN –.
(4) The output may be shorted to either supply. Temperature and/or supply voltages must be limited to ensure that the maximum dissipation rating is not exceeded (see application section).

DISSIPATION RATINGS

PACKAGE	$T_A \le 25°C$ POWER RATING	DERATING FACTOR ABOVE $T_A = 25°C$	$T_A = 70°C$ POWER RATING	$T_A = 85°C$ POWER RATING	$T_A = 125°C$ POWER RATING
D	950 mW	7.6 mW/°C	608 mW	494 mW	—
FK	1375 mW	11.0 mW/°C	880 mW	715 mW	275 mW
J	1375 mW	11.0 mW/°C	880 mW	715 mW	275 mW
N	1575 mW	12.6 mW/°C	1008 mW	819 mW	—
PW	700 mW	5.6 mW/°C	448 mW	—	—

RECOMMENDED OPERATING CONDITIONS

		MIN	MAX	MIN	MAX	MIN	MAX	UNIT
Supply voltage, V_{DD}		3	16	4	16	4	16	V
Common mode input voltage, V_{IC}	V_{DD} = 5 V	–0.2	3.5	–0.2	3.5	0	3.5	V
	V_{DD} = 10 V	–0.2	8.5	–0.2	8.5	0	8.5	
Operating free-air temperature, T_A		0	70	–40	85	–55	125	°C

Copyright © 1987–2012, Texas Instruments Incorporated

ELECTRICAL CHARACTERISTICS

at specified free-air temperature, V_{DD} = 5 V (unless otherwise noted)

PARAMETER			TEST CONDITIONS		T_A[1]	TLC27M4C TLC27M4AC TLC27M4BC TLC27M9C			UNIT
						MIN	TYP	MAX	
V_{IO}	Input offset voltage	TLC27M4C	V_O = 1.4 V, R_S = 50 Ω,	V_{IC} = 0, R_L = 100 kΩ	25°C		1.1	10	mV
					Full range			12	
		TLC27M4AC	V_O = 1.4 V, R_S = 50 Ω,	V_{IC} = 0, R_L = 100 kΩ	25°C		0.9	5	
					Full range			6.5	
		TLC274BC	V_O = 1.4 V, R_S = 50 Ω,	V_{IC} = 0, R_L = 100 kΩ	25°C		250	2000	µV
					Full range			3000	
		TLC279C	V_O = 1.4 V, R_S = 50 Ω,	V_{IC} = 0, R_L = 100 kΩ	25°C		210	900	
					Full range			1500	
α_{VIO}	Average temperature coefficient of input offset voltage				25°C to 70°C		1.7		µV/°C
I_{IO}	Input offset current[2]		V_O = 2.5 V,	V_{IC} = 2.5 V	25°C		0.1		pA
					70°C		7	300	
I_{IB}	Input bias current[2]		V_O = 2.5 V,	V_{IC} = 2.5 V	25°C		0.6		pA
					70°C		40	600	
V_{ICR}	Common-mode input voltage range[3]				25°C	–0.2 to 4	–0.3 to 4.2		V
					Full range	–0.2 to 3.5			V
V_{OH}	High-level output voltage		V_{ID} = 100 mV,	R_L = 100 kΩ	25°C	3.2	3.9		V
					0°C	3	3.9		
					70°C	3	4		
V_{OL}	Low-level output voltage		V_{ID} = –100 mV,	I_{OL} = 0	25°C		0	50	mV
					0°C		0	50	
					70°C		0	50	
A_{VD}	Large-signal differential voltage amplification		V_O = 0.25 V to 2 V,	R_L = 100 kΩ	25°C	25	170		V/mV
					0°C	15	200		
					70°C	15	140		
CMRR	Common-mode rejection ratio		V_{IC} = V_{ICR}min		25°C	65	91		dB
					0°C	60	91		
					70°C	60	92		
k_{SVR}	Supply-voltage rejection ratio ($\Delta V_{DD}/\Delta V_{IO}$)		V_{DD} = 5 V to 10 V,	V_O = 1.4 V	25°C	70	93		dB
					0°C	60	92		
					70°C	60	94		
I_{DD}	Supply current (four amplifiers)		V_O = 2.5 V, No load	V_{IC} = 2.5 V,	25°C		420	1120	µA
					0°C		500	1280	
					70°C		340	880	

(1) Full range is 0°C to 70°C.
(2) The typical values of input bias current and input offset current below 5 pA were determined mathematically.
(3) This range also applies to each input individually.

Copyright © 1987–2012, Texas Instruments Incorporated

ELECTRICAL CHARACTERISTICS

at specified free-air temperature, V_{DD} = 10 V (unless otherwise noted)

PARAMETER			TEST CONDITIONS		T_A (1)	TLC27M4C TLC27M4AC TLC27M4BC TLC27M9C			UNIT
						MIN	TYP	MAX	
V_{IO}	Input offset voltage	TLC27M4C	V_O = 1.4 V, R_S = 50 Ω,	V_{IC} = 0, R_L = 100 kΩ	25°C		1.1	10	mV
					Full range			12	
		TLC27M4AC	V_O = 1.4 V, R_S = 50 Ω,	V_{IC} = 0, R_L = 100 kΩ	25°C		0.9	5	
					Full range			6.5	
		TLC274BC	V_O = 1.4 V, R_S = 50 Ω,	V_{IC} = 0, R_L = 100 kΩ	25°C		260	2000	µV
					Full range			3000	
		TLC279C	V_O = 1.4 V, R_S = 50 Ω,	V_{IC} = 0, R_L = 100 kΩ	25°C		220	1200	
					Full range			1900	
α_{VIO}	Average temperature coefficient of input offset voltage				25°C to 70°C		2.1		µV/°C
I_{IO}	Input offset current (2)		V_O = 5 V,	V_{IC} = 5 V	25°C		0.1		pA
					70°C		7	300	
I_{IB}	Input bias current (2)		V_O = 5 V,	V_{IC} = 5 V	25°C		0.7		pA
					70°C		50	600	
V_{ICR}	Common-mode input voltage range (3)				25°C	–0.2 to 9	–0.3 to 9.2		V
					Full range	–0.2 to 8.5			V
V_{OH}	High-level output voltage		V_{ID} = 100 mV,	R_L = 100 kΩ	25°C	8	8.7		V
					0°C	7.8	8.7		
					70°C	7.8	8.7		
V_{OL}	Low-level output voltage		V_{ID} = –100 mV,	I_{OL} = 0	25°C		0	50	mV
					0°C		0	50	
					70°C		0	50	
A_{VD}	Large-signal differential voltage amplification		V_O = 1 V to 6 V,	R_L = 100 kΩ	25°C	25	275		V/mV
					0°C	15	320		
					70°C	15	230		
CMRR	Common-mode rejection ratio		V_{IC} = V_{ICR}min		25°C	65	94		dB
					0°C	60	94		
					70°C	60	94		
k_{SVR}	Supply-voltage rejection ratio ($\Delta V_{DD}/\Delta V_{IO}$)		V_{DD} = 5 V to 10 V,	V_O = 1.4 V	25°C	70	93		dB
					0°C	60	92		
					70°C	60	94		
I_{DD}	Supply current (four amplifiers)		V_O = 5 V, No load	V_{IC} = 5 V,	25°C		570	1200	µA
					0°C		690	1600	
					70°C		440	1120	

(1) Full range is 0°C to 70°C.
(2) The typical values of input bias current and input offset current below 5 pA were determined mathematically.
(3) This range also applies to each input individually.

Copyright © 1987–2012, Texas Instruments Incorporated

ELECTRICAL CHARACTERISTICS

at specified free-air temperature, V_{DD} = 5 V (unless otherwise noted)

PARAMETER			TEST CONDITIONS		T_A (1)	TLC27M4I TLC27M4AI TLC27M4BI TLC27M9I			UNIT
						MIN	TYP	MAX	
V_{IO}	Input offset voltage	TLC27M4I	V_O = 1.4 V, R_S = 50 Ω,	V_{IC} = 0, R_L = 100 kΩ	25°C		1.1	10	mV
					Full range			13	
		TLC27M4AI	V_O = 1.4 V, R_S = 50 Ω,	V_{IC} = 0, R_L = 100 kΩ	25°C		0.9	5	
					Full range			6.5	
		TLC27M4BI	V_O = 1.4 V, R_S = 50 Ω,	V_{IC} = 0, R_L = 100 kΩ	25°C		250	2000	µV
					Full range			3000	
		TLC27M9I	V_O = 1.4 V, R_S = 50 Ω,	V_{IC} = 0, R_L = 100 kΩ	25°C		210	900	
					Full range			2000	
α_{VIO}	Average temperature coefficient of input offset voltage				25°C to 85°C		1.7		µV/°C
I_{IO}	Input offset current (2)		V_O = 2.5 V,	V_{IC} = 2.5 V	25°C		0.1		pA
					85°C		24	1000	
I_{IB}	Input bias current (2)		V_O = 2.5 V,	V_{IC} = 2.5 V	25°C		0.6		pA
					85°C		200	2000	
V_{ICR}	Common-mode input voltage range (3)				25°C	–0.2 to 4	–0.3 to 4.2		V
					Full range	–0.2 to 3.5			V
V_{OH}	High-level output voltage		V_{ID} = 100 mV,	R_L = 100 kΩ	25°C	3.2	3.9		V
					–40°C	3	3.9		
					85°C	3	4		
V_{OL}	Low-level output voltage		V_{ID} = –100 mV,	I_{OL} = 0	25°C		0	50	mV
					–40°C		0	50	
					85°C		0	50	
A_{VD}	Large-signal differential voltage amplification		V_O = 0.25 V to 2 V,	R_L = 100 kΩ	25°C	25	170		V/mV
					–40°C	15	270		
					85°C	15	130		
CMRR	Common-mode rejection ratio		V_{IC} = V_{ICR}min		25°C	65	91		dB
					–40°C	60	90		
					85°C	60	90		
k_{SVR}	Supply-voltage rejection ratio ($\Delta V_{DD}/\Delta V_{IO}$)		V_{DD} = 5 V to 10 V,	V_O = 1.4 V	25°C	70	93		dB
					–40°C	60	91		
					85°C	60	94		
I_{DD}	Supply current (four amplifiers)		V_O = 2.5 V, No load	V_{IC} = 2.5 V,	25°C		420	1120	µA
					–40°C		630	1600	
					85°C		320	800	

(1) Full range is –40°C to 85°C.
(2) The typical values of input bias current and input offset current below 5 pA were determined mathematically.
(3) This range also applies to each input individually.

Copyright © 1987–2012, Texas Instruments Incorporated

ELECTRICAL CHARACTERISTICS

at specified free-air temperature, V_{DD} = 10 V (unless otherwise noted)

PARAMETER			TEST CONDITIONS		T_A[1]	TLC27M4I TLC27M4AI TLC27M4BI TLC27M9I			UNIT
						MIN	TYP	MAX	
V_{IO}	Input offset voltage	TLC27M4I	V_O = 1.4 V, R_S = 50 Ω,	V_{IC} = 0, R_L = 100 kΩ	25°C		1.1	10	mV
					Full range			13	
		TLC27M4AI	V_O = 1.4 V, R_S = 50 Ω,	V_{IC} = 0, R_L = 100 kΩ	25°C		0.9	5	
					Full range			7	
		TLC27M4BI	V_O = 1.4 V, R_S = 50 Ω,	V_{IC} = 0, R_L = 100 kΩ	25°C		260	2000	µV
					Full range			3500	
		TLC27M9I	V_O = 1.4 V, R_S = 50 Ω,	V_{IC} = 0, R_L = 100 kΩ	25°C		220	1200	
					Full range			2900	
α_{VIO}	Average temperature coefficient of input offset voltage				25°C to 85°C		2.1		µV/°C
I_{IO}	Input offset current[2]		V_O = 5 V,	V_{IC} = 5 V	25°C		0.1		pA
					85°C		26	1000	
I_{IB}	Input bias current[2]		V_O = 5 V,	V_{IC} = 5 V	25°C		0.7		pA
					85°C		220	2000	
V_{ICR}	Common-mode input voltage range[3]				25°C	–0.2 to 9	–0.3 to 9.2		V
					Full range	–0.2 to 8.5			V
V_{OH}	High-level output voltage		V_{ID} = 100 mV,	R_L = 100 kΩ	25°C	8	8.7		V
					–40°C	7.8	8.7		
					85°C	7.8	8.7		
V_{OL}	Low-level output voltage		V_{ID} = –100 mV,	I_{OL} = 0	25°C		0	50	mV
					–40°C		0	50	
					85°C		0	50	
A_{VD}	Large-signal differential voltage amplification		V_O = 1 V to 6 V,	R_L = 100 kΩ	25°C	25	275		V/mV
					–40°C	15	390		
					85°C	15	220		
CMRR	Common-mode rejection ratio		V_{IC} = V_{ICR}min		25°C	65	94		dB
					–40°C	60	93		
					85°C	60	94		
k_{SVR}	Supply-voltage rejection ratio ($\Delta V_{DD}/\Delta V_{IO}$)		V_{DD} = 5 V to 10 V,	V_O = 1.4 V	25°C	70	93		dB
					–40°C	60	91		
					85°C	60	94		
I_{DD}	Supply current (four amplifiers)		V_O = 5 V, No load	V_{IC} = 5 V,	25°C		570	1200	µA
					–40°C		900	1800	
					85°C		410	1040	

(1) Full range is –40°C to 85°C.
(2) The typical values of input bias current and input offset current below 5 pA were determined mathematically.
(3) This range also applies to each input individually.

Copyright © 1987–2012, Texas Instruments Incorporated

ELECTRICAL CHARACTERISTICS

at specified free-air temperature, V_{DD} = 5 V (unless otherwise noted)

PARAMETER			TEST CONDITIONS		T_A (1)	TLC27M4M TLC27M9M			UNIT
						MIN	TYP	MAX	
V_{IO}	Input offset voltage	TLC27M4M	V_O = 1.4 V, R_S = 50 Ω,	V_{IC} = 0, R_L = 100 kΩ	25°C		1.1	10	mV
					Full range			12	
		TLC27M9M	V_O = 1.4 V, R_S = 50 Ω,	V_{IC} = 0, R_L = 100 kΩ	25°C		210	900	µV
					Full range			3750	
α_{VIO}	Average temperature coefficient of input offset voltage				25°C to 125°C		1.7		µV/°C
I_{IO}	Input offset current (2)		V_O = 2.5 V,	V_{IC} = 2.5 V	25°C		0.1		pA
					125°C		1.4	15	nA
I_{IB}	Input bias current (2)		V_O = 2.5 V,	V_{IC} = 2.5 V	25°C		0.6		pA
					85°C		9	35	nA
V_{ICR}	Common-mode input voltage range (3)				25°C	0 to 4	–0.3 to 4.2		V
					Full range	0 to 3.5			V
V_{OH}	High-level output voltage		V_{ID} = 100 mV,	R_L = 100 kΩ	25°C	3.2	3.9		V
					–55°C	3	3.9		
					125°C	3	4		
V_{OL}	Low-level output voltage		V_{ID} = –100 mV,	I_{OL} = 0	25°C		0	50	mV
					–55°C		0	50	
					125°C		0	50	
A_{VD}	Large-signal differential voltage amplification		V_O = 0.25 V to 2 V,	R_L = 100 kΩ	25°C	25	170		V/mV
					–55°C	15	270		
					125°C	15	120		
CMRR	Common-mode rejection ratio		V_{IC} = V_{ICR}min		25°C	65	91		dB
					–55°C	60	89		
					125°C	60	91		
k_{SVR}	Supply-voltage rejection ratio ($\Delta V_{DD}/\Delta V_{IO}$)		V_{DD} = 5 V to 10 V,	V_O = 1.4 V	25°C	70	93		dB
					–55°C	60	91		
					125°C	60	94		
I_{DD}	Supply current (four amplifiers)		V_O = 2.5 V, No load	V_{IC} = 2.5 V,	25°C		420	1120	µA
					–55°C		680	1760	
					125°C		280	720	

(1) Full range is –55°C to 125°C.
(2) The typical values of input bias current and input offset current below 5 pA were determined mathematically.
(3) This range also applies to each input individually.

Copyright © 1987–2012, Texas Instruments Incorporated

ELECTRICAL CHARACTERISTICS

at specified free-air temperature, V_{DD} = 10 V (unless otherwise noted)

PARAMETER			TEST CONDITIONS		T_A (1)	TLC27M4M TLC27M9M			UNIT
						MIN	TYP	MAX	
V_{IO}	Input offset voltage	TLC27M4M	V_O = 1.4 V, R_S = 50 Ω,	V_{IC} = 0, R_L = 100 kΩ	25°C		1.1	10	mV
					Full range			12	
		TLC27M9M	V_O = 1.4 V, R_S = 50 Ω,	V_{IC} = 0, R_L = 100 kΩ	25°C		220	1200	µV
					Full range			4300	
α_{VIO}	Average temperature coefficient of input offset voltage				25°C to 125°C		2.1		µV/°C
I_{IO}	Input offset current (2)		V_O = 5 V,	V_{IC} = 5 V	25°C		0.1		pA
					125°C		1.8	15	nA
I_{IB}	Input bias current (2)		V_O = 5 V,	V_{IC} = 5 V	25°C		0.7		pA
					125°C		10	35	nA
V_{ICR}	Common-mode input voltage range (3)				25°C	0 to 9	–0.3 to 9.2		V
					Full range	–0.2 to 8.5			V
V_{OH}	High-level output voltage		V_{ID} = 100 mV,	R_L = 100 kΩ	25°C	8	8.7		V
					–55°C	7.8	8.6		
					125°C	7.8	8.8		
V_{OL}	Low-level output voltage		V_{ID} = –100 mV,	I_{OL} = 0	25°C		0	50	mV
					–55°C		0	50	
					125°C		0	50	
A_{VD}	Large-signal differential voltage amplification		V_O = 1 V to 6 V,	R_L = 100 kΩ	25°C	25	275		V/mV
					–55°C	15	420		
					125°C	15	190		
CMRR	Common-mode rejection ratio		V_{IC} = V_{ICR}min		25°C	65	94		dB
					–55°C	60	93		
					125°C	60	93		
k_{SVR}	Supply-voltage rejection ratio ($\Delta V_{DD}/\Delta V_{IO}$)		V_{DD} = 5 V to 10 V,	V_O = 1.4 V	25°C	70	93		dB
					–55°C	60	91		
					125°C	60	94		
I_{DD}	Supply current (four amplifiers)		V_O = 5 V, No load	V_{IC} = 5 V,	25°C		570	1200	µA
					–55°C		980	2000	
					125°C		360	960	

(1) Full range is –55°C to 70°C.
(2) The typical values of input bias current and input offset current below 5 pA were determined mathematically.
(3) This range also applies to each input individually.

Copyright © 1987–2012, Texas Instruments Incorporated

ELECTRICAL CHARACTERISTICS

V_{DD} = 5 V, T_A = 25°C (unless otherwise noted)

PARAMETER		TEST CONDITIONS		TLC27M4Y			UNIT
				MIN	TYP	MAX	
V_{IO}	Input offset voltage	V_O = 1.4 V, R_S = 50 Ω,	V_{IC} = 0, R_L = 100 kΩ		1.1	10	mV
α_{VIO}	Temperature coefficient of input offset voltage	T_A = 25°C to 70°C			1.7		µV/°C
I_{IO}	Input offset current(1)	V_O = 2.5 V,	V_{IC} = 2.5 V		0.1		pA
I_{IB}	Input bias current(1)	V_O = 2.5 V,	V_{IC} = 2.5 V		0.6		pA
V_{ICR}	Common-mode input voltage range(2)			–0.2 to 4	–0.3 to 4.2		V
V_{OH}	High-level output voltage	V_{ID} = 100 mV,	R_L = 100 kΩ	3.2	3.9		V
V_{OL}	Low-level output voltage	V_{ID} = –100 mV,	I_{OL} = 0		0	50	mV
A_{VD}	Large-signal differential voltage amplification	V_O = 0.25 V to 2 V,	R_L= 100 kΩ	25	170		V/mV
CMRR	Common-mode rejection ratio	V_{IC} = V_{ICR}min		65	91		dB
k_{SVR}	Supply-voltage rejection ratio ($\Delta V_{DD}/\Delta V_{IO}$)	V_{DD} = 5 V to 10 V,	V_O = 1.4 V	70	93		dB
I_{DD}	Supply current (four amplifiers)	V_O = 2.5 V, No load	V_{IC} = 2.5 V,		420	1120	µA

(1) The typical values of input bias current and input offset current below 5 pA were determined mathematically
(2) This range also applies to each input individually.

ELECTRICAL CHARACTERISTICS

V_{DD} = 10 V, T_A = 25°C (unless otherwise noted)

PARAMETER		TEST CONDITIONS		TLC27M4Y			UNIT
				MIN	TYP	MAX	
V_{IO}	Input offset voltage	V_O = 1.4 V, R_S = 50 Ω,	V_{IC} = 0, R_L = 100 kΩ		1.1	10	mV
α_{VIO}	Temperature coefficient of input offset voltage	T_A = 25°C to 70°C			1.7		µV/°C
I_{IO}	Input offset current(1)	V_O = 5 V,	V_{IC} = 5 V		0.1		pA
I_{IB}	Input bias current(1)	V_O = 5 V,	V_{IC} = 5 V		0.6		pA
V_{ICR}	Common-mode input voltage range(2)			–0.2 to 9	–0.3 to 9.2		V
V_{OH}	High-level output voltage	V_{ID} = 100 mV,	R_L = 100 kΩ	8	8.7		V
V_{OL}	Low-level output voltage	V_{ID} = –100 mV,	I_{OL} = 0		0	50	mV
A_{VD}	Large-signal differential voltage amplification	V_O = 1 V to 6 V,	R_L= 100 kΩ	25	275		V/mV
CMRR	Common-mode rejection ratio	V_{IC} = V_{ICR}min		65	94		dB
k_{SVR}	Supply-voltage rejection ratio ($\Delta V_{DD}/\Delta V_{IO}$)	V_{DD} = 5 V to 10 V,	V_O = 1.4 V	70	93		dB
I_{DD}	Supply current (four amplifiers)	V_O = 5 V, No load	V_{IC} = 5 V,		570	1200	µA

(1) The typical values of input bias current and input offset current below 5 pA were determined mathematically.
(2) This range also applies to each input individually.

Copyright © 1987–2012, Texas Instruments Incorporated

OPERATING CHARACTERISTICS

at specified free-air temperature, V_{DD} = 5 V

PARAMETER		TEST CONDITIONS		T_A	TLC27M4C TLC27M4AC TLC27M4BC TLC27M9C			UNIT
					MIN	TYP	MAX	
SR	Slew rate at unity gain	R_L = 100 kΩ, C_L = 20 pF, See Figure 1	V_{IPP} = 1 V	25°C		0.43		V/μs
				0°C		0.46		
				70°C		0.36		
			V_{IPP} = 2.5 V	25°C		0.40		
				0°C		0.43		
				70°C		0.34		
V_n	Equivalent input noise voltage	f = 1 kHz, See Figure 2	R_S = 20 Ω	25°C		32		nV/√Hz
B_{OM}	Maximum output-swing bandwidth	V_O = V_{OH}, R_L = 100 kΩ,	C_L = 20 pF, See Figure 1	25°C		55		kHz
				0°C		60		
				70°C		50		
B_1	Unity-gain bandwidth	V_I = 10 mV, See Figure 3	C_L = 20 pF	25°C		525		kHz
				0°C		610		
				70°C		400		
φ_m	Phase margin	V_I = 10 mV, C_L = 20 pF,	f = B_1, See Figure 3	25°C		40°		
				0°C		41°		
				70°C		39°		

OPERATING CHARACTERISTICS

at specified free-air temperature, V_{DD} = 10 V

PARAMETER		TEST CONDITIONS		T_A	TLC27M4C TLC27M4AC TLC27M4BC TLC27M9C			UNIT
					MIN	TYP	MAX	
SR	Slew rate at unity gain	R_L = 100 kΩ, C_L = 20 pF, See Figure 1	V_{IPP} = 1 V	25°C		0.62		V/μs
				0°C		0.67		
				70°C		0.51		
			V_{IPP} = 5.5 V	25°C		0.56		
				0°C		0.61		
				70°C		0.46		
V_n	Equivalent input noise voltage	f = 1 kHz, See Figure 2	R_S = 20 Ω	25°C		32		nV/√Hz
B_{OM}	Maximum output-swing bandwidth	V_O = V_{OH}, R_L = 100 kΩ,	C_L = 20 pF, See Figure 1	25°C		35		kHz
				0°C		40		
				70°C		30		
B_1	Unity-gain bandwidth	V_I = 10 mV, See Figure 3	C_L = 20 pF	25°C		635		kHz
				0°C		710		
				70°C		510		
φ_m	Phase margin	V_I = 10 mV, C_L = 20 pF,	f = B_1, See Figure 3	25°C		43°		
				0°C		44°		
				70°C		42°		

Copyright © 1987–2012, Texas Instruments Incorporated

OPERATING CHARACTERISTICS

at specified free-air temperature, V_{DD} = 5 V

PARAMETER		TEST CONDITIONS		T_A	TLC27M4I TLC27M4AI TLC27M4BI TLC27M9I			UNIT
					MIN	TYP	MAX	
SR	Slew rate at unity gain	R_L = 100 kΩ, C_L = 20 pF, See Figure 1	V_{IPP} = 1 V	25°C		0.43		V/μs
				–40°C		0.51		
				85°C		0.35		
			V_{IPP} = 2.5 V	25°C		0.40		
				–40°C		0.48		
				85°C		0.32		
V_n	Equivalent input noise voltage	f = 1 kHz, See Figure 2	R_S = 20 Ω	25°C		32		nV/√Hz
B_{OM}	Maximum output-swing bandwidth	V_O = V_{OH}, R_L = 100 kΩ,	C_L = 20 pF, See Figure 1	25°C		55		kHz
				–40°C		75		
				85°C		45		
B_1	Unity-gain bandwidth	V_I = 10 mV, See Figure 3	C_L = 20 pF	25°C		525		kHz
				–40°C		770		
				85°C		370		
φ_m	Phase margin	V_I = 10 mV, C_L = 20 pF,	f = B_1, See Figure 3	25°C		40°		
				–40°C		43°		
				85°C		38°		

OPERATING CHARACTERISTICS

at specified free-air temperature, V_{DD} = 10 V

PARAMETER		TEST CONDITIONS		T_A	TLC27M4I TLC27M4AI TLC27M4BI TLC27M9I			UNIT
					MIN	TYP	MAX	
SR	Slew rate at unity gain	R_L = 100 kΩ, C_L = 20 pF, See Figure 1	V_{IPP} = 1 V	25°C		0.62		V/μs
				–40°C		0.77		
				85°C		0.47		
			V_{IPP} = 5.5 V	25°C		0.56		
				–40°C		0.70		
				85°C		0.44		
V_n	Equivalent input noise voltage	f = 1 kHz, See Figure 2	R_S = 20 Ω	25°C		32		nV/√Hz
B_{OM}	Maximum output-swing bandwidth	V_O = V_{OH}, R_L = 100 kΩ,	C_L = 20 pF, See Figure 1	25°C		35		kHz
				–40°C		45		
				85°C		25		
B_1	Unity-gain bandwidth	V_I = 10 mV, See Figure 3	C_L = 20 pF	25°C		635		kHz
				–40°C		880		
				85°C		480		
φ_m	Phase margin	V_I = 10 mV, C_L = 20 pF,	f = B_1, See Figure 3	25°C		43°		
				–40°C		46°		
				85°C		41°		

Copyright © 1987–2012, Texas Instruments Incorporated

OPERATING CHARACTERISTICS

at specified free-air temperature, V_{DD} = 5 V

PARAMETER		TEST CONDITIONS		T_A	TLC27M4M TLC27M9M			UNIT
					MIN	TYP	MAX	
SR	Slew rate at unity gain	R_L = 100 kΩ, C_L = 20 pF, See Figure 1	V_{IPP} = 1 V	25°C		0.43		V/μs
				–55°C		0.54		
				125°C		0.29		
			V_{IPP} = 2.5 V	25°C		0.40		
				–55°C		0.50		
				125°C		0.28		
V_n	Equivalent input noise voltage	f = 1 kHz, See Figure 2	R_S = 20 Ω	25°C		32		nV/√Hz
B_{OM}	Maximum output-swing bandwidth	$V_O = V_{OH}$, R_L = 100 kΩ,	C_L = 20 pF, See Figure 1	25°C		56		kHz
				–55°C		80		
				125°C		40		
B_1	Unity-gain bandwidth	V_I = 10 mV, See Figure 3	C_L = 20 pF	25°C		525		kHz
				–55°C		850		
				125°C		330		
φ_m	Phase margin	V_I = 10 mV, C_L = 20 pF,	f = B_1, See Figure 3	25°C		40°		
				–55°C		44°		
				125°C		36°		

OPERATING CHARACTERISTICS

at specified free-air temperature, V_{DD} = 10 V

PARAMETER		TEST CONDITIONS		T_A	TLC27M4M TLC27M9M			UNIT
					MIN	TYP	MAX	
SR	Slew rate at unity gain	R_L = 100 kΩ, C_L = 20 pF, See Figure 1	V_{IPP} = 1 V	25°C		0.62		V/μs
				–55°C		0.81		
				125°C		0.38		
			V_{IPP} = 5.5 V	25°C		0.56		
				–55°C		0.73		
				125°C		0.35		
V_n	Equivalent input noise voltage	f = 1 kHz, See Figure 2	R_S = 20 Ω	25°C		32		nV/√Hz
B_{OM}	Maximum output-swing bandwidth	$V_O = V_{OH}$, R_L = 100 kΩ,	C_L = 20 pF, See Figure 1	25°C		35		kHz
				–55°C		50		
				125°C		20		
B_1	Unity-gain bandwidth	V_I = 10 mV, See Figure 3	C_L = 20 pF	25°C		635		kHz
				–55°C		960		
				125°C		440		
φ_m	Phase margin	V_I = 10 mV, C_L = 20 pF,	f = B_1, See Figure 3	25°C		43°		
				–55°C		47°		
				125°C		39°		

Copyright © 1987–2012, Texas Instruments Incorporated

OPERATING CHARACTERISTICS

at specified free-air temperature, V_{DD} = 5 V, T_A = 25°C

PARAMETER		TEST CONDITIONS		TLC27M4Y			UNIT
				MIN	TYP	MAX	
SR	Slew rate at unity gain	R_L = 100 kΩ, C_L = 20 pF, See Figure 1	V_{IPP} = 1 V		0.43		V/µs
			V_{IPP} = 2.5 V		0.40		
V_n	Equivalent input noise voltage	f = 1 kHz, See Figure 2	R_S = 20 Ω		32		nV/√Hz
B_{OM}	Maximum output-swing bandwidth	V_O = V_{OH}, R_L = 100 kΩ,	C_L = 20 pF, See Figure 1		55		kHz
B_1	Unity-gain bandwidth	V_I = 10 mV, See Figure 3	C_L = 20 pF		525		kHz
φ_m	Phase margin	V_I = 10 mV, C_L = 20 pF,	f = B_1, See Figure 3		40°		

OPERATING CHARACTERISTICS

at specified free-air temperature, V_{DD} = 10 V, T_A = 25°C

PARAMETER		TEST CONDITIONS		TLC27M4Y			UNIT
				MIN	TYP	MAX	
SR	Slew rate at unity gain	R_L = 100 kΩ, C_L = 20 pF, See Figure 1	V_{IPP} = 1 V		0.62		V/µs
			V_{IPP} = 5.5 V		0.56		
V_n	Equivalent input noise voltage	f = 1 kHz, See Figure 2	R_S = 20 Ω		32		nV/√Hz
B_{OM}	Maximum output-swing bandwidth	V_O = V_{OH}, R_L = 100 kΩ,	C_L = 20 pF, See Figure 1		35		kHz
B_1	Unity-gain bandwidth	V_I = 10 mV, See Figure 3	C_L = 20 pF		635		kHz
φ_m	Phase margin	V_I = 10 mV, C_L = 20 pF,	f = B_1, See Figure 3		43°		

Copyright © 1987–2012, Texas Instruments Incorporated

PARAMETER MEASUREMENT INFORMATION

Single-Supply versus Split-Supply Test Circuits

Because the TLC27M4 and TLC27M9 are optimized for single-supply operation, circuit configurations used for the various tests often present some inconvenience since the input signal, in many cases, must be offset from ground. This inconvenience can be avoided by testing the device with split supplies and the output load tied to the negative rail. A comparison of single-supply versus split-supply test circuits is shown below. The use of either circuit gives the same result.



Figure 1. Unity-Gain Amplifier



Figure 2. Noise-Test Circuit



Figure 3. Gain-of-100 Inverting Amplifier

Copyright © 1987–2012, Texas Instruments Incorporated

PARAMETER MEASUREMENT INFORMATION (continued)

Input Bias Current

Because of the high input impedance of the TLC27M4 and TLC27M9 operational amplifiers, attempts to measure the input bias current can result in erroneous readings. The bias current at normal room ambient temperature is typically less than 1 pA, a value that is easily exceeded by leakages on the test socket. Two suggestions are offered to avoid erroneous measurements:

1. Isolate the device from other potential leakage sources. Use a grounded shield around and between the device inputs (see Figure 4). Leakages that would otherwise flow to the inputs are shunted away.
2. Compensate for the leakage of the test socket by actually performing an input bias current test (using a picoammeter) with no device in the test socket. The actual input bias current can then be calculated by subtracting the open-socket leakage readings from the readings obtained with a device in the test socket.

One word of caution—many automatic testers as well as some bench-top operational amplifier testers use the servo-loop technique with a resistor in series with the device input to measure the input bias current; the voltage drop across the series resistor is measured and the bias current is calculated. This method requires that a device be inserted into the test socket to obtain a correct reading; therefore, an open-socket reading is not feasible using this method.



Figure 4. Isolation Metal Around Device Inputs (J and N packages)

Low-Level Output Voltage

To obtain low-supply-voltage operation, some compromise was necessary in the input stage. This compromise results in the device low-level output being dependent on both the common-mode input voltage level as well as the differential input voltage level. When attempting to correlate low-level output readings with those quoted in the electrical specifications, these two conditions should be observed. If conditions other than these are to be used, please refer to Figure 14 through Figure 19 in the *Typical Characteristics* of this data sheet.

Input Offset Voltage Temperature Coefficient

Erroneous readings often result from attempts to measure temperature coefficient of input offset voltage. This parameter is actually a calculation using input offset voltage measurements obtained at two different temperatures. When one (or both) of the temperatures is below freezing, moisture can collect on both the device and the test socket. This moisture results in leakage and contact resistance, which can cause erroneous input offset voltage readings. The isolation techniques previously mentioned have no effect on the leakage since the moisture also covers the isolation metal itself, thereby rendering it useless. It is suggested that these measurements be performed at temperatures above freezing to minimize error.

Copyright © 1987–2012, Texas Instruments Incorporated

PARAMETER MEASUREMENT INFORMATION (continued)

Full-Power Response

Full-power response, the frequency above which the operational amplifier slew rate limits the output voltage swing, is often specified two ways: full-linear response and full-peak response. The full-linear response is generally measured by monitoring the distortion level of the output, while increasing the frequency of a sinusoidal input signal until the maximum frequency is found above which the output contains significant distortion. The full-peak response is defined as the maximum output frequency, without regard to distortion, above which full peak-to-peak output swing cannot be maintained.

Because there is no industry-wide accepted value for significant distortion, the full-peak response is specified in this data sheet and is measured using the circuit of Figure 1. The initial setup involves the use of a sinusoidal input to determine the maximum peak-to-peak output of the device (the amplitude of the sinusoidal wave is increased until clipping occurs). The sinusoidal wave is then replaced with a square wave of the same amplitude. The frequency is then increased until the maximum peak-to-peak output can no longer be maintained (Figure 5). A square wave is used to allow a more accurate determination of the point at which the maximum peak-to-peak output is reached.



(a) f = 1 kHz (b) 1 kHz < f < B_{OM} (c) f = B_{OM} (d) f > B_{OM}

Figure 5. Full-Power-Response Output Signal

Test Time

Inadequate test time is a frequent problem, especially when testing CMOS devices in a high-volume, short-test-time environment. Internal capacitances are inherently higher in CMOS than in bipolar and BiFET devices and require longer test times than their bipolar and BiFET counterparts. The problem becomes more pronounced with reduced supply levels and lower temperatures.

Copyright © 1987–2012, Texas Instruments Incorporated

TYPICAL CHARACTERISTICS

Table of Graphs

			FIGURE
V_{IO}	Input offset voltage	Distribution	6, 7
α_{VIO}	Temperature coefficient of input offset voltage	Distribution	8, 9
V_{OH}	High-level output voltage	vs High-level output current vs Supply voltage vs Free-air temperature	10, 11 12 13
V_{OL}	Low-level output voltage	vs Common-mode input voltage vs Differential input voltage vs Free-air temperature vs Low-level output current	14, 15 16 17 18, 19
A_{VD}	Differential voltage amplification	vs Supply voltage vs Free-air temperature Free vs Frequency	20 21 32, 33
I_{IB}	Input bias current	vs Free-air temperature	22
I_{IO}	Input offset current	vs Free-air temperature	22
V_{IC}	Common-mode input voltage	vs Supply voltage	23
I_{DD}	Supply current	vs Supply voltage vs Free-air temperature	24 25
SR	Slew rate	vs Supply voltage vs Free-air temperature	26 27
	Normalized slew rate	vs Free-air temperature	28
$V_{O(PP)}$	Maximum peak-to-peak output voltage	vs Frequency	29
B_1	Unity gain bandwidth	vs Free-air temperature Free vs Supply voltage	30 31
	Phase shift	vs Frequency	32, 33
φ_m	Phase margin	vs Supply voltage vs Free-air temperature Free vs Load capacitance	34 35 36
Vn	Equivalent input noise voltage	vs Frequency	37

Copyright © 1987–2012, Texas Instruments Incorporated

TYPICAL CHARACTERISTICS



Figure 6.



Figure 7.



Figure 8.



Figure 9.

TYPICAL CHARACTERISTICS (1)

HIGH-LEVEL OUTPUT VOLTAGE vs HIGH-LEVEL OUTPUT CURRENT



Figure 10.

HIGH-LEVEL OUTPUT VOLTAGE vs HIGH-LEVEL OUTPUT CURRENT



Figure 11.

HIGH-LEVEL OUTPUT VOLTAGE vs SUPPLY VOLTAGE



Figure 12.

HIGH-LEVEL OUTPUT VOLTAGE vs FREE-AIR TEMPERATURE



Figure 13.

(1) Data at high and low temperatures are applicable only within the rated operating free-air temperature ranges of the various devices.

Copyright © 1987–2012, Texas Instruments Incorporated

TYPICAL CHARACTERISTICS (1)



Figure 14.



Figure 15.



Figure 16.



Figure 17.

(1) Data at high and low temperatures are applicable only within the rated operating free-air temperature ranges of the various devices.

Copyright © 1987–2012, Texas Instruments Incorporated

TYPICAL CHARACTERISTICS (1)

LOW-LEVEL OUTPUT VOLTAGE
vs
LOW-LEVEL OUTPUT CURRENT



Figure 18.

LOW-LEVEL OUTPUT VOLTAGE
vs
LOW-LEVEL OUTPUT CURRENT



Figure 19.

LARGE-SIGNAL
DIFFERENTIAL VOLTAGE AMPLIFICATION
vs
SUPPLY VOLTAGE



Figure 20.

LARGE-SIGNAL
DIFFERENTIAL VOLTAGE AMPLIFICATION
vs
FREE-AIR TEMPERATURE



Figure 21.

(1) Data at high and low temperatures are applicable only within the rated operating free-air temperature ranges of the various devices.

Copyright © 1987–2012, Texas Instruments Incorporated

TYPICAL CHARACTERISTICS (1)

INPUT BIAS CURRENT AND INPUT OFFSET CURRENT vs FREE-AIR TEMPERATURE



NOTE A: The typical values of input bias current and input offset current below 5 pA were determined mathematically.

Figure 22.

COMMON-MODE INPUT VOLTAGE POSITIVE LIMIT vs SUPPLY VOLTAGE



Figure 23.

SUPPLY CURRENT vs SUPPLY VOLTAGE



Figure 24.

SUPPLY CURRENT vs FREE-AIR TEMPERATURE



Figure 25.

(1) Data at high and low temperatures are applicable only within the rated operating free-air temperature ranges of the various devices.

Copyright © 1987–2012, Texas Instruments Incorporated

TYPICAL CHARACTERISTICS (1)

SLEW RATE
vs
SUPPLY VOLTAGE



Figure 26.

SLEW RATE
vs
FREE-AIR TEMPERATURE



Figure 27.

NORMALIZED SLEW RATE
vs
FREE-AIR TEMPERATURE



Figure 28.

MAXIMUM PEAK-TO-PEAK OUTPUT VOLTAGE
vs
FREQUENCY



Figure 29.

(1) Data at high and low temperatures are applicable only within the rated operating free-air temperature ranges of the various devices.

Copyright © 1987–2012, Texas Instruments Incorporated

TYPICAL CHARACTERISTICS (1)



Figure 30.



Figure 31.



Figure 32.

(1) Data at high and low temperatures are applicable only within the rated operating free-air temperature ranges of the various devices.

TYPICAL CHARACTERISTICS (1)



Figure 33.



Figure 34.



Figure 35.

(1) Data at high and low temperatures are applicable only within the rated operating free-air temperature ranges of the various devices.

Copyright © 1987–2012, Texas Instruments Incorporated

TYPICAL CHARACTERISTICS



Figure 36.



Figure 37.

APPLICATION INFORMATION

Single-Supply Operation

While the TLC27M4 and TLC27M9 perform well using dual power supplies (also called balanced or split supplies), the design is optimized for single-supply operation. This design includes an input common-mode voltage range that encompasses ground as well as an output voltage range that pulls down to ground. The supply voltage range extends down to 3 V (C-suffix types), thus allowing operation with supply levels commonly available for TTL and HCMOS; however, for maximum dynamic range, 16-V single-supply operation is recommended.

Many single-supply applications require that a voltage be applied to one input to establish a reference level that is above ground. A resistive voltage divider is usually sufficient to establish this reference level (see Figure 38). The low input bias current of the TLC27M4 and TLC27M9 permits the use of very large resistive values to implement the voltage divider, thus minimizing power consumption.

The TLC27M4 and TLC27M9 work well in conjunction with digital logic; however, when powering both linear devices and digital logic from the same power supply, the following precautions are recommended:

1. Power the linear devices from separate bypassed supply lines (see Figure 39); otherwise, the linear device supply rails can fluctuate due to voltage drops caused by high switching currents in the digital logic.
2. Use proper bypass techniques to reduce the probability of noise-induced errors. Single capacitive decoupling is often adequate; however, high-frequency applications may require RC decoupling.



$$V_{REF} = V_{DD} \frac{R3}{R1 + R3}$$

$$V_O = (V_{REF} - V_I) \frac{R4}{R2} + V_{REF}$$

Figure 38. Inverting Amplifier With Voltage Reference



Figure 39. Common Versus Separate Supply Rails

Copyright © 1987–2012, Texas Instruments Incorporated

Input Characteristics

The TLC27M4 and TLC27M9 are specified with a minimum and a maximum input voltage that, if exceeded at either input, could cause the device to malfunction. Exceeding this specified range is a common problem, especially in single-supply operation. Note that the lower range limit includes the negative rail, while the upper range limit is specified at V_{DD} – 1 V at T_A = 25°C and at V_{DD} – 1.5 V at all other temperatures.

The use of the polysilicon-gate process and the careful input circuit design gives the TLC27M4 and TLC27M9 very good input offset voltage drift characteristics relative to conventional metal-gate processes. Offset voltage drift in CMOS devices is highly influenced by threshold voltage shifts caused by polarization of the phosphorus dopant implanted in the oxide. Placing the phosphorus dopant in a conductor (such as a polysilicon gate) alleviates the polarization problem, thus reducing threshold voltage shifts by more than an order of magnitude. The offset voltage drift with time has been calculated to be typically 0.1 µV/month, including the first month of operation.

Because of the extremely high input impedance and resulting low bias current requirements, the TLC27M4 and TLC27M9 are well suited for low-level signal processing; however, leakage currents on printed-circuit boards and sockets can easily exceed bias current requirements and cause a degradation in device performance. It is good practice to include guard rings around inputs (similar to those of Figure 4 in the *Parameter Measurement Information* section). These guards should be driven from a low-impedance source at the same voltage level as the common-mode input (see Figure 40).

Unused amplifiers should be connected as unity-gain followers to avoid possible oscillation.

Noise Performance

The noise specifications in operational amplifier circuits are greatly dependent on the current in the first-stage differential amplifier. The low input bias current requirements of the TLC27M4 and TLC27M9 result in a very low noise current, which is insignificant in most applications. This feature makes the devices especially favorable over bipolar devices when using values of circuit impedance greater than 50 kΩ, since bipolar devices exhibit greater noise currents.



(a) NONINVERTING AMPLIFIER (b) INVERTING AMPLIFIER (c) UNITY-GAIN AMPLIFIER

Figure 40. Guard-Ring Schemes

Output Characteristics

The output stage of the TLC27M4 and TLC27M9 is designed to sink and source relatively high amounts of current (see *typical characteristics*). If the output is subjected to a short-circuit condition, this high current capability can cause device damage under certain conditions. Output current capability increases with supply voltage.

All operating characteristics of the TLC27M4 and TLC27M9 were measured using a 20-pF load. The devices drive higher capacitive loads; however, as output load capacitance increases, the resulting response pole occurs at lower frequencies, thereby causing ringing, peaking, or even oscillation (see Figure 41). In many cases, adding a small amount of resistance in series with the load capacitance alleviates the problem.



(a) C_L = 20 pF, R_L = NO LOAD



(b) C_L = 170 pF, R_L = NO LOAD



(c) C_L = 190 pF, R_L = NO LOAD



(d) TEST CIRCUIT

Figure 41. Effect of Capacitive Loads and Test Circuit

Although the TLC27M4 and TLC27M9 possess excellent high-level output voltage and current capability, methods for boosting this capability are available, if needed. The simplest method involves the use of a pullup resistor (RP) connected from the output to the positive supply rail (see Figure 42). There are two disadvantages to the use of this circuit. First, the NMOS pulldown transistor N4 (see equivalent schematic) must sink a comparatively large amount of current. In this circuit, N4 behaves like a linear resistor with an on-resistance between approximately 60 Ω and 180 Ω, depending on how hard the operational amplifier input is driven. With very low values of RP, a voltage offset from 0 V at the output occurs. Second, pullup resistor RP acts as a drain load to N4 and the gain of the operational amplifier is reduced at output voltage levels where N5 is not supplying the output current.

Copyright © 1987–2012, Texas Instruments Incorporated



Figure 42. Resistive Pullup to Increase V_{OH}



Figure 43. Compensation for Input Capacitance

Feedback

Operational amplifier circuits nearly always employ feedback, and since feedback is the first prerequisite for oscillation, some caution is appropriate. Most oscillation problems result from driving capacitive loads (discussed previously) and ignoring stray input capacitance. A small-value capacitor connected in parallel with the feedback resistor is an effective remedy (see Figure 43). The value of this capacitor is optimized empirically.

Electrostatic Discharge Protection

The TLC27M4 and TLC27M9 incorporate an internal electrostatic discharge (ESD) protection circuit that prevents functional failures at voltages up to 2000 V as tested under MIL-STD-883C, Method 3015.2. Care should be exercised, however, when handling these devices, as exposure to ESD may result in the degradation of the device parametric performance. The protection circuit also causes the input bias currents to be temperature-dependent and have the characteristics of a reverse-biased diode.

Latch-Up

Because CMOS devices are susceptible to latch-up due to their inherent parasitic thyristors, the TLC27M4 and TLC27M9 inputs and outputs were designed to withstand —100-mA surge currents without sustaining latch-up; however, techniques should be used to reduce the chance of latch-up whenever possible. Internal protection diodes should not, by design, be forward biased. Applied input and output voltage should not exceed the supply voltage by more than 300 mV. Care should be exercised when using capacitive coupling on pulse generators. Supply transients should be shunted by the use of decoupling capacitors (0.1 μF typical) located across the supply rails as close to the device as possible.

The current path established if latch-up occurs is usually between the positive supply rail and ground; it can be triggered by surges on the supply lines and/or voltages on either the output or inputs that exceed the supply voltage. Once latch-up occurs, the current flow is limited only by the impedance of the power supply and the forward resistance of the parasitic thyristor and usually results in the destruction of the device. The chance of latch-up occurring increases with increasing temperature and supply voltages.

Copyright © 1987–2012, Texas Instruments Incorporated



NOTE: $V_{OPP} \approx 2$ V

$$f_O = \frac{1}{2\pi \sqrt{R1R2C1C2}}$$

Figure 44. Wien Oscillator

Copyright © 1987–2012, Texas Instruments Incorporated



NOTE: V_I = 0 V to 3 V

$$I_S = \frac{V_I}{R}$$

Figure 45. Precision Low-Current Sink



NOTE A: Low to medium impedance dynamic mike

Figure 46. Microphone Preamplifier



NOTE: V_{DD} = 4 V to 15 V
V_{REF} = 0 V to V_{DD} – 2 V

Figure 47. Photo-Diode Amplifier With Ambient Light Rejection



NOTE: V_{DD} = 8 V to 16 V
V_O = 5 V, 10 mA

Figure 48. Low-Power Voltage Regulator



Figure 49. Single-Rail AC Amplifier

Copyright © 1987–2012, Texas Instruments Incorporated

PACKAGING INFORMATION

Orderable part number	Status (1)	Material type (2)	Package | Pins	Package qty | Carrier	RoHS (3)	Lead finish/ Ball material (4)	MSL rating/ Peak reflow (5)	Op temp (°C)	Part marking (6)
TLC27M4ACD	Obsolete	Production	SOIC (D) | 14	-	-	Call TI	Call TI	0 to 70	27M4AC
TLC27M4ACDR	Active	Production	SOIC (D) | 14	2500 | LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	0 to 70	27M4AC
TLC27M4ACDR.A	Active	Production	SOIC (D) | 14	2500 | LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	0 to 70	27M4AC
TLC27M4ACDR.B	Active	Production	SOIC (D) | 14	2500 | LARGE T&R	-	Call TI	Call TI	-40 to 85	
TLC27M4ACN	Active	Production	PDIP (N) | 14	25 | TUBE	Yes	NIPDAU	N/A for Pkg Type	0 to 70	TLC27M4ACN
TLC27M4ACN.A	Active	Production	PDIP (N) | 14	25 | TUBE	Yes	NIPDAU	N/A for Pkg Type	0 to 70	TLC27M4ACN
TLC27M4ACNE4	Active	Production	PDIP (N) | 14	25 | TUBE	Yes	NIPDAU	N/A for Pkg Type	0 to 70	TLC27M4ACN
TLC27M4AID	Obsolete	Production	SOIC (D) | 14	-	-	Call TI	Call TI	-40 to 85	27M4AI
TLC27M4AIDR	Active	Production	SOIC (D) | 14	2500 | LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 85	27M4AI
TLC27M4AIDR.A	Active	Production	SOIC (D) | 14	2500 | LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 85	27M4AI
TLC27M4AIN	Active	Production	PDIP (N) | 14	25 | TUBE	Yes	NIPDAU	N/A for Pkg Type	-40 to 85	TLC27M4AIN
TLC27M4AIN.A	Active	Production	PDIP (N) | 14	25 | TUBE	Yes	NIPDAU	N/A for Pkg Type	-40 to 85	TLC27M4AIN
TLC27M4BCD	Obsolete	Production	SOIC (D) | 14	-	-	Call TI	Call TI	0 to 70	27M4BC
TLC27M4BCDR	Active	Production	SOIC (D) | 14	2500 | LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	0 to 70	27M4BC
TLC27M4BCDR.A	Active	Production	SOIC (D) | 14	2500 | LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	0 to 70	27M4BC
TLC27M4BCN	Active	Production	PDIP (N) | 14	25 | TUBE	Yes	NIPDAU	N/A for Pkg Type	0 to 70	TLC27M4BCN
TLC27M4BCN.A	Active	Production	PDIP (N) | 14	25 | TUBE	Yes	NIPDAU	N/A for Pkg Type	0 to 70	TLC27M4BCN
TLC27M4BID	Obsolete	Production	SOIC (D) | 14	-	-	Call TI	Call TI	-40 to 85	27M4BI
TLC27M4BIDR	Active	Production	SOIC (D) | 14	2500 | LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 85	27M4BI
TLC27M4BIDR.A	Active	Production	SOIC (D) | 14	2500 | LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 85	27M4BI
TLC27M4BIN	Active	Production	PDIP (N) | 14	25 | TUBE	Yes	NIPDAU	N/A for Pkg Type	-40 to 85	TLC27M4BIN
TLC27M4BIN.A	Active	Production	PDIP (N) | 14	25 | TUBE	Yes	NIPDAU	N/A for Pkg Type	-40 to 85	TLC27M4BIN
TLC27M4CD	Obsolete	Production	SOIC (D) | 14	-	-	Call TI	Call TI	0 to 70	TLC27M4C
TLC27M4CDR	Active	Production	SOIC (D) | 14	2500 | LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	0 to 70	TLC27M4C
TLC27M4CDR.A	Active	Production	SOIC (D) | 14	2500 | LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	0 to 70	TLC27M4C
TLC27M4CDR.B	Active	Production	SOIC (D) | 14	2500 | LARGE T&R	-	Call TI	Call TI	-40 to 85	
TLC27M4CDRG4	Active	Production	SOIC (D) | 14	2500 | LARGE T&R	-	Call TI	Call TI	0 to 70	
TLC27M4CN	Active	Production	PDIP (N) | 14	25 | TUBE	Yes	NIPDAU	N/A for Pkg Type	0 to 70	TLC27M4CN
TLC27M4CN.A	Active	Production	PDIP (N) | 14	25 | TUBE	Yes	NIPDAU	N/A for Pkg Type	0 to 70	TLC27M4CN

Orderable part number	Status (1)	Material type (2)	Package | Pins	Package qty | Carrier	RoHS (3)	Lead finish/ Ball material (4)	MSL rating/ Peak reflow (5)	Op temp (°C)	Part marking (6)
TLC27M4CNS	Active	Production	SOP (NS) | 14	50 | TUBE	Yes	NIPDAU	Level-1-260C-UNLIM	0 to 70	TLC27M4
TLC27M4CNS.A	Active	Production	SOP (NS) | 14	50 | TUBE	Yes	NIPDAU	Level-1-260C-UNLIM	0 to 70	TLC27M4
TLC27M4CNSR	Active	Production	SOP (NS) | 14	2000 | LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	0 to 70	TLC27M4
TLC27M4CNSR.A	Active	Production	SOP (NS) | 14	2000 | LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	0 to 70	TLC27M4
TLC27M4CPWR	Active	Production	TSSOP (PW) | 14	2000 | LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	0 to 70	P27M4
TLC27M4CPWR.A	Active	Production	TSSOP (PW) | 14	2000 | LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	0 to 70	P27M4
TLC27M4ID	Obsolete	Production	SOIC (D) | 14	-	-	Call TI	Call TI	-40 to 85	TLC27M4I
TLC27M4IDR	Active	Production	SOIC (D) | 14	2500 | LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 85	TLC27M4I
TLC27M4IDR.A	Active	Production	SOIC (D) | 14	2500 | LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 85	TLC27M4I
TLC27M4IDR1G4	Active	Production	SOIC (D) | 14	2500 | LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 85	TLC27M4I
TLC27M4IDR1G4.A	Active	Production	SOIC (D) | 14	2500 | LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 85	TLC27M4I
TLC27M4IDRG4	Active	Production	SOIC (D) | 14	2500 | LARGE T&R	-	Call TI	Call TI	-40 to 85	
TLC27M4IN	Active	Production	PDIP (N) | 14	25 | TUBE	Yes	NIPDAU	N/A for Pkg Type	-40 to 85	TLC27M4IN
TLC27M4IN.A	Active	Production	PDIP (N) | 14	25 | TUBE	Yes	NIPDAU	N/A for Pkg Type	-40 to 85	TLC27M4IN
TLC27M4IPW	Obsolete	Production	TSSOP (PW) | 14	-	-	Call TI	Call TI	-40 to 85	P27M4I
TLC27M4IPWR	Active	Production	TSSOP (PW) | 14	2000 | LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 85	P27M4I
TLC27M4IPWR.A	Active	Production	TSSOP (PW) | 14	2000 | LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 85	P27M4I
TLC27M9CD	Obsolete	Production	SOIC (D) | 14	-	-	Call TI	Call TI	0 to 70	TLC27M9C
TLC27M9CDR	Active	Production	SOIC (D) | 14	2500 | LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	0 to 70	TLC27M9C
TLC27M9CDR.A	Active	Production	SOIC (D) | 14	2500 | LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	0 to 70	TLC27M9C
TLC27M9CDRG4	Active	Production	SOIC (D) | 14	2500 | LARGE T&R	-	Call TI	Call TI	0 to 70	
TLC27M9CN	Active	Production	PDIP (N) | 14	25 | TUBE	Yes	NIPDAU	N/A for Pkg Type	0 to 70	TLC27M9CN
TLC27M9CN.A	Active	Production	PDIP (N) | 14	25 | TUBE	Yes	NIPDAU	N/A for Pkg Type	0 to 70	TLC27M9CN
TLC27M9ID	Obsolete	Production	SOIC (D) | 14	-	-	Call TI	Call TI	-40 to 85	TLC27M9I
TLC27M9IDR	Active	Production	SOIC (D) | 14	2500 | LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 85	TLC27M9I
TLC27M9IDR.A	Active	Production	SOIC (D) | 14	2500 | LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 85	TLC27M9I
TLC27M9IN	Active	Production	PDIP (N) | 14	25 | TUBE	Yes	NIPDAU	N/A for Pkg Type	-40 to 85	TLC27M9IN
TLC27M9IN.A	Active	Production	PDIP (N) | 14	25 | TUBE	Yes	NIPDAU	N/A for Pkg Type	-40 to 85	TLC27M9IN

(1) **Status:** For more details on status, see our product life cycle.

(2) Material type: When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

(3) RoHS values: Yes, No, RoHS Exempt. See the TI RoHS Statement for additional information and value definition.

(4) Lead finish/Ball material: Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

(5) MSL rating/Peak reflow: The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

(6) Part marking: There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

TAPE AND REEL INFORMATION

REEL DIMENSIONS



TAPE DIMENSIONS



A0	Dimension designed to accommodate the component width
B0	Dimension designed to accommodate the component length
K0	Dimension designed to accommodate the component thickness
W	Overall width of the carrier tape
P1	Pitch between successive cavity centers

QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
TLC27M4ACDR	SOIC	D	14	2500	330.0	16.4	6.5	9.0	2.1	8.0	16.0	Q1
TLC27M4AIDR	SOIC	D	14	2500	330.0	16.4	6.5	9.0	2.1	8.0	16.0	Q1
TLC27M4BCDR	SOIC	D	14	2500	330.0	16.4	6.5	9.0	2.1	8.0	16.0	Q1
TLC27M4BIDR	SOIC	D	14	2500	330.0	16.4	6.5	9.0	2.1	8.0	16.0	Q1
TLC27M4CDR	SOIC	D	14	2500	330.0	16.4	6.5	9.0	2.1	8.0	16.0	Q1
TLC27M4CNSR	SOP	NS	14	2000	330.0	16.4	8.1	10.4	2.5	12.0	16.0	Q1
TLC27M4CPWR	TSSOP	PW	14	2000	330.0	12.4	6.9	5.6	1.6	8.0	12.0	Q1
TLC27M4CPWR	TSSOP	PW	14	2000	330.0	12.4	6.9	5.6	1.6	8.0	12.0	Q1
TLC27M4IDR	SOIC	D	14	2500	330.0	16.4	6.5	9.0	2.1	8.0	16.0	Q1
TLC27M4IDR1G4	SOIC	D	14	2500	330.0	16.4	6.5	9.0	2.1	8.0	16.0	Q1
TLC27M4IPWR	TSSOP	PW	14	2000	330.0	12.4	6.9	5.6	1.6	8.0	12.0	Q1
TLC27M4IPWR	TSSOP	PW	14	2000	330.0	12.4	6.9	5.6	1.6	8.0	12.0	Q1
TLC27M9CDR	SOIC	D	14	2500	330.0	16.4	6.5	9.0	2.1	8.0	16.0	Q1
TLC27M9IDR	SOIC	D	14	2500	330.0	16.4	6.5	9.0	2.1	8.0	16.0	Q1

TAPE AND REEL BOX DIMENSIONS



*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
TLC27M4ACDR	SOIC	D	14	2500	353.0	353.0	32.0
TLC27M4AIDR	SOIC	D	14	2500	353.0	353.0	32.0
TLC27M4BCDR	SOIC	D	14	2500	353.0	353.0	32.0
TLC27M4BIDR	SOIC	D	14	2500	353.0	353.0	32.0
TLC27M4CDR	SOIC	D	14	2500	353.0	353.0	32.0
TLC27M4CNSR	SOP	NS	14	2000	353.0	353.0	32.0
TLC27M4CPWR	TSSOP	PW	14	2000	353.0	353.0	32.0
TLC27M4CPWR	TSSOP	PW	14	2000	353.0	353.0	32.0
TLC27M4IDR	SOIC	D	14	2500	353.0	353.0	32.0
TLC27M4IDR1G4	SOIC	D	14	2500	353.0	353.0	32.0
TLC27M4IPWR	TSSOP	PW	14	2000	353.0	353.0	32.0
TLC27M4IPWR	TSSOP	PW	14	2000	353.0	353.0	32.0
TLC27M9CDR	SOIC	D	14	2500	353.0	353.0	32.0
TLC27M9IDR	SOIC	D	14	2500	353.0	353.0	32.0

TUBE



*All dimensions are nominal

Device	Package Name	Package Type	Pins	SPQ	L (mm)	W (mm)	T (µm)	B (mm)
TLC27M4ACN	N	PDIP	14	25	506	13.97	11230	4.32
TLC27M4ACN.A	N	PDIP	14	25	506	13.97	11230	4.32
TLC27M4ACNE4	N	PDIP	14	25	506	13.97	11230	4.32
TLC27M4AIN	N	PDIP	14	25	506	13.97	11230	4.32
TLC27M4AIN.A	N	PDIP	14	25	506	13.97	11230	4.32
TLC27M4BCN	N	PDIP	14	25	506	13.97	11230	4.32
TLC27M4BCN.A	N	PDIP	14	25	506	13.97	11230	4.32
TLC27M4BIN	N	PDIP	14	25	506	13.97	11230	4.32
TLC27M4BIN.A	N	PDIP	14	25	506	13.97	11230	4.32
TLC27M4CN	N	PDIP	14	25	506	13.97	11230	4.32
TLC27M4CN.A	N	PDIP	14	25	506	13.97	11230	4.32
TLC27M4CNS	NS	SOP	14	50	530	10.5	4000	4.1
TLC27M4CNS.A	NS	SOP	14	50	530	10.5	4000	4.1
TLC27M4IN	N	PDIP	14	25	506	13.97	11230	4.32
TLC27M4IN.A	N	PDIP	14	25	506	13.97	11230	4.32
TLC27M9CN	N	PDIP	14	25	506	13.97	11230	4.32
TLC27M9CN.A	N	PDIP	14	25	506	13.97	11230	4.32
TLC27M9IN	N	PDIP	14	25	506	13.97	11230	4.32
TLC27M9IN.A	N	PDIP	14	25	506	13.97	11230	4.32



PACKAGE OUTLINE

D0014A

SOIC - 1.75 mm max height

SMALL OUTLINE INTEGRATED CIRCUIT



NOTES:

1. All linear dimensions are in millimeters. Dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm, per side.
4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.43 mm, per side.
5. Reference JEDEC registration MS-012, variation AB.



LAND PATTERN EXAMPLE
SCALE:8X



SOLDER MASK DETAILS

4220718/A 09/2016

NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.
7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

EXAMPLE STENCIL DESIGN

D0014A

SOIC - 1.75 mm max height

SMALL OUTLINE INTEGRATED CIRCUIT



SOLDER PASTE EXAMPLE
BASED ON 0.125 mm THICK STENCIL
SCALE:8X

4220718/A 09/2016

NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.

MECHANICAL DATA

NS (R-PDSO-G)** **PLASTIC SMALL-OUTLINE PACKAGE**

14-PINS SHOWN



DIM \ PINS **	14	16	20	24
A MAX	10,50	10,50	12,90	15,30
A MIN	9,90	9,90	12,30	14,70

4040062/C 03/03

NOTES:
A. All linear dimensions are in millimeters.
B. This drawing is subject to change without notice.
C. Body dimensions do not include mold flash or protrusion, not to exceed 0,15.

N (R–PDIP–T**)

PLASTIC DUAL–IN–LINE PACKAGE

16 PINS SHOWN



DIM \ PINS **	14	16	18	20
A MAX	0.775 (19,69)	0.775 (19,69)	0.920 (23,37)	1.060 (26,92)
A MIN	0.745 (18,92)	0.745 (18,92)	0.850 (21,59)	0.940 (23,88)
MS–001 VARIATION (C)	AA	BB	AC	AD



4040049/E 12/2002

NOTES:
A. All linear dimensions are in inches (millimeters).
B. This drawing is subject to change without notice.
C. Falls within JEDEC MS–001, except 18 and 20 pin minimum body length (Dim A).
D. The 20 pin end lead shoulder width is a vendor option, either half or full width.

PACKAGE OUTLINE

PW0014A

TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



NOTES:

1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm per side.
4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.25 mm per side.
5. Reference JEDEC registration MO-153.



LAND PATTERN EXAMPLE
EXPOSED METAL SHOWN
SCALE: 10X



SOLDER MASK DETAILS

4220202/B 12/2023

NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.
7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.



SOLDER PASTE EXAMPLE
BASED ON 0.125 mm THICK STENCIL
SCALE: 10X

4220202/B 12/2023

NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES “AS IS” AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI’s products are provided subject to TI’s Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI’s provision of these resources does not expand or otherwise alter TI’s applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2025, Texas Instruments Incorporated