





LOC		DIST			REVISIONS			
AA		22	P	F	ZONE	LTR	DESCRIPTION	DATE
								APPD
							D SUPERSEDED: -2; EC OUF0-0006-01	20SEP01
								DD
								LV

- 1 MATERIAL: HOUSING - PBT POLYESTER, BLACK
TERMINALS - 0.36[.014] THICK PH05-BRONZE
PLATED WITH 1.27µm[.000050] MINIMUM THICK
HARD GOLD IN LOCALIZED GOLD PLATE AREA
AND 3.81µm[.000150] MINIMUM THICK TIN-LEAD
IN SOLDER AREA OVER 1.27µm[.000050] MINIMUM
THICK NICKEL UNDERPLATE.
- 2 ALL DIMENSIONS SHOWN ARE MAXIMUM
UNLESS OTHERWISE SPECIFIED.
3. TERMINALS LOCATED IN CENTER POSITIONS.
- 4 CAVITY CONFORMS TO FCC RULES AND
REGULATIONS PART 68 AND REA BULLETIN
345-81 PE-76 SPECIFICATION FOR MODULAR
TELEPHONE HARDWARE.
- 5 BULK PACKAGED IN A TRAY.
- 6 36 ASSEMBLIES PACKAGED PER TUBE.



PRINTED CIRCUIT BOARD LAYOUT
NONCOMPONENT SIDE SHOWN



PANEL CUTOUT

SUPERSEDED BY 555979-1	6	555979-2
	5	555979-1
	PACKAGED	PART NUMBER

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON : 2 PLC DEC ± 3 PLC DEC ± ANGLES ±		DR 6-5-95 S. TUCKER	AMP AMP Incorporated Harrisburg, PA 17105-3608		
		CHK 6-5-95 B. FOX			
MATERIAL		APPD 6-5-95 J. TONEY	NAME		
		APPD 6-5-95 H. McGRATH	MODULAR JACK ASSEMBLY, SIDE ENTRY, 6 POSITION/4 CONTACTS, FLANGELESS WITHOUT PANEL STOPS		
FINISH		PRODUCT SPEC 108-1163			
		APPLICATION SPEC 114-2048	SIZE D	CAGE CODE 00779	DRAWING NO C-555979
		WEIGHT -	SCALE 4:1	SHEET 1 OF 1	

THIS DRAWING IS A CONTROLLED DOCUMENT FOR
AMP INCORPORATED. IT IS SUBJECT TO CHANGE
AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.