

**SERIES:** PDS1-M | **DESCRIPTION:** DC-DC CONVERTER

**FEATURES**

- 1 W isolated output
- smaller package
- single and dual unregulated outputs
- 1,500 Vdc isolation
- continuous short circuit protection
- extended temperature range (-40~105°C)
- antistatic protection up to 8kV
- high efficiency at light load
- efficiency up to 82%




| MODEL          | input voltage |             | output voltage<br>(Vdc) | output current |          | output power<br>max (W) | ripple and noise <sup>1</sup><br>typ (mVp-p) | efficiency<br>typ (%) |
|----------------|---------------|-------------|-------------------------|----------------|----------|-------------------------|----------------------------------------------|-----------------------|
|                | typ (Vdc)     | range (Vdc) |                         | min (mA)       | max (mA) |                         |                                              |                       |
| PDS1-S3-D5-M   | 3.3           | 2.97~3.63   | ±5                      | ±10            | ±100     | 1                       | 30                                           | 78                    |
| PDS1-S3-D12-M  | 3.3           | 2.97~3.63   | ±12                     | ±5             | ±42      | 1                       | 30                                           | 80                    |
| PDS1-S3-D15-M  | 3.3           | 2.97~3.63   | ±15                     | ±3             | ±33      | 1                       | 60                                           | 80                    |
| PDS1-S5-S5-M   | 5             | 4.5~5.5     | 5                       | 20             | 200      | 1                       | 30                                           | 80                    |
| PDS1-S5-S9-M   | 5             | 4.5~5.5     | 9                       | 12             | 111      | 1                       | 30                                           | 80                    |
| PDS1-S5-S12-M  | 5             | 4.5~5.5     | 12                      | 9              | 84       | 1                       | 30                                           | 80                    |
| PDS1-S5-S15-M  | 5             | 4.5~5.5     | 15                      | 7              | 67       | 1                       | 60                                           | 80                    |
| PDS1-S5-S24-M  | 5             | 4.5~5.5     | 24                      | 4              | 42       | 1                       | 60                                           | 80                    |
| PDS1-S5-D5-M   | 5             | 4.5~5.5     | ±5                      | ±10            | ±100     | 1                       | 30                                           | 80                    |
| PDS1-S5-D9-M   | 5             | 4.5~5.5     | ±9                      | ±6             | ±56      | 1                       | 30                                           | 80                    |
| PDS1-S5-D12-M  | 5             | 4.5~5.5     | ±12                     | ±5             | ±42      | 1                       | 30                                           | 81                    |
| PDS1-S5-D15-M  | 5             | 4.5~5.5     | ±15                     | ±3             | ±33      | 1                       | 60                                           | 81                    |
| PDS1-S5-D24-M  | 5             | 4.5~5.5     | ±24                     | ±2             | ±21      | 1                       | 60                                           | 81                    |
| PDS1-S12-S5-M  | 12            | 10.8~13.2   | 5                       | 20             | 200      | 1                       | 30                                           | 80                    |
| PDS1-S12-S9-M  | 12            | 10.8~13.2   | 9                       | 12             | 111      | 1                       | 30                                           | 80                    |
| PDS1-S12-S12-M | 12            | 10.8~13.2   | 12                      | 9              | 84       | 1                       | 30                                           | 81                    |
| PDS1-S12-S15-M | 12            | 10.8~13.2   | 15                      | 7              | 67       | 1                       | 60                                           | 81                    |
| PDS1-S12-D5-M  | 12            | 10.8~13.2   | ±5                      | ±10            | ±100     | 1                       | 30                                           | 80                    |
| PDS1-S12-D9-M  | 12            | 10.8~13.2   | ±9                      | ±6             | ±56      | 1                       | 30                                           | 80                    |
| PDS1-S12-D12-M | 12            | 10.8~13.2   | ±12                     | ±5             | ±42      | 1                       | 30                                           | 81                    |
| PDS1-S12-D15-M | 12            | 10.8~13.2   | ±15                     | ±3             | ±33      | 1                       | 60                                           | 81                    |
| PDS1-S12-D24-M | 12            | 10.8~13.2   | ±24                     | ±2             | ±21      | 1                       | 60                                           | 81                    |
| PDS1-S15-S15-M | 15            | 13.5~16.5   | 15                      | 7              | 67       | 1                       | 60                                           | 81                    |
| PDS1-S24-S5-M  | 24            | 21.6~26.4   | 5                       | 20             | 200      | 1                       | 30                                           | 80                    |
| PDS1-S24-S9-M  | 24            | 21.6~26.4   | 9                       | 11             | 110      | 1                       | 30                                           | 80                    |
| PDS1-S24-S12-M | 24            | 21.6~26.4   | 12                      | 8              | 83       | 1                       | 30                                           | 81                    |
| PDS1-S24-S15-M | 24            | 21.6~26.4   | 15                      | 7              | 67       | 1                       | 60                                           | 81                    |
| PDS1-S24-S24-M | 24            | 21.6~26.4   | 24                      | 4              | 42       | 1                       | 60                                           | 81                    |

**MODEL  
(CONTINUED)**

|                | input voltage |             | output voltage<br>(Vdc) | output current |          | output power<br>max (W) | ripple and noise <sup>1</sup><br>typ (mVp-p) | efficiency<br>typ (%) |
|----------------|---------------|-------------|-------------------------|----------------|----------|-------------------------|----------------------------------------------|-----------------------|
|                | typ (Vdc)     | range (Vdc) |                         | min (mA)       | max (mA) |                         |                                              |                       |
| PDS1-S24-D5-M  | 24            | 21.6~26.4   | ±5                      | ±10            | ±100     | 1                       | 30                                           | 82                    |
| PDS1-S24-D9-M  | 24            | 21.6~26.4   | ±9                      | ±6             | ±56      | 1                       | 30                                           | 82                    |
| PDS1-S24-D12-M | 24            | 21.6~26.4   | ±12                     | ±5             | ±42      | 1                       | 30                                           | 82                    |
| PDS1-S24-D15-M | 24            | 21.6~26.4   | ±15                     | ±3             | ±33      | 1                       | 60                                           | 82                    |
| PDS1-S24-D24-M | 24            | 21.6~26.4   | ±24                     | ±2             | ±21      | 1                       | 60                                           | 82                    |

Notes: 1. ripple and noise are measured at 20 MHz BW by "parallel cable" method

**PART NUMBER KEY****INPUT**

| parameter               | conditions/description  | min  | typ | max  | units |
|-------------------------|-------------------------|------|-----|------|-------|
| operating input voltage | 3.3 V input models      | 2.97 | 3.3 | 3.63 | Vdc   |
|                         | 5 V input models        | 4.5  | 5   | 5.5  | Vdc   |
|                         | 12 V input models       | 10.8 | 12  | 13.2 | Vdc   |
|                         | 15 V input models       | 13.5 | 15  | 16.5 | Vdc   |
|                         | 24 V input models       | 21.6 | 24  | 26.4 | Vdc   |
| surge voltage           | for maximum of 1 second |      |     |      |       |
|                         | 3.3 V input models      | -0.7 |     | 5    | Vdc   |
|                         | 5 V input models        | -0.7 |     | 9    | Vdc   |
|                         | 12 V input models       | -0.7 |     | 18   | Vdc   |
|                         | 15 V input models       | -0.7 |     | 21   | Vdc   |
|                         | 24 V input models       | -0.7 |     | 30   | Vdc   |
| filter                  | capacitance filter      |      |     |      |       |

**OUTPUT**

| parameter               | conditions/description              | min | typ | max   | units |
|-------------------------|-------------------------------------|-----|-----|-------|-------|
| line regulation         | for Vin change of 1%                |     |     | ±1.2  | %     |
| load regulation         | measured from 10% load to full load |     |     |       |       |
|                         | 5 Vdc output models                 |     | 12  |       | %     |
|                         | 9 Vdc output models                 |     | 8   |       | %     |
|                         | 12 Vdc output models                |     | 7   |       | %     |
|                         | 15 Vdc output models                |     | 6   |       | %     |
|                         | 24 Vdc output models                |     | 5   |       | %     |
| voltage accuracy        | see tolerance envelope curve        |     |     |       |       |
| switching frequency     | 100% load, nominal input voltage    |     | 100 | 300   | kHz   |
| temperature coefficient | 100% load                           |     |     | ±0.03 | %/°C  |

**PROTECTIONS**

| parameter                | conditions/description         | min | typ | max | units |
|--------------------------|--------------------------------|-----|-----|-----|-------|
| short circuit protection | continuous, automatic recovery |     |     |     |       |

## SAFETY AND COMPLIANCE


| parameter            | conditions/description                                             | min       | typ | max | units |
|----------------------|--------------------------------------------------------------------|-----------|-----|-----|-------|
| isolation voltage    | for 1 minute at 1 mA max.                                          | 1,500     |     |     | Vdc   |
| isolation resistance | at 500 Vdc                                                         | 1,000     |     |     | MΩ    |
| conducted emissions  | CISPR22/EN55022, class B (external circuit required, see Figure 1) |           |     |     |       |
| ESD                  | IEC/EN 61000-4-2, class B, contact ±8KV                            |           |     |     |       |
| MTBF                 | MIL-HDBK-217F @ 25 °C                                              | 3,500,000 |     |     | hours |
| RoHS                 | 2011/65/EU                                                         |           |     |     |       |

## ENVIRONMENTAL

| parameter             | conditions/description | min | typ | max | units |
|-----------------------|------------------------|-----|-----|-----|-------|
| operating temperature | see derating curve     | -40 |     | 105 | °C    |
| storage temperature   |                        | -55 |     | 125 | °C    |
| storage humidity      | non-condensing         |     |     | 95  | %     |
| temperature rise      | at full load           |     | 25  |     | °C    |

## SOLDERABILITY

| parameter        | conditions/description          | min | typ | max | units |
|------------------|---------------------------------|-----|-----|-----|-------|
| hand soldering   | 1.5 mm from case for 10 seconds |     |     | 300 | °C    |
| reflow soldering | see reflow soldering profile    |     |     | 245 | °C    |



## MECHANICAL

| parameter     | conditions/description                                                              | min | typ         | max | units    |
|---------------|-------------------------------------------------------------------------------------|-----|-------------|-----|----------|
| dimensions    | single output models: 12.7 x 8.30 x 7.25<br>dual output models: 15.24 x 8.30 x 7.25 |     |             |     | mm<br>mm |
| case material | epoxy resin (UL94-V0)                                                               |     |             |     |          |
| weight        | single output models<br>dual output models                                          |     | 1.52<br>1.8 |     | g<br>g   |


## MECHANICAL DRAWING

### SINGLE OUTPUT MODELS


units: mm[inch]

tolerance:  $\pm 0.25[\pm 0.010]$ pin section tolerance:  $\pm 0.10[\pm 0.004]$ 




| PIN CONNECTIONS |          |
|-----------------|----------|
| PIN             | function |
| 1               | GND      |
| 2               | Vin      |
| 4               | 0V       |
| 5               | +Vo      |
| 8               | NC       |



Top View



Front View

PCB Layout  
Top View

Side View


## MECHANICAL DRAWING

### DUAL OUTPUT MODELS


units: mm[inch]

tolerance:  $\pm 0.25[\pm 0.010]$ pin section tolerance:  $\pm 0.10[\pm 0.004]$ 


| PIN CONNECTIONS |          |
|-----------------|----------|
| PIN             | function |
| 1               | GND      |
| 2               | Vin      |
| 4               | 0V       |
| 5               | -Vo      |
| 7               | +Vo      |
| 10              | NC       |




Top View




Front View



Side View

PCB Layout  
Top View

DERATING CURVES



EMC RECOMMENDED CIRCUIT




Table 1

| Recommended external circuit components |           |       |                 |
|-----------------------------------------|-----------|-------|-----------------|
| Vin (Vdc)                               | C1        | LDM   | C2 <sup>1</sup> |
| 3.3                                     | 4.7μF/50V | 6.8μH | NC              |
| 5                                       | 4.7μF/50V | 6.8μH | NC              |
| 12                                      | 4.7μF/50V | 6.8μH | NC              |
| 15                                      | 4.7μF/50V | 6.8μH | 470pF/2kV       |
| 24                                      | 4.7μF/50V | 6.8μH | 470pF/2kV       |

Note: 1. C2 is not required for dual output models.

TEST CONFIGURATION




Table 2

| External components |                              |
|---------------------|------------------------------|
| Lin                 | 4.7μH                        |
| Cin                 | 220μF, ESR < 1.0Ω at 100 KHz |

Note: Input reflected-ripple current is measured with an inductor Lin and Capacitor Cin to simulate source impedance.

## APPLICATION NOTES

### 1. Output load requirement

To ensure this module can operate efficiently and reliably, the minimum output load may not be less than 10% of the full load during operation. If the actual output power is low, connect a resistor at the output end in parallel to increase the load.


### 2. Overload Protection

Under normal operating conditions, the output circuit of this product has no protection against overload. The simplest method to add this is to add a circuit breaker to the circuit.

### 3. Recommended circuit

If you want to further decrease the input/output ripple, you can increase the capacitance accordingly or choose capacitors with low ESR (see Figure 3 & Table 3). However, the capacitance of the output filter capacitor must be appropriate. If the capacitance is too high, a startup problem might arise. For every channel of the output, to ensure safe and reliable operation, the maximum capacitance must be less than the maximum capacitive load (see Table 4).

**Figure 3**



**Table 3**

| Vin (Vdc) | Cin (μF) | Single Vo (Vdc) | Cout (μF) | Dual Vo (Vdc) | Cout (μF) |
|-----------|----------|-----------------|-----------|---------------|-----------|
| 3.3       | 4.7      | 5               | 10        | ±5            | 4.7       |
| 5         | 4.7      | 9               | 4.7       | ±9            | 2.2       |
| 12        | 2.2      | 12              | 2.2       | ±12           | 1         |
| 15        | 2.2      | 15              | 1         | ±15           | 1         |
| 24        | 1        | 24              | 0.47      | ±24           | 0.47      |

Note: It's not recommended to connect any external capacitors in applications with less than 0.5 watt output.

**Table 4**


| Single Vout (Vdc) | Max. Capacitive Load (μF) | Dual Vout (Vdc) | Max. Capacitive Load <sup>1</sup> (μF) |
|-------------------|---------------------------|-----------------|----------------------------------------|
| 5                 | 220                       | 5               | 100                                    |
| 9                 | 220                       | 9               | 100                                    |
| 12                | 220                       | 12              | 100                                    |
| 15                | 220                       | 15              | 100                                    |
| 24                | 220                       | 24              | 100                                    |

Note: 1. For each output.

### 4. Output Voltage Regulation and Over-voltage Protection Circuit

The device for output voltage regulation, over-voltage and over-current protection is a linear regulator and a capacitor filtering network with overheat protection which can be connected to the input or output end in series (see Figure 4). The recommended capacitance of its filter capacitor (see Table 3), and the linear regulator is based on the actual voltage and current required.

**Figure 4**



Note: 1. Operation under minimum load will not damage the converter; however, they may not meet all specifications listed.  
2. Max. capacitive load tested at input voltage range and full load.  
3. All specifications measured at: Ta=25°C, humidity<75%, nominal input voltage and rated output load, unless otherwise specified.

## REVISION HISTORY

| rev. | description                | date       |
|------|----------------------------|------------|
| 1.0  | initial release            | 03/19/2013 |
| 1.01 | added PDS1-S24-S12-M model | 06/11/2013 |
| 1.02 | added dual output models   | 02/17/2014 |

The revision history provided is for informational purposes only and is believed to be accurate.

**CUI INC®**

**Headquarters**  
20050 SW 112th Ave.  
Tualatin, OR 97062  
**800.275.4899**

Fax 503.612.2383  
**cui.com**  
techsupport@cui.com

CUI offers a two (2) year limited warranty. Complete warranty information is listed on our website.

CUI reserves the right to make changes to the product at any time without notice. Information provided by CUI is believed to be accurate and reliable. However, no responsibility is assumed by CUI for its use, nor for any infringements of patents or other rights of third parties which may result from its use.

CUI products are not authorized or warranted for use as critical components in equipment that requires an extremely high level of reliability. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.