









4 CKT SHOWN



4-24 CKT



2 CKT ONLY



LEGEND

46992 - * * * 0













CIRCUIT SIZE

MATERIAL
(SEE NOTE 1)
0 = 225NS
1 = 225S
2 = 250RS
3 = 250GS
4 = 250BS
5 = 250WS

CONFIGURATION
DUAL ROW

- NOTES:
- 1) MATERIAL:
 - 225S = NYLON 6, UL94V-2, GLOW WIRE MATERIAL COLOR: BLACK
 - 225NS = NYLON 6, UL94V-2, GLOW WIRE MATERIAL COLOR: NATURAL
 - 250RS = NYLON 6/6, UL94V-0, GLOW WIRE MATERIAL COLOR: RED
 - 250GS = NYLON 6/6, UL94V-0, GLOW WIRE MATERIAL COLOR: GREEN
 - 250BS = NYLON 6/6, UL94V-0, GLOW WIRE MATERIAL COLOR: BLUE
 - 250WS = NYLON 6/6, UL94V-0, GLOW WIRE MATERIAL COLOR: NATURAL
 - 2) FINISH: NOT APPLICABLE
 - 3) PRODUCT SPECIFICATION: PS-5556-001
 - 4) PACKAGING: BULK
 - 5) PART MATES WITH MOLEX PLUG #46993 AND HEADERS #172447, #172448.
 - 6) PART TO BE USED WITH MOLEX FEMALE TERMINAL #5556,#45750,#46018.
 - 7) PART IS NOT DESIGNED FOR CURRENT SHARING.
 - 8) CONNECTORS ARE NOT TO BE MATED OR UNMATED WHILE CIRCUITS ARE LIVE.
 - 9) WIRES ARE TO BE DRESSED IN SUCH A MANNER TO ALLOW THE TERMINALS TO FLOAT FREELY IN THE POCKET.
 - 10) PART CONFORMS TO CLASS "B" REQUIREMENTS OF COSMETIC SPECIFICATION PS-45499-002 WITH THE EXCEPTION OF DISCOLORATION, FLASH AND SINK MEET CLASS "C" REQUIREMENTS.
△11 TO BE MEASURED AT SURFACE Z
 - 12) TEXT ON PART IS FOR REFERENCE ONLY. TEXT AND TEXT LOCATION MAY VARY DEPENDING ON PART NUMBER AND/OR TOOL.
 - 13) APPLICATION SPECIFICATION :469920000-AS.
 - 14) BUBBLE IS ACCEPTABLE ON LATCH AREA.

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION													
DIMENSION UNITS		SCALE		CURRENT REV DESC:				molex					
mm NTS													
GENERAL TOLERANCES (UNLESS SPECIFIED)				MINIFIT JR RECEPTACLE HOUSING DUAL ROW, 2-24 CKT									
										MM		INCH	
										4 PLACES ±		±	
				3 PLACES ±		± 0.01							
				2 PLACES ±		0.25 ± 0.015							
1 PLACE ±		0.38 ±		PRODUCT CUSTOMER DRAWING									
0 PLACES ±													
ANGULAR TOL ± 3.0 °				DOCUMENT NUMBER		DOC TYPE		DOC PART	REVISION				
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				SD-46992-0000		PSD		000	A10				
THIRD ANGLE PROJECTION				DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
				C-SIZE		46992		SEE TABLE		GENERAL MARKET		1 OF 2	
EC NO: 776137				2024/02/01									
DRWN: JERRYW8				2024/02/22									
CHK'D: XQZHANG				2024/02/22									
APPR: XQZHANG				2024/02/22									
INITIAL REVISION:													
DRWN: NNGUYEN				2013/04/12									
APPR: FSMITH				2014/05/16									



CIRCUIT SIZE LAYOUT
(NOT TO SCALE)

PART NUMBER		CKT SIZE	DIM "A"	DIM "B"	MATERIAL CODE & COLOR ⚠
46992-0240		02	.21/5.40	--	250BS BLUE (V0)
46992-0440		04	.38/9.60	.165/4.20	
46992-0640		06	.54/13.8	.331/8.40	
46992-0840		08	.71/18.0	.496/12.60	
46992-1040		10	.87/22.2	.661/16.8	
46992-1240		12	1.04/26.4	.827/21.00	
46992-0250		02	.21/5.40	--	250WS NATURAL (V0)
46992-0450		04	.38/9.60	.165/4.20	
46992-0650		06	.54/13.8	.331/8.40	
46992-0850		08	.71/18.0	.496/12.60	
46992-1050		10	.87/22.2	.661/16.8	
46992-1250		12	1.04/26.4	.827/21.00	

PART NUMBER		CKT SIZE	DIM "A"	DIM "B"	MATERIAL CODE & COLOR ⚠
46992-0200		02	.21/5.40	--	225NS NATURAL (V2)
46992-0400		04	.38/9.60	.165/4.20	
46992-0600		06	.54/13.8	.331/8.40	
46992-0800		08	.71/18.0	.496/12.60	
46992-1000		10	.87/22.2	.661/16.8	
46992-1200		12	1.04/26.4	.827/21.00	
46992-1400		14	1.21 / 30.6	.992/25.20	
46992-1600		16	1.37 / 34.8	1.158/29.40	
46992-1800		18	1.54 / 39.0	1.323/33.60	
46992-2000	X	20	1.70 / 43.2	1.488/37.80	
46992-2200	X	22	1.87 / 47.4	1.654/42.00	
46992-2400	X	24	2.03 / 51.6	1.819/46.20	
46992-0210		02	.21/5.40	--	225S BLACK (V2)
46992-0410		04	.38/9.60	.165/4.20	
46992-0610		06	.54/13.8	.331/8.40	
46992-0810		08	.71/18.0	.496/12.60	
46992-1010		10	.87/22.2	.661/16.8	
46992-1210		12	1.04/26.4	.827/21.00	
46992-1410		14	1.21 / 30.6	.992/25.20	
46992-1610		16	1.37 / 34.8	1.158/29.40	
46992-1810		18	1.54 / 39.0	1.323/33.60	
46992-2010	X	20	1.70 / 43.2	1.488/37.80	
46992-2210	X	22	1.87 / 47.4	1.654/42.00	
46992-2410		24	2.03 / 51.6	1.819/46.20	
46992-0220		02	.21/5.40	--	250RS RED (V0)
46992-0420		04	.38/9.60	.165/4.20	
46992-0620		06	.54/13.8	.331/8.40	
46992-0820		08	.71/18.0	.496/12.60	
46992-1020		10	.87/22.2	.661/16.8	
46992-1220		12	1.04/26.4	.827/21.00	
46992-0230		02	.21/5.40	--	250GS GREEN (V0)
46992-0430		04	.38/9.60	.165/4.20	
46992-0630		06	.54/13.8	.331/8.40	
46992-0830		08	.71/18.0	.496/12.60	
46992-1030		10	.87/22.2	.661/16.8	
46992-1230		12	1.04/26.4	.827/21.00	
X = NOT TOOLED					

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION															
DIMENSION UNITS		SCALE		CURRENT REV DESC:				molex							
mm		NTS													
GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 776137 DRWN: JERRYW8 2024/02/01 CHK'D: XQZHANG 2024/02/22 APPR: XQZHANG 2024/02/22				MINIFIT JR RECEPTACLE HOUSING DUAL ROW, 2-24 CKT							
	MM		INCH												
4 PLACES	±	±													
3 PLACES	±	± 0.01													
2 PLACES	± 0.25	± 0.015													
1 PLACE	± 0.38	±		PRODUCT CUSTOMER DRAWING				DOCUMENT NUMBER SD-46992-0000					DOC TYPE PSD	DOC PART 000	REVISION A10
0 PLACES	±	±													
ANGULAR TOL ± 3.0 °				INITIAL REVISION: DRWN: NNGUYEN 2013/04/12 APPR: FSMITH 2014/05/16											
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION 		DRAWING C-SIZE		SERIES 46992		MATERIAL NUMBER SEE TABLE		CUSTOMER GENERAL MARKET		SHEET NUMBER 2 OF 2	