

## Type HOLCO Series

### Key Features

- Ultra Precision - Down To 0.05%
- Matched Sets Available To 2ppm/°C
- High Pulse Withstand
- Low Reactance
- Low TCR - Down To 5ppm/°C
- Long Term Stability
- Up To 1 Watt At 70°C
- Released To CECC 40101 004, 030 And 804



The Holco range of Precision Metal Film Resistors meets the requirement for economically priced components for industrial and military applications. The manufacturing facility utilises closely controlled production processes including the sputter coating of metal alloy films to ceramic substrates, and laser spiralling to achieve close tolerance and high stability resistors. An epoxy coating is applied for environmental and mechanical protection. Commercially the Series is available in two case sizes, from 1 ohm to 4M ohms, tolerances from 0.05% to 1% and TCR's from 5ppm/°C to 100ppm/°C. Offered with release to BS CECC 40101 004, 030 and 804 the H8 is available via distribution.

### Characteristics - Electrical

|                           | H4P  | H4     | H8     |        |
|---------------------------|------|--------|--------|--------|
| BS CECC 40101 004         |      |        |        |        |
| Style:                    |      | K      | H      | J      |
| Power Rating at 70°C:     |      | 0.25W  | 0.063W | 0.125W |
| Temperature Rise (max):   |      | 32°C   | 14°C   | 28°C   |
| Limiting Element Voltage: |      | 250V   | 200V   | 200V   |
| BS CECC 40101 030         |      |        |        |        |
| Style:                    |      | J      | H      |        |
| Power Rating at 125°C:    |      | 0.125W | 0.1W   |        |
| Temperature Rise (max):   |      | 30°C   | 30°C   |        |
| Limiting Element Voltage: |      | 250V   | 200V   |        |
| BS CECC 40101 804         |      |        |        |        |
| Style:                    |      | B      | A      |        |
| Power Rating at 125°C:    |      | 0.25W  | 0.125W |        |
| Limiting Element Voltage: |      | 250V   | 200V   |        |
| Commercial Ratings        |      |        |        |        |
| Power Rating at 70°C:     | 1.0W | 0.5W   | 0.25W  |        |
| Temperature Rise:         | 70°C | 55°C   | 40°C   |        |
| Limiting Element Voltage: | 500V | 350V   | 350V   |        |

### General Data

|                            |                                                                                                          |
|----------------------------|----------------------------------------------------------------------------------------------------------|
| <b>Lead Material:</b>      | Solderability to BS CECC 40101 004 Para 4.15.1                                                           |
| <b>Encapsulation:</b>      | Conformal Epoxy Coating                                                                                  |
| <b>Resistor Marking:</b>   | Legend printed in accordance with CECC 40000 Para 2.4                                                    |
| <b>Solvent Resistance:</b> | The epoxy coating and print will withstand the action of all commonly used industrial cleansing solvents |

## Type HOLCO Series

### Temperature Coefficient / Tolerance Ranges

| TCR<br>ppm/°C | H4P      |            |           | H4       |            |           | H8       |            |           |
|---------------|----------|------------|-----------|----------|------------|-----------|----------|------------|-----------|
|               | 0.05%    | 0.1%-0.25% | 0.5%-1.0% | 0.05%    | 0.1%-0.25% | 0.5%-1.0% | 0.05%    | 0.1%-0.25% | 0.5%-1.0% |
| 5             | 10R-500K | 10R-500K   | 10R-500K  | 10R-500K | 10R-500K   | 10R-500K  | 10R-500K | 10R-500K   | 10R-500K  |
| 10            | 10R-1M0  | 10R-1M0    | 10R-1M0   | 10R-1M0  | 10R-1M0    | 10R-1M0   | 10R-1M0  | 10R-1M0    | 10R-1M0   |
| 15            | 10R-1M0  | 10R-1M0    | 10R-1M0   | 10R-1M0  | 10R-1M0    | 10R-1M0   | 10R-1M0  | 10R-1M0    | 10R-1M0   |
| 25            | 10R-1M0  | 10R-2M0    | 10R-2M0   | 10R-1M0  | 10R-2M0    | 10R-2M0   | 10R-1M0  | 10R-2M0    | 10R-2M0   |
| 50            | 10R-1M0  | 10R-2M0    | 10R-4M0   | 10R-1M0  | 10R-2M0    | 10R-4M0   | 10R-1M0  | 10R-2M0    | 10R-4M0   |
| 100           | 10R-1M0  | 1R0-2M0    | 1R0-4M0   | 10R-1M0  | 1R0-2M0    | 1R0-4M0   | 10R-1M0  | 1R0-2M0    | 1R0-4M0   |

### Approved Value Ranges 40101-004, 40101-030

| Type | Style<br>004 | Style<br>030 | Z<br>100ppm | C<br>50ppm | D<br>25ppm | Y<br>15ppm |
|------|--------------|--------------|-------------|------------|------------|------------|
| H4   | K            | J            | 10R-1M0     | 49R9-1M0   | 49R9-1M0   | 49R9-1M0   |
| H8   | HJ           | H            | 10R-1M0     | 49R9-1M0   | 49R9-1M0   | 49R9-1M0   |

Tolerances 0.1%, 0.25%, 0.5%, 1%

### 40101-804

| Type | Style | C<br>50ppm | D<br>25ppm | T<br>15ppm |
|------|-------|------------|------------|------------|
| H4   | B     | 49R9-1M0   | 49R9-1M0   | 49R9-1M0   |
| H8   | A     | 49R9-1M0   | 49R9-1M0   | 49R9-1M0   |

Tolerances 0.1%, 0.25%, 0.5%, 1%


### Characteristics - Electrical

|                                                                                                                          | Typical Data                       | Reference                                            |
|--------------------------------------------------------------------------------------------------------------------------|------------------------------------|------------------------------------------------------|
| Voltage Coefficient of Resistance (Between 10% and Full Rated Voltage)                                                   | Less Than 5ppm/Volt Applied        | n/a                                                  |
| Insulation Resistance at 500 Volts                                                                                       | Greater Than 10 <sup>12</sup> Ohms | n/a                                                  |
| Resistance to Soldering Heat (260°C for 10 Secs.)                                                                        | Less Than 0.05%                    | BS CECC 40101 004<br>Para 4.15.2                     |
| Short Term Overload (6.25 Times Rated BS CECC Wattage for 5 Seconds)                                                     | Less Than 0.06%                    | BS CECC 40101 004<br>Para 4.11                       |
| Ambient Temperature Range                                                                                                | -55°C to +155°C                    | BS CECC 40101 004,<br>BS CECC 40101 030 & Commercial |
| Rapid Change of Temperature (-55°C to +155°C, 5 cycles)                                                                  | Less Than 0.04%                    | BS CECC 40101 004<br>Para 4.16                       |
| Shelf Life (at Normal Room Temp.)                                                                                        | Less Than 0.05% Per Annum          | n/a                                                  |
| Vibration (10-500 HZ, Amplitude 0.75mm, or Acceleration 98m/s <sup>2</sup> which is less severe, sweep duration 6 hours) | Less Than 0.04%                    | BS CECC 40101 004<br>Para 4.19                       |
| Vibration (55-2000 Hz Simple Harmonic Motion, Max. Acceleration 98m/s <sup>2</sup> , Duration 35±5 Minutes)              | Less Than 0.04%                    | MIL STD 202<br>METHOD 204-C                          |
| Bump (390m/s <sup>2</sup> , 4000 Bumps)                                                                                  | Less Than 0.03%                    | BS 2011 Part 2.1 Eb 1977 (1984)                      |
| Load Stability                                                                                                           | See Graphs                         | n/a                                                  |
| Damp Heat Steady State                                                                                                   | See Graph                          | BS CECC 40101 004<br>Para 4.21                       |

## Type HOLCO Series


### Dimensions

To prevent damage to the components conformal coating, the leads should be adequately supported during the forming process




|                             | H4P     | H4      | H8      |
|-----------------------------|---------|---------|---------|
| Body Length (L) maximum:    | 10.0 mm | 10.0 mm | 7.20 mm |
| Body Diameter (D) maximum:  | 3.70 mm | 3.70 mm | 2.50 mm |
| Lead Diameter (d) maximum:  | 0.60 mm | 0.60 mm | 0.60 mm |
| Lead Length (l) nominal:    | 30.0 mm | 30.0 mm | 30.0 mm |
| Recommended Mounting Pitch: | 12.7 mm | 12.7 mm | 10.2 mm |
| Weight (g/100 resistors)    | 40      | 40      | 24      |


### Characteristics - Long Term Stability




**Long Term Stability**  
BS CECC 40101 004  
Ratings at 70°C  
H4 - 0.25 W  
H8 - 0.125 W



**Long Term Stability**  
BS CECC 40101 030  
Ratings at 125°C  
H4 - 0.125 W  
H8 - 0.1 W




**Long Term Stability**  
Commercial  
Ratings at 125°C  
H4P - 1W  
H4 - 0.5 W  
H8 - 0.25 W



**Damp Heat Steady State**  
93% RH at 40°C

## Type HOLCO Series

### Derating Graph - Approved and Commercial Ratings



### How to Order

| H8          | 100R                             | B         | Y           | B                                                                        |
|-------------|----------------------------------|-----------|-------------|--------------------------------------------------------------------------|
| Common Part | Resistance Value                 | Tolerance | T.C.R. Code | Release                                                                  |
| H4P         | 1.0 ohm<br>(1000 milli ohms) 1R0 | A - 0.05% | A - 5ppm    | A - Part can only<br>be sold with<br>Commercial or<br>C of C release.    |
| H4          | 10 ohm<br>(10 ohms) 10R          | B - 0.1%  | B - 10ppm   |                                                                          |
| H8          | 100 ohm<br>(100 ohms) 100R       | C - 0.25% | Y - 15ppm   | B - Part can be<br>sold to BS CECC<br>40101 004,<br>BS CECC 40101<br>030 |
|             | 1K Ohm<br>(1000 ohms) 1K0        | D - 0.5%  | D - 25ppm   |                                                                          |
|             | 10K ohm<br>(10000 ohms) 10K      | F - 1.0%  | C - 50ppm   | D - Part can<br>be sold to<br>BS CECC 40101<br>804                       |
|             | 100K ohm<br>(100000 ohms) 100K   |           | Z - 100ppm  |                                                                          |
|             | 1M ohm<br>(1000000 ohms) 1M0     |           |             |                                                                          |

TE Connectivity, TE connectivity (logo) and TE (logo) are trademarks.

Other logos, product and Company names mentioned herein may be trademarks of their respective owners.

While TE has made every reasonable effort to ensure the accuracy of the information in this datasheet, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this datasheet are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.