

2SK1931

(F5E20)

200V 5A

FEATURES

●Applicable to 4V drive.

●The static Rds(on) is small.

●Built-in ZD for Gate Protection.

APPLICATION

●DC/DC converters

●Power supplies of DC 12-24V input

●Product related to


Integrated Service Digital Network

RATINGS

●Absolute Maximum Ratings (Tc = 25°C)

Item	Symbol	Conditions	Ratings	Unit
Storage Temperature	T _{stg}		-55~150	°C
Channel Temperature	T _{ch}		150	
Drain-Source Voltage	V _{DSS}		200	V
Gate-Source Voltage	V _{GS}		±30	
Continuous Drain Current (DC)	I _D		5	A
Continuous Drain Current (Peak)	I _{DP}		10	
Continuous Source Current (DC)	I _S		5	
Total Power Dissipation	P _T		20	W

OUTLINE DIMENSIONS




●Electrical Characteristics $T_c = 25^\circ\text{C}$


Item	Symbol	Conditions	Min.	Typ.	Max.	Unit
Drain-Source Breakdown Voltage	$V_{(BR)DSS}$	$I_D = 1\text{mA}$, $V_{GS} = 0\text{V}$	200			V
Zero Gate Voltage Drain Current	I_{DSS}	$V_{DS} = 200\text{V}$, $V_{GS} = 0\text{V}$			250	μA
Gate-Source Leakage Current	I_{GSS}	$V_{GS} = \pm 30\text{V}$, $V_{DS} = 0\text{V}$			± 0.1	
Forward Transconductance	g_{fs}	$I_D = 2.5\text{A}$, $V_{DS} = 10\text{V}$	0.9	1.8		S
Static Drain-Source On-state Resistance	$R_{DS(ON)}$	$I_D = 2.5\text{A}$, $V_{GS} = 10\text{V}$		0.45	0.65	Ω
Gate Threshold Voltage	V_{TH}	$I_D = 1\text{mA}$, $V_{DS} = 10\text{V}$	2	3	4	V
Source-Drain Diode Forward Voltage	V_{SD}	$I_S = 2.5\text{A}$, $V_{GS} = 0\text{V}$			1.5	
Thermal Resistance	θ_{jc}	junction to case			6.25	$^\circ\text{C}/\text{W}$
Total Gate Charge	Q_g	$V_{GS} = 10\text{V}$, $I_D = 5\text{A}$, $V_{DD} = 150\text{V}$		11		nC
Input Capacitance	C_{iss}	$V_{DS} = 10\text{V}$, $V_{GS} = 0\text{V}$, $f = 1\text{MHz}$		360		pF
Reverse Transfer Capacitance	C_{rss}			45		
Output Capacitance	C_{oss}			190		
Turn-On Time	t_{on}	$I_D = 2.5\text{A}$, $V_{GS} = 10\text{V}$, $R_L = 40\Omega$		55	110	ns
Turn-Off Time	t_{off}			75	150	

2SK1931


Transfer Characteristics



2SK1931 Static Drain-Source On-state Resistance




2SK1931 Gate Threshold Voltage




2SK1931


Safe Operating Area



2SK1931 Transient Thermal Impedance



2SK1931 Capacitance



2SK1931

Power Derating

