

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

LOC

DIST

REVISONS

DESCRIPTION

DATE

DWN

APVD

1.570

1.680

1.600

1.200

12

26

7-102692-9

8.270

8.380

8.300

7.900

79

160

7-102692-8

4.970

5.080

5.000

4.600

46

94

7-102692-7

2.470

2.580

2.500

2.100

21

44

7-102692-6

.970

1.080

1.000

.600

6

14

7-102692-5

9.270

9.380

9.300

8.900

89

180

7-102692-4

7.670

7.780

7.700

7.300

73

148

7-102692-3

6.670

6.780

6.700

6.300

63

128

7-102692-2

7.270

7.380

7.300

6.900

69

140

7-102692-1

6.770

6.880

6.800

6.400

64

130

7-102692-0

4.570

4.680

4.600

4.200

42

86

6-102692-9

3.870

3.980

3.900

3.500

35

72

6-102692-8

1.770

1.880

1.800

1.400

14

30

6-102692-7

1.270

1.380

1.300

.900

9

20

6-102692-6

1.070

1.180

1.100

.700

7

16

6-102692-5

3.770

3.880

3.800

3.400

34

70

6-102692-4

2.270

2.380

2.300

1.900

19

40

6-102692-3

4.770

4.880

4.800

4.400

44

90

6-102692-2

10.270

10.380

10.300

9.900

99

200

6-102692-1

5.770

5.880

5.800

5.400

54

110

6-102692-0

6.270

6.380

6.300

5.900

59

120

5-102692-9

5.270

5.380

5.300

4.900

49

100

5-102692-8

5.070

5.180

5.100

4.700

47

96

5-102692-7

4.270

4.380

4.300

3.900

39

80

5-102692-6

3.270

3.380

3.300

2.900

29

60

5-102692-5

2.770

2.880

2.800

2.400

24

50

5-102692-4

2.070

2.180

2.100

1.700

17

36

5-102692-3

1.470

1.580

1.500

1.100

11

24

5-102692-2

.870

.980

.900

.500

5

12

5-102692-1

1.570

1.680

1.600

1.200

12

26

2-102692-9

8.270

8.380

8.300

7.900

79

160

2-102692-8

4.970

5.080

5.000

4.600

46

94

2-102692-7

2.470

2.580

2.500

2.100

21

44

2-102692-6

.970

1.080

1.000

.600

6

14

2-102692-5

9.270

9.380

9.300

8.900

89

180

2-102692-4

7.670

7.780

7.700

7.300

73

148

2-102692-3

6.670

6.780

6.700

6.300

63

128

2-102692-2

7.270

7.380

7.300

6.900

69

140

2-102692-1

6.770

6.880

6.800

6.400

64

130

2-102692-0

4.570

4.680

4.600

4.200

42

86

1-102692-9

3.870

3.980

3.900

3.500

35

72

1-102692-8

1.770

1.880

1.800

1.400

14

30

1-102692-7

1.270

1.380

1.300

.900

9

20

1-102692-6

1.070

1.180

1.100

.700

7

16

1-102692-5

3.770

3.880

3.800

3.400

34

70

1-102692-4

2.270

2.380

2.300

1.900

19

40

1-102692-3

4.770

4.880

4.800

4.400

44

90

1-102692-2

10.270

10.380

10.300

9.900

99

200

1-102692-1

5.770

5.880

5.800

5.400

54

110

1-102692-0

6.270

6.380

6.300

5.900

59

120

102692-9

5.270

5.380

5.300

4.900

49

100

102692-8

5.070

5.180

5.100

4.700

47

96

102692-7

4.270

4.380

4.300

3.900

39

80

102692-6

3.270

3.380

3.300

2.900

29

60

102692-5

2.770

2.880

2.800

2.400

24

50

102692-4

2.070

2.180

2.100

1.700

17

36

102692-3

1.470

1.580

1.500

1.100

11

24

102692-2

.870

.980

.900

.500

5

12

102692-1

E

D

C ± .010

B

A

NO. OF POSN

PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN B. HAYMAKER 11JAN01

CHK J. GESFORD 12NOV98

APVD J. GESFORD 12NOV98

NAME

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

DIMENSIONS: INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± .005

4 PLC ± -

ANGLES ± -

FINISH SEE TABLE

MATERIAL: GLASS FILLED FLAME RETARDANT THERMOPLASTIC COLOR:BLACK POST: COPPER ALLOY

SIZE CAGE CODE DRAWING NO

RESTRICTED TO

SCALE 4:1 SHEET 1 OF 1 REV L5

TE Connectivity

HEADER ASSEMBLY, MOD II, .100C.100CL, .025 SQ POSTS

00779C=102692

SECTION Y-Y

SECTION X-X

RECOMMENDED HOLE SIZE

1 POINT OF MEASUREMENT FOR PLATING THICKNESS.

2 FINISH OVER INDICATED AREA: .000030 GOLD OVER .000050 NICKEL.

3 FINISH OVER INDICATED AREA: .000100-.000200 BRIGHT TIN LEAD OVER .000050 NICKEL.

4 RECESSED DATE CODE AND LOGO.

5 OBSOLETE PART NUMBER.

6 PRELIMINARY PART - NOT RELEASED FOR PRODUCTION

7 FINISH OVER INDICATED AREA: .000100-.000200 MATTE TIN OVER .000050 NICKEL.

8 ROHS 2002/95/EC COMPLIANT

9 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI