

10 Base-T Transformers with Common Mode Choke Transformers

EPE6062S




- 2000 Vrms Isolation •
- Package in Tubes or Tape and Reel •
- Complies with or exceed IEEE802.3, 10 Base- T Requirements •

Electrical Parameters @ 25° C

Primary Inductance (mH Min.) (*)	Leakage Inductance (μH Max.)	Interwinding Capacitance (pF Max.)	DCR (Ω Max.)
200	.30	20	.90


• *Measured @ 100 KHz, 20m Vrms, Pins 1-3 & Pins 9-11 •

Schematic



Pins # 4, 5, 12, 13 N/C

Package



Dimensions

Dim.	(Inches)			(Millimeters)		
	Min.	Max.	Nom.	Min.	Max.	Nom.
A	.440	.460		11.18	11.68	
B	.240	.260		6.10	6.60	
C	.215	.235		5.46	5.97	
D	.350	Typ.		8.89	Typ.	
E	.005	.015		.127	.381	
F	.050	Typ.		1.27	Typ.	
G	.355	.375		9.02	9.53	
H	.016	.022		.406	.560	
I	.010	Typ.		.254	Typ.	
J	.05	Typ.		1.27	Typ.	
K	0°	8°		0°	8°	
L	.030	.050		.762	1.27	
M			.025			.635
N			.050			1.27
P			.090			2.29
Q			.420			10.67