



ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART, CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

SPC-F005.DWG


REVISIONS

DOC. NO. SPC-F005 * Effective: 7/8/02 * DCP No: 1398

DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
1906	A	RELEASED	EO	04/17/06	TL	05/25/06	HO	05/25/06



RoHS
Compliant



ITEM#	QTY	DESCRIPTION
(1)	A/R	CABLE, OPTICAL FIBER, MM, DUPLEX, 62.5/125 μ M, Ø2.0MM ZIPCORD, ORANGE PVC JACKET, UL, CSA.
(2)	1	CONNECTOR, OPTICAL FIBER, MTRJ, MULTI-MODE, POLYMER FERRULE, BLACK HOUSING.
(3)	1	CONNECTOR ACCESSORY, OPTICAL FIBER, MTRJ, MULTI-MODE, BOOT, BLACK POLYVINYL CHLORIDE.
(4)	2	CONNECTOR, OPTICAL FIBER, SC, MULTI-MODE, CERAMIC FERRULE, BEIGE HOUSING.
(5)	1	CONNECTOR ACCESSORY, OPTICAL FIBER, SC, MULTI-MODE, BOOT, BEIGE POLYVINYL CHLORIDE.
(6)	1	CONNECTOR ACCESSORY, OPTICAL FIBER, SC, MULTI-MODE, BOOT, BEIGE POLYVINYL CHLORIDE.

SPECIFICATION:

1. MAXIMUM INSERTION LOSS: 0.5dB (SC), 0.7dB (MTRJ).

SPC TYPE No.	LENGTH(M)
SPC20010	3
SPC19998	2
SPC19963	1

DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED
HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE
BELIEVE TO BE ACCURATE AND RELIABLE. SINCE
CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE
USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT
FOR THE INTENDED USE AND ASSUME ALL RISK AND
LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:
UNLESS OTHERWISE
SPECIFIED,
DIMENSIONS ARE
FOR REFERENCE
PURPOSES ONLY.

DRAWN BY:
EKLAS ODISH 04/17/06
CHECKED BY:
THOMAS LEE 05/25/06
APPROVED BY:
HISHAM ODISH 05/25/06

DRAWING TITLE:
Fiber Optic Cable, MTRJ to SC, 62.5/125 Micron, MM
SIZE DWG. NO. ELECTRONIC FILE REV
A TA-728 TA-728.DWG A
SCALE: NTS U.O.M.: meters SHEET: 1 OF 1