NLAS2066

Ultra-Small Dual Single Pole, Single Throw Analog Switch with Over Voltage Tolerance

The NLAS2066 is a Dual SPST (Single Pole, Single Throw) Analog Switch high performance version of the popular NLAS323. Packaged in the ultra−small US8 package. It is designed as a general analog/digital switch and can also be used to isolate USB ports.

Features

- Same Pinout as the Popular NLAS323
- Excellent Performance – Maximum RDS_{ON} 15 Ω at 3.0 V
- Matching Between the Switches ±1.5 Ω at 3.0 V
- 1.65 V to 5.5 V Operating Range
- Lower Threshold Voltages for LVTTL/CMOS Levels
- Ultra−Low Charge Injection ≤ 4.8 pC at 3.0 V
- Low Standby Power – I_{CC} = 1.0 nA (max) @ T_A = 25°C
- CMOS Level Compatibility
- OVT* (Pins 1, 3, 5, and 7) These Pins may be Subjected to 0 to +7.0 V, Regardless of Operating Voltage
- Allows a Short from USB Line without Damage to the Device
- This is a Pb−Free Device*

Typical Applications

- USB Isolation
- Cell Phones
- PDAs
- MP3s Digital Still Cameras

Important Information

- ESD Protection: Human Body Model; > 1500 V
  Machine Model; > 200 V
- Latch−Up Maximum Rating: 200 mA

*Over Voltage Tolerance (OVT) enables pins to function outside (higher) of their operating voltages, with no damage to the devices or to signal integrity.

**For additional information on our Pb−Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

ON Semiconductor®

http://onsemi.com



US8
US SUFFIX
CASE 493

MARKING DIAGRAM



AH = Specific Device Code
M = Date Code
▪ = Pb−Free Package
(Note: Microdot may be in either location)



PIN ASSIGNMENT

Pin	Function	OVT
1	NO1	Yes
2	COM1	–
3	IN2	Yes
4	GND	–
5	NO2	Yes
6	COM2	–
7	IN1	Yes
8	V_{CC}	–

FUNCTION TABLE

On/Off Enable Input	State of Analog Switch
L	Off
H	On

ORDERING INFORMATION

See detailed ordering and shipping information in the package dimensions section on page 8 of this data sheet.

MAXIMUM RATINGS

Symbol	Rating		Value	Unit
V_{CC}	DC Supply Voltage		−0.5 to +7.0	V
V_I	DC Input Voltage	Pins 1, 3, 5, 7 Pins 2, 6	−0.5 to +7.0 −0.5 to V_{CC}	V
V_O	DC Output Voltage		−0.5 to +7.0	V
I_{IK}	DC Input Diode Current	V_I < GND	−50	mA
I_{OK}	DC Output Diode Current	V_O < GND	−50	mA
I_O	DC Output Sink Current		±50	mA
I_{CC}	DC Supply Current per Supply Pin		±100	mA
I_{GND}	DC Ground Current per Ground Pin		±100	mA
T_{STG}	Storage Temperature Range		−65 to +150	°C
T_L	Lead Temperature, 1 mm from Case for 10 Seconds		260	°C
T_J	Junction Temperature under Bias		+150	°C
θ_{JA}	Thermal Resistance (Note 1)		250	°C/W
P_D	Power Dissipation in Still Air at 85°C		250	mW
MSL	Moisture Sensitivity		Level 1	–
F_R	Flammability Rating	Oxygen Index: 28 to 34	UL 94 V−0 @ 0.125 in	–
V_{ESD}	ESD Withstand Voltage	Human Body Model (Note 2) Machine Model (Note 3) Charged Device Model (Note 4)	> 1500 > 200 N/A	V

Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.

1. Measured with minimum pad spacing on an FR4 board, using 10 mm−by−1 inch, 2−ounce copper trace with no air flow
2. Tested to EIA/JESD22−A114−A
3. Tested to EIA/JESD22−A115−A
4. Tested to JESD22−C101−A

RECOMMENDED OPERATING CONDITIONS

Symbol	Characteristics		Min	Max	Unit
V_{CC}	Positive DC Supply Voltage		1.65	5.5	V
V_{IN}	Digital Input Voltage (Enable)		GND	5.5	V
V_{IO}	Static or Dynamic Voltage Across an Off Switch		GND	V_{CC}	V
V_{IS}	Analog Input Voltage	NO COM	GND GND	V_{CC} 5.5	V
T_A	Operating Temperature Range, All Package Types		−55	+125	°C
t_r, t_f	Input Rise or Fall Time (Enable Input)	V_{CC} = 3.3 V ± 0.3 V V_{CC} = 5.0 V ± 0.5 V	0 0	100 20	ns/V

DEVICE JUNCTION TEMPERATURE VS. TIME TO 0.1% BOND FAILURES

Junction Temperature °C	Time, Hours	Time, Years
80	1,032,200	117.8
90	419,300	47.9
100	178,700	20.4
110	79,600	9.4
120	37,000	4.2
130	17,800	2.0
140	8,900	1.0



Figure 1. Failure Rate vs. Time Junction Temperature

DC CHARACTERISTICS – Digital Section (Voltages Referenced to GND)

Symbol	Parameter	Condition	V_{CC}	Guaranteed Max Limit			Unit
				25°C	–40 to 85°C	–55 to <125°C	
V_{IH}	Minimum High–Level Input Voltage, Enable Inputs		2.3 ± 10% 2.7 ± 10% 3.0 ± 10% 5.0 ± 10%	V_{CC} x 0.55 V_{CC} x 0.55 V_{CC} x 0.55 V_{CC} x 0.55	V_{CC} x 0.55 V_{CC} x 0.55 V_{CC} x 0.55 V_{CC} x 0.55	V_{CC} x 0.55 V_{CC} x 0.55 V_{CC} x 0.55 V_{CC} x 0.55	V
V_{IL}	Maximum Low–Level Input Voltage, Enable Inputs		2.3 ± 10% 2.7 ± 10% 3.0 ± 10% 5.0 ± 10%	V_{CC} x 0.30 V_{CC} x 0.30 V_{CC} x 0.30 V_{CC} x 0.30	V_{CC} x 0.30 V_{CC} x 0.30 V_{CC} x 0.30 V_{CC} x 0.30	V_{CC} x 0.30 V_{CC} x 0.30 V_{CC} x 0.30 V_{CC} x 0.30	V
I_{IN}	Maximum Input Leakage Current, Enable Inputs	V_{IN} = 5.5 V or GND	0 V to 5.5 V	±0.1	±1.0	±1.0	μA
I_{CC}	Maximum Quiescent Supply Current (per package)	Enable and V_{IS} = V_{CC} or GND	5.5	1.0	1.0	2.0	μA

DC ELECTRICAL CHARACTERISTICS – Analog Section

Symbol	Parameter	Condition	V_{CC}	Guaranteed Max Limit			Unit
				25°C	–40 to 85°C	–55 to <125°C	
R_{ON}	Maximum On Resistance	$V_{IN} = V_{IH}$ I_s = 8 mA $V_{IS} = V_{CC}$ to GND I_s = 8 mA I_s = 24 mA I_s = 32 mA (Figures 2 and 3)	2.3 2.7 3.0 4.5	50 20 15 7	54 24 19 11	54 24 19 11	Ω
$R_{FLAT(ON)}$	On Resistance Flatness	$V_{IN} = V_{IH}$ I_s = 8 mA V_{IS} = 0 to V_{CC} I_s = 8 mA I_s = 24 mA I_s = 32 mA (Figure 5)	2.3 2.7 3.0 4.5	60 24 13.5 3.0	60 24 13.5 3.0	60 24 13.5 3.0	Ω
ΔR_{ON}	On Resistance Match Between Channels	V_{IS} = 1.4 V V_{IS} = 1.6 V V_{IS} = 1.8 V V_{IS} = 2.7 V (Figures 4, 5 and 6)	2.3 2.7 3.0 4.5	1.3 1.4 1.5 2.0	1.3 1.4 1.5 2.0	1.3 1.4 1.5 2.0	Ω
$I_{NO(OFF)}$	Off Leakage Current	$V_{IN} = V_{IL}$ V_{NO} = 1.0 V, V_{COM} = 4.5 V or V_{COM} = 1.0 V and V_{NO} 4.5 V	5.5	1.0	10	100	nA
$I_{COM(OFF)}$	Off Leakage Current	$V_{IN} = V_{IL}$ V_{NO} = 4.5 V or 1.0 V V_{COM} = 1.0 V or 4.5 V	5.5	1.0	10	100	nA

AC ELECTRICAL CHARACTERISTICS (Input $t_r = t_f$ = 3.0 ns)

Symbol	Parameter	Condition	V_{CC}	Guaranteed Max Limit									Unit
				25°C			–40 to 85°C			–55 to <125°C			
			(V)	Min	Typ	Max	Min	Typ	Max	Min	Typ	Max	
t_{ON}	Turn–On Time	R_L = 300 Ω, C_L = 35 pF (Figures 7, 14 and 15)	2.3 2.7 3.0 4.5		8 4 3 2	9 5 4 3			10 7 6 5			10 7 6 5	ns
t_{OFF}	Turn–Off Time	R_L = 300 Ω, C_L = 35 pF (Figures 7, 14 and 15)	2.3 2.7 3.0 4.5		8 6 5 4	10 8 7 6			11 9 8 7			11 9 8 7	ns

		Typical @ 25°C, V_{CC} = 5.0 V	Unit
C_{IN}	Maximum Input Capacitance, Select Input	3.0	pF
C_{NO} or C_{NC}	Analog I/O (Switch Off)	10	
$C_{COM(OFF)}$	Common I/O (Switch Off)	10	
$C_{COM(ON)}$	Feedthrough (Switch Off)	10	

ADDITIONAL APPLICATIONS CHARACTERISTICS (Voltage Reference to GND Unless Noted)

Symbol	Parameter	Condition	V_{CC} (V)	Typical 25°C	Unit
BW	Maximum On−Channel −3.0 dB Bandwidth or Minimum Frequency Response	V_{IS} = 0 dBm (Figure 8 and 9)	2.3 2.7 3.0 4.5	102 175 180 186	MHz
V_{ONL}	Maximum Feed−Through On Loss	V_{IS} = 0 dBm @ 10 kHz (Figure 8 and 9)	2.3 2.7 3.0 4.5	−2.2 −0.9 −0.8 −0.4	dB
V_{ISO}	Off−Channel Isolation	f = 100 kHz V_{IS} = 1.0 V RMS (Figure 10 and 11)	2.3 2.7 3.0 4.5	−73 −74 −74 −75	dB
Q	Charge Injection Enable Input to Common I/O	V_{IS} = V_{CC} to GND, F_{IS} = 20 kHz (Figure 12)	3.0 5.5	4.8 7.4	pC
THD	Total Harmonic Distortion TDH + Noise	F_{IS} = 10 Hz to 100 kHz, R_L = Rgen = 600 Ω, C_L = 50 pF (Figure 13)	3.0 5.5	0.19 0.06	%



Figure 2. R_{ON} vs. V_{COM} and V_{CC} (@25°C)



Figure 3. R_{ON} vs. V_{COM} and Temperature, V_{CC} = 2.0 V



Figure 4. R_{ON} vs. V_{COM} and Temperature, V_{CC} = 2.5 V



Figure 5. R_{ON} vs. V_{COM} and Temperature, V_{CC} = 3.0 V



Figure 6. R_{ON} vs. V_{COM} and Temperature, V_{CC} = 4.5 V



Figure 7. Switching Time vs. Supply Voltage, T = 25°C



Figure 8. ON Channel Bandwidth and Phase Shift Over Frequency



Figure 9. ON Channel Bandwidth and Phase Shift Over Frequency



Figure 10. Off Isolation and Crosstalk



Figure 11. Off Isolation and Crosstalk



Figure 12. Charge Injection vs. V_{COM}



Figure 13. THD vs. Frequency

TIMING INFORMATION



Figure 14. t_{ON}/t_{OFF}



Figure 15. t_{ON}/t_{OFF}

V_{CC}	VMI
2.0 V	1.0 V
3.0 V	1.5 V
4.5 V	1.5 V

DEVICE ORDERING INFORMATION

Device	Device Nomenclature				Package Type	Shipping†
	Circuit Indicator	Technology	Device Function	Package Suffix		
NLAS2066USG	NL	AS	2066	US	US8 (Pb−Free)	3,000 / Tape & Reel
NLAS2066UST3G	NL	AS	2066	UST3	US8 (Pb−Free)	10,000 / Tape & Reel

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

PACKAGE DIMENSIONS

US8
US SUFFIX
CASE 493−02
ISSUE B



DETAIL E

NOTES:
1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
2. CONTROLLING DIMENSION: MILLIMETERS.
3. DIMENSION “A” DOES NOT INCLUDE MOLD FLASH, PROTRUSION OR GATE BURR. MOLD FLASH. PROTRUSION AND GATE BURR SHALL NOT EXCEED 0.140 MM (0.0055”) PER SIDE.
4. DIMENSION “B” DOES NOT INCLUDE INTER−LEAD FLASH OR PROTRUSION. INTER−LEAD FLASH AND PROTRUSION SHALL NOT E3XCEED 0.140 (0.0055”) PER SIDE.
5. LEAD FINISH IS SOLDER PLATING WITH THICKNESS OF 0.0076−0.0203 MM. (300−800 “).
6. ALL TOLERANCE UNLESS OTHERWISE SPECIFIED ±0.0508 (0.0002 “).

	MILLIMETERS		INCHES	
DIM	MIN	MAX	MIN	MAX
A	1.90	2.10	0.075	0.083
B	2.20	2.40	0.087	0.094
C	0.60	0.90	0.024	0.035
D	0.17	0.25	0.007	0.010
F	0.20	0.35	0.008	0.014
G	0.50 BSC		0.020 BSC	
H	0.40 REF		0.016 REF	
J	0.10	0.18	0.004	0.007
K	0.00	0.10	0.000	0.004
L	3.00	3.20	0.118	0.126
M	0 °	6 °	0 °	6 °
N	5 °	10 °	5 °	10 °
P	0.23	0.34	0.010	0.013
R	0.23	0.33	0.009	0.013
S	0.37	0.47	0.015	0.019
U	0.60	0.80	0.024	0.031
V	0.12 BSC		0.005 BSC	

SOLDERING FOOTPRINT*



SCALE 8:1 $\left(\frac{\text{mm}}{\text{inches}}\right)$

*For additional information on our Pb−Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:
Literature Distribution Center for ON Semiconductor
P.O. Box 5163, Denver, Colorado 80217 USA
Phone: 303−675−2175 or 800−344−3860 Toll Free USA/Canada
Fax: 303−675−2176 or 800−344−3867 Toll Free USA/Canada
Email: orderlit@onsemi.com

N. American Technical Support: 800−282−9855 Toll Free USA/Canada

Japan: ON Semiconductor, Japan Customer Focus Center
2−9−1 Kamimeguro, Meguro−ku, Tokyo, Japan 153−0051
Phone: 81−3−5773−3850

ON Semiconductor Website: http://onsemi.com

Order Literature: http://www.onsemi.com/litorder

For additional information, please contact your local Sales Representative.