

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [99-99-0994](#)
Status: **Active**
Overview: [KK® Interconnect System - Molex](#)
Description: 2.50mm Pitch SPOX™ Wire-to-Board Header, Vertical, Shrouded, 10 Circuits, Tin (Sn) Plating, with Swaged PC Tails

Documents:
[3D Model](#)
[Drawing \(PDF\)](#)
[Product Specification PS-5264-001 \(PDF\)](#)
[Packaging Specification SPK-5267-001 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification


CSA LR19980
UL E29179

General

Product Family PCB Headers
Series [5267](#)
Application Signal, Wire-to-Board
Overview [KK® Interconnect System - Molex](#)
Product Name SPOX™
UPC 800753577046

Physical

Breakaway No
Circuits (Loaded) 10
Circuits (maximum) 10
Color - Resin Natural
Durability (mating cycles max) 30
First Mate / Last Break No
Flammability 94V-0
Glow-Wire Compliant No
Guide to Mating Part No
Keying to Mating Part None
Lock to Mating Part Yes
Material - Plating Mating Tin
Material - Plating Termination Tin
Material - Resin Nylon
Net Weight 851.900/mg
Number of Rows 1
Orientation Vertical
PC Tail Length 3.50mm
PCB Locator No
PCB Retention Yes
PCB Thickness - Recommended 1.60mm
Packaging Type Bag
Pitch - Mating Interface 2.50mm
Plating min - Mating 4.064µm
Plating min - Termination 4.064µm
Polarized to Mating Part Yes
Polarized to PCB No
Shrouded Fully
Stackable No
Surface Mount Compatible (SMC) No
Temperature Range - Operating -40°C to +105°C
Termination Interface: Style Through Hole



EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Not Low-Halogen



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[5267Series](#)

Mates With
5264 SPOX™ Wire-to-Board Crimp Housing, [42219](#) SPOX™ IDT Receptacle Housing

Electrical

Current - Maximum per Contact	3A
Voltage - Maximum	250V

Material Info

Old Part Number	5267-10A-X
-----------------	------------

Reference - Drawing Numbers

Packaging Specification	SPK-5267-001
Product Specification	PS-5264-001, RPS-5264-003, RPS-5264-004, RPS-5264-005, RPS-5264-006, RPS-5264-007
Sales Drawing	SD-5267-NA-X

This document was generated on 07/09/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:
99-99-0994