


HDSL LINE TRANSFORMERS



- For use with Conexant chipsets
- Excellent THD performance
- Small footprint
- Designed to meet UL 1950 supplementary insulation requirements for working voltage up to 250 Vrms

Electrical Specifications @ 25°C — Operating Temperature -40°C to +85°C

Part Number	Mount.	Matched to Conexant's Chipset No.	Application	Turns Ratio Line - Chip (±2%)	Inductance - Line Side @ 10 kHz, 100 mV (1-5) with (2-4) shorted	Leakage Inductance - Line Side @ 100 kHz (1-5) with (2-4) and (7-9) shorted	DC Resistance	
							Line Side (1-4) = (2-5)	Chip Side (7-9)
B1017	THT	BT8921/BT8970	784 Kbps	2CS:1	3.0 mH ±6%	15 µH MAX @ 0.02 Vrms	≤ 1.25 Ω	≤ 1.00 Ω
B1059 ¹	SMT	BT8921/BT8970	784 Kbps	2CS:1	3.0 mH ±10%	15 µH MAX @ 0.02 Vrms	≤ 1.25 Ω	≤ 1.00 Ω
B1018	THT	BT8921/BT8970	1168 Kbps	2CS:1CT	2.0 mH ±10%	13 µH MAX @ 0.10 Vrms	≤ 1.25 Ω	≤ 1.00 Ω
B1028 ¹	SMT	BT8921/BT8970	1168 Kbps	2CS:1CT	2.0 mH ±6%	11 µH MAX @ 0.10 Vrms	≤ 1.20 Ω	≤ 1.00 Ω
B1020A	THT	RS8973	272 to 2320 Kbps	2CS:1	2.0 mH ±6%	6.5 µH MAX @ 0.02 Vrms	≤ 2.00 Ω	≤ 1.10 Ω
B1040A ¹	SMT	RS8973	272 to 2320 Kbps	2CS:1	2.0 mH ±10%	6.5 µH MAX @ 0.02 Vrms	≤ 1.60 Ω	≤ 1.05 Ω
B1075	THT	RS8973	272 to 2320 Kbps	2CS:1CT	2.0 mH ±6%	8 µH MAX @ 0.02 Vrms	≤ 2.00 Ω	≤ 0.70 Ω
B1077 ¹	SMT	RS8973	272 to 2320 Kbps	2CS:1CT	2.0 mH ±8%	8 µH MAX @ 0.02 Vrms	≤ 2.00 Ω	≤ 0.70 Ω

Additional Electrical Specifications



Part Number	Longitudinal Balance (dB)	THD @ 135 Ω (dB)	Insertion Loss @ 135 Ω (dB)	Return Loss @ 135 Ω (dB)	Isolation Voltage (Vrms @ 60 sec)
B1017	≤ -53 (40 kHz to 200 kHz)	≤ -70 (10 kHz, 5.0 Vrms)	≤ 0.40 (26 kHz to 200 kHz)	≥ 19 (40 kHz to 200 kHz)	1500
B1059	≤ -53 (40 kHz to 200 kHz)	≤ -70 (10 kHz, 5.0 Vrms)	≤ 0.40 (26 kHz to 200 kHz)	≥ 19 (40 kHz to 200 kHz)	1500
B1018	≤ -53 (30 kHz to 300 kHz)	≤ -70 (40 kHz, 1.85 Vrms)	≤ 0.50 (40 kHz)	≥ 16 (40 kHz to 300 kHz)	1500
B1028	≤ -50 (40 kHz to 300 kHz)	≤ -70 (20 kHz, 4.5 Vrms)	(Data not available)	≥ 16.5 (40 kHz to 300 kHz)	1500
B1020A	≤ -50 (30 kHz to 300 kHz)	≤ -70 (10 kHz, 5.0 Vrms)	≤ 0.65 (30 kHz to 580 kHz)	≥ 16 (40 kHz to 300 kHz)	1500
B1040A	≤ -50 (30 kHz to 420 kHz)	≤ -70 (10 kHz, 5.0 Vrms)	≤ 0.60 (30 kHz to 580 kHz)	≥ 16 (40 kHz to 300 kHz)	1500
B1075	≤ -50 (30 kHz to 300 kHz)	≤ -70 (10 kHz, 5.0 Vrms)	≤ 0.50 (30 kHz to 580 kHz)	≥ 16 (40 kHz to 300 kHz)	1500
B1077	≤ -50 (30 kHz to 300 kHz)	≤ -70 (10 kHz, 5.0 Vrms)	≤ 0.60 (30 kHz to 580 kHz)	≥ 16 (40 kHz to 300 kHz)	1500

¹Transformers are shipped in trays unless Tape & Reel packaging is specified by adding the suffix "T" to the part number (i.e. B1028T)


²DCR on the chip side of part numbers B1075 and B1077 is given for (7-8) = (8-9)

Mechanicals


Schematics



B1017, B1020A, B1040A & B1059



B1018, B1028, B1075 & B1077



For More Information :

Dimensions: $\frac{\text{Inches}}{\text{mm}}$

Unless otherwise specified, all tolerances are $\pm \frac{.010}{0.25}$

UNITED STATES (Worldwide)

12220 World Trade Drive
San Diego, CA 92128
U.S.A.
http://www.pulseeng.com
TEL: 858 674 8100
FAX: 858 674 8262

UNITED KINGDOM (Northern Europe)

1 & 2 Huxley Road
The Surrey Research Park
Guildford, Surrey GU2 5RE
United Kingdom
TEL: 44 1483 401700
FAX: 44 1483 401701

FRANCE (Southern Europe)

Zone Industrielle
F-39270
Orgelet
France
TEL: 33 3 84 35 04 04
FAX: 33 3 84 25 46 41

SINGAPORE (Southern Asia)

150 Kampong Ampat
#07-01/02
KA Centre
Singapore 368324
TEL: 65 287 8998
FAX: 65 280 0080

TAIWAN, R.O.C. (Northern Asia)

3F-4, No. 81, Sec. 1
HsinTai Wu Road
Hsi-Chih, Taipei Hsien
Taiwan, R.O.C.
Tel: 886 2 2698 0228
FAX: 886 2 2698 0948

HONG KONG (China/Hong Kong)

19/F, China United Plaza
1008 Tai Nan West Street
Cheung Sha Wan, Kowloon
Hong Kong, China
Tel: 852 2788 6588
FAX: 852 2776 1055

DISTRIBUTOR

Performance warranty of products offered on this data sheet is limited to the parameters specified. Data is subject to change without notice. Other brand and product names mentioned herein may be trademarks or registered trademarks of their respective owners.