

INTERCONNECTION

9.5mm (.374") Pitch Tri Barrier PCB Barrier Strip

- 2 to 30 poles
- Moulded in Black UL94-V0 Flame retardant PBT
- Rising saddle washer terminals
- Other Terminal styles available on request
-  approved


CBS44



TYPE NO.	POLES	LENGTH
CBS44ST8/2	2	20.4mm
CBS44ST8/3	3	29.4mm
CBS44ST8/4	4	39.4mm
CBS44ST8/5	5	48.9mm
CBS44ST8/6	6	58.4mm
CBS44ST8/7	7	67.9mm
CBS44ST8/8	8	77.4mm
CBS44ST8/9	9	86.9mm
CBS44ST8/10	10	96.4mm
CBS44ST8/11	11	106mm
CBS44ST8/12	12	115mm

SPECIFICATION

Rating	15A/300V AC
Wire range	0.3 - 2mm ² (14-22AWG)
Working temperature	- 40°C to 120°C
Moulding	Black UL94-V0 PBT
Screw torque	1.35Nm (12lb-in)
Screw	M3.5, steel Ni plated
Terminal	Brass, tin plated
Withstand voltage	2000V AC
Insulation Resistance	>5000MQ @ 500VDC
Recommended PCB hole size	ø2mm - ø2.2mm



9.5mm (.374") Pitch Dual Barrier PCB Barrier Strip

- 2 to 30 poles
- Moulded in Black UL94-V0 Flame retardant PBT
- Rising saddle washer terminals
- Other Terminal styles available on request
-  approved


CBS34



TYPE NO.	POLES	LENGTH
CBS34ST8/2	2	21.5mm
CBS34ST8/3	3	31mm
CBS34ST8/4	4	40.5mm
CBS34ST8/5	5	50mm
CBS34ST8/6	6	59.5mm
CBS34ST8/7	7	69mm
CBS34ST8/8	8	78.5mm
CBS34ST8/9	9	88mm
CBS34ST8/10	10	97.5mm
CBS34ST8/11	11	107mm
CBS34ST8/12	12	117mm

SPECIFICATION

Rating	20A/300V AC
Wire range	0.3 - 3.3mm ² (14-22AWG)
Working temperature	- 40°C to 120°C
Moulding	Black UL94-V0 PBT
Screw torque	1.35Nm (12lb-in)
Screw	M3.5, steel Ni plated
Terminal	Brass, tin plated
Withstand voltage	2000V AC
Insulation Resistance	>5000MQ @ 500VDC
Recommended PCB hole size	ø2mm - ø2.2mm



PCB
TERMINAL
BLOCKS

INTER-
CONNECTION

FUSES &
FUSE-
HOLDERS

LEDs &
INDICATORS

MINIATURE
SWITCHES

LIMIT &
SAFETY
SWITCHES

CONTROL
PRODUCTS

INTERFACE
MODULES &
SUPPORTS

RELAY
BASES

ENCLOSURES

BATTERIES

TRANS-
FORMERS