



ACTUATOR-/INDICATOR COMPONENT WITH
INTEGRATED LED 24V AC/DC LAMP HOLDER SCREW
TERMINAL GREEN

Contact block / lampholder

product designation		lampholder
Number of NC contacts / for auxiliary contacts		0
Number of NO contacts / for auxiliary contacts		0
Number of change-over switches / for auxiliary contacts		0
Product function / positive opening		No
Number of lampholders		1
Execution of the mounting		integrated
Nature of fluorescent material		LED
Color / of the fluorescent material		green
Design of the electrical connection		screw-type terminals

General technical details:

Degree of pollution		class 3
Design of the fuse link / for short-circuit protection of the auxiliary switch / with type of assignment 1 / required		gG / Dz 10 A
Type of voltage / of the supply voltage / of the fluorescent material		AC/DC
Supply voltage / 1 / of the fluorescent material		
• at 60 Hz / for AC / rated value	V	24
• at 50 Hz / for AC / rated value	V	24

• for DC / rated value	V	24
Type of voltage / of the operating voltage		AC/DC
Item designation		
• according to DIN EN 61346-2		P
• according to DIN 40719 extendable after IEC 204-2 / according to IEC 750		H
Ambient temperature		
• during operating	°C	-25 ... +70
• during storage	°C	-25 ... +80
protection class IP		
• of the terminal		IP20
• of the housing		IP40
Operating voltage / 1 / at 50 Hz / for AC / rated value	V	24
Operating voltage / 1 / at 60 Hz / for AC / rated value	V	24
Operating voltage		
• 1 / for DC / rated value	V	24
• at 50 Hz / at AC / rated value	V	21.6 ... 26.4
• at 60 Hz / at AC / rated value	V	21.6 ... 26.4
• for DC		
• rated value	V	21.6 ... 26.4
Suitability for integration		
• pressure selection button		front element
• front element		Yes
• suspension switch		Yes
• suspension pushbutton		Yes
Insulation voltage / rated value	V	250
Impulse voltage resistance / rated value	kV	4
Tightening torque / for auxiliary contacts / with screw-type terminals	N·m	0.8
Product component		
• fluorescent materials		Yes
• diode		Yes
• lamp transformer		No
• series resistance		No
Type of mounting		front mounting

Connections:

Type of the connectable conductor cross-section

- | | |
|--|-----------------------|
| • for auxiliary contacts / solid | 2x (1 ... 1.5 mm²) |
| • for auxiliary contacts / solid / with conductor end processing | 2x (0.5 ... 0.75 mm²) |

- for auxiliary contacts / finely stranded / with conductor end processing
- for AWG conductors / for auxiliary contacts

2x (0.5 ... 1.5 mm²)

2x (18 ... 14)

Certificates/approvals:

General Product Approval



CCC



CSA



GOST



UL

Test Certificates

[Special Test Certificate](#)

other

[Confirmation](#)



UL

Further information:

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<http://www.siemens.com/industrial-controls/mall>

Cax online generator:



<http://www.siemens.com/cax>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/3SB3400-1PC/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3SB3400-1PC



last change:

Apr 17, 2012