





PRODUCT NUMBER
63346-XYX
63346-XYXLF




PLATING IN CONTACT AREA		
DASH NUMBER	PERFORMANCE LEVEL	NOTES
-1YY	TELCORDIA CO	-
-2YY	TELECOM CLASS	-
-3YY	IEC CLASS I	-
-5YY	TELCORDIA UE	-
-9YY	TELCORDIA CO	-
-1YYLF	TELCORDIA CO IEC CLASS I	SEE NOTE 8
-2YYLF	TELECOM CLASS	SEE NOTE 8
-5YYLF	TELCORDIA UE	SEE NOTE 8

mat'l code				tolerances unless otherwise specified		CUSTOMER		FCI		www.fciconnect.com	
ltr	ecn no.	dr	date	linear	0.X ±0.3	projection	COPY	title	product family	METRAL	code
A	V02642	JWS	10/17/00		0.XX ±0.13						
B	V10908	CGD	02/22/01		.XXX ±.051						
C	V11897	CGD	08/27/01	angles	0° ±2°	MM	scale	A	size	dwg no	213
D	V21671	TAB	10/21/02	dr	T.BRUNGARD	11/19/99					
E	V05-1131	VS	02/25/06	enrg	M.STRAWER	11/19/99					
F	V06-0498	DCH	2006-05-30	chr	M.STRAWER	11/19/99	2:1	A	63346	1 of 3	sheet
				appd	M.STRAWER	02/29/00					
sheet index	revision sheet	F	F	F							
		1	2	3							



PRODUCT NUMBER
63346-XXX
63346-XXYLF



REQUIRED PC BOARD LAYOUT
COMPONENT SIDE
SEE PRINT 58351 FOR
ADDITIONAL PCB INFORMATION

KEY		
CODE	DIMENSIONS	
	DIM "A" MATE	DIM "B" TAIL
P01	6.50	4.25
P02	7.25	4.25
P03	8.00	4.25
P04	5.00	4.25
P05	5.75	4.25

NOTES:

- FOR DIM A AND B SEE SHEET 2 AND UP.
- BODY MATERIAL: LIQUID CRYSTAL POLYMER 30 % GLASS.
FLAME RETARDANT ACC. UL 94-V0.
- PIN MATERIAL:
PHOSPHOR BRONZE.
- PLATING ON PRESS-FIT TAIL:
63346-XXX IS SnPb
63346-XXYLF IS Sn (LEAD FREE).
PLATING ON CONTACT AREA CONFORMS
TO PERFORMANCE LEVEL SHOWN IN TABLE.
- PRODUCT MARKING:
PART NUMBER DESIGNATION & BATCH I.D.
- ALL PRODUCTS WITH PART NUMBERS SHOWN IN
SUBSEQUENT TABLES WILL BE PACKAGED IN TUBES.
IF TRAY PACKAGING IS REQUIRED, A SUFFIX "P"
WILL BE ADDED TO THE END OF THE PART NUMBER.
EXAMPLE: XXXXX-XXXP OR XXXXX-XXXP.
- PRODUCT SPECIFICATION GS-12-180.
APPLICATION SPECIFICATION BUS-20-073.
- THE PRODUCTS WHERE THE PART NUMBER ENDS IN LF
MEET THE EUROPEAN UNION DIRECTIVES AND OTHER
COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
- FOR LEAD FREE PART NUMBERS, ADD AN "LF" SUFFIX.
EXAMPLE: 63346-XXYLF
- ALL PRODUCTS WILL WITHSTAND EXPOSURE TO 260° FOR
60 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR
PHASE REFLOW OVEN.

mat'l code				tolerances unless otherwise specified		CUSTOMER		FCI		www.fciconnect.com	
ltr	ecr no.	dr	date	linear	0.X ± 0.3	projection	COPY	title	product family	METRAL	code
F					0.XX ± 0.13						
				angles	.XXX ± .051		MM	size	dwg no	A	213
					0° ± 2°						
				dr	T.BRUNGARD	11/19/99	scale	2:1	A	63346	sheet 2
				enrg	M.STRAWER	11/19/99					
				chr	M.STRAWER	11/19/99					
				appd	M.STRAWER	02/29/00					
sheet	revision										
index	sheet										

cage code 22526

Pro/E

PDM: Rev:F


STATUS: Released


Printed: May 03, 2009

This document is the property of and embodies
CONFIDENTIAL and PROPRIETARY information of FCI.
No part of the information shown on this
document may be used in any way or disclosed
to others without the written consent of FCI.
Copyright FCI.



METRAL P/N		CONTACT CODE MOD. I		METRAL P/N		CONTACT CODE MOD. I		METRAL P/N		CONTACT CODE MOD. I				
ROW		I	2	ROW		I	2	ROW		I	2			
63346-X01 SEE NOTE 9 LEAD FREE OPTION		E	P04	P04	63346-X05 SEE NOTE 9 LEAD FREE OPTION		E	P05	P05	63346-X09 SEE NOTE 9 LEAD FREE OPTION		E	P02	P02
		D	P04	P04			D	P05	P05			D	P02	P02
		C	P04	P04			C	P05	P05			C	P02	P02
		B	P04	P04			B	P02	P02			B	P02	P02
		A	P04	P04			A	P05	P05			A	P02	P02
METRAL P/N		CONTACT CODE MOD. I		METRAL P/N		CONTACT CODE MOD. I		METRAL P/N		CONTACT CODE MOD. I				
ROW		I	2	ROW		I	2	ROW		I	2			
63346-X02 SEE NOTE 9 LEAD FREE OPTION		E	P04	P04	63346-X06 SEE NOTE 9 LEAD FREE OPTION		E	P01	P01	63346-X10 SEE NOTE 9 LEAD FREE OPTION		E	P03	P03
		D	P04	P04			D	P01	P01			D	P03	P03
		C	P04	P04			C	P02	P02			C	P03	P03
		B	P04	P04			B	P03	P03			B	P03	P03
		A	P01	P01			A	P03	P03			A	P03	P03
METRAL P/N		CONTACT CODE MOD. I		METRAL P/N		CONTACT CODE MOD. I		METRAL P/N		CONTACT CODE MOD. I				
ROW		I	2	ROW		I	2	ROW		I	2			
63346-X03 SEE NOTE 9 LEAD FREE OPTION		E	P05	P05	63346-X07 SEE NOTE 9 LEAD FREE OPTION		E	P01	P01					
		D	P01	P01			D	P01	P01					
		C	P05	P05			C	P01	P01					
		B	P05	P05			B	P03	P03					
		A	P01	P01			A	P01	P01					
METRAL P/N		CONTACT CODE MOD. I		METRAL P/N		CONTACT CODE MOD. I		METRAL P/N		CONTACT CODE MOD. I				
ROW		I	2	ROW		I	2	ROW		I	2			
63346-X04 SEE NOTE 9 LEAD FREE OPTION		E	P01	P01	63346-X08 SEE NOTE 9 LEAD FREE OPTION		E	P05	P05					
		D	P01	P01			D	P05	P05					
		C	P01	P01			C	P05	P05					
		B	P01	P01			B	P05	P05					
		A	P01	P01			A	P05	P05					

mat'l code				tolerances unless otherwise specified				CUSTOMER		 www.fcjconnect.com			
ltr	ecn no.	dr	date	linear	0.X ±0.3			COPY		title METRAL POWER HEADER 1 MOD, 5 ROW STB			
F					0.XX ±0.13			projection					
					.XXX ±.051			0° ±2°					
				angles	0° ±2°					product family METRAL			
				dr	T.BRUNGARD	11/19/99	MM		size A				
				enr	M.STRAWSER	11/19/99	scale				sheet index		revision sheet
				chr	M.STRAWSER	11/19/99	2:1		sheet				
				appd	M.STRAWSER	02/29/00							

mat'l code				--		tolerances unless otherwise specified		CUSTOMER		FCI		www.fciconnect.com					
ltr	ecn no.	dr	date	linear	0. X ±0.3		projection	COPY		title METRAL POWER HEADER I MOD, 5 ROW STB							
F					0. XX ±0.13												
					. XXX ±.051												
				angles	0° ±2°					product family METRAL							
				dr	T. BRUNGARD	11/19/99		MM						size		dwg no	
				enrg	M. STRAWSER	11/19/99								A		213	
				chr	M. STRAWSER	11/19/99	scale				63346		sheet				
				appd	M. STRAWSER	02/29/00	2:1						3				
sheet index		revision sheet															