

Features

Regulated Converters

- 10W DIP24 Package
- 2kVDC and 3kVDC Isolation Options
- 2:1 and 4:1 Versions
- Continuous Short Circuit Protection (power limiting)
- Synchronous Rectification on 3.3, 5V outputs
- Full SMD internal design
- Through Hole or SMD Pinning Options
- Remote Control Pin
- Efficiency to 87%

Description

The REC10-xxxxSRW/DRW-series offer single and dual regulated outputs in a DIP24 package with 2kV or 3kV isolation options and are suitable for higher power industrial or medical applications. Remote on/off control is standard and SMD pinning is offered with the /SMD option. The converters can deliver 150% rated power for short periods of time to cope with applications with large capacitive loads or high start up currents.

Selection Guide

Part Number	Input Voltage (VDC)	Output Voltage (VDC)	Output Current (mA)	Efficiency (%)	Max. Cap. Load
REC10-xx3.3SRW/H*/A/M	9-18, 18-36, 36-75	3.3	2000	84-85	2200µF
REC10-xx05SRW/H*/A/M	9-18, 18-36, 36-75	5	2000	86-87	2200µF
REC10-xx12SRW/H*/A/M	9-18, 18-36, 36-75	12	833	85-86	470µF
REC10-xx15SRW/H*/A/M	9-18, 18-36, 36-75	15	667	85-86	220µF
REC10-xx05DRW/H*/A/M	9-18, 18-36, 36-75	±5	±1000	84	±1000µF
REC10-xx12DRW/H*/A/M	9-18, 18-36, 36-75	±12	±416	86	±220µF
REC10-xx15DRW/H*/A/M	9-18, 18-36, 36-75	±15	±333	86	±100µF
REC10-xx3.3SRWZ/H*/A/M	9-36, 18-75	3.3	2000	84	2200µF
REC10-xx05SRWZ/H*/A/M	9-36, 18-75	5	2000	86	2200µF
REC10-xx12SRWZ/H*/A/M	9-36, 18-75	12	833	85	470µF
REC10-xx15SRWZ/H*/A/M	9-36, 18-75	15	667	85	220µF
REC10-xx05DRWZ/H*/A/M	9-36, 18-75	±5	±1000	83	±1000µF
REC10-xx12DRWZ/H*/A/M	9-36, 18-75	±12	±416	85	±220µF
REC10-xx15DRWZ/H*/A/M	9-36, 18-75	±15	±333	85	±100µF

* Standard is /H2 for 2kVDC isolation,
use /H3 for 3kVDC Isolation (not SMD)

* add suffix "/SMD" for SMD package, e.g.
REC10-2405SRW/H2/A/M/SMD

2:1

xx = 9-18Vin = 12,
xx = 18-36Vin = 24,
xx = 36-75Vin = 48

4:1

xx = 9-36Vin = 24,
xx = 18-75Vin = 48

Specifications (measured at $T_A = 25^\circ\text{C}$, nominal input voltage, full load and after warm-up)

Input Voltage Range	2:1 & 4:1
Input Filter	PI Network
Output Voltage Accuracy	±1.5% max.
Line Voltage Regulation (V_L to V_H at full load)	±0.5% max.
Load Voltage Regulation (25% to 100% full load)	Single ±0.5% max. Dual ±1.2% max.
Cross Regulation (100%: 25% to 100% full load)	±5% max.
Output Ripple and Noise (with 100n output capacitor and 20MHz BW)	50mVp-p max.
Start-up time	300ms typ.
Operating Frequency (Full Load)	400kHz typ.
Efficiency at Full Load	see Selection Guide
Minimum Load	0%
	cont.


ECONOLINE

DC/DC-Converter

with 3 year Warranty

RECOM

10 Watt DIP24 & SMD Single & Dual Output



E-224736



EN-60950-1 Certified
UL-60950-1 Certified

REC10

Specifications cont. (measured at $T_A = 25^\circ\text{C}$, nominal input voltage, full load and after warm-up)



Input Surge Voltage (100ms max.)	12V Input	36VDC
	24V Input	50VDC
	48V Input	100VDC
Isolation Voltage	/H2 and SMD	(tested for 1 second) 2000VDC
		(rated for 1 minute) 1000VAC / 60Hz
	/H3 Version	(tested for 1 second) 3000VDC
		(rated for 1 minute) 1500VAC / 60Hz
Isolation Capacitance		1200pF typ.
Isolation Resistance		1 G Ω min.
Overload Protection		150% typ.
Short Circuit Protection		Continuous, Auto Restart
Operating Temperature Range	4:1	-40°C to +65°C (see Graph)
(free air convection)	2:1	-40°C to +75°C (see Graph)
Remote On/Off	DC/DC ON	Open or $3.5\text{V} < V_r < 12\text{V}$
	DC/DC OFF	Short or $0\text{V} < V_r < 1.2\text{V}$
Storage Temperature Range		-55°C to +105°C
Temperature Coefficient		$\pm 0.05\%$ max.
Relative Humidity		95% RH
Case Material		Nickel Plated Metal with Non-Conductive Base
Thermal Impedance	Natural convection	15°C/W
Maximum Case Temperature		100°C
Vibration		10-55Hz, 2G, 30mins along X,Y & Z
Package Weight		18g
Packing Quantity		15 pcs per Tube
MTBF (+25°C)	Detailed Information see Application Notes chapter "MTBF"	using MIL-HDBK 217F 1000 x 10 ³ hours
(+71°C)		using MIL-HDBK 217F >250 x 10 ³ hours

Derating-Graph (Ambient Temperature)



Typical Characteristics

REC10-1205SRW/H2/A/M (/SMD) REC10-1212SRW/H2/A/M (/SMD)



Note: Refer to Application Notes for EMC Class B Filter suggestion

Specifications (cont.)




Certifications

EN General Safety	Report: PS090302950C2	EN60950-1:2006
UL General Safety	Report: E248550	UL 60950-1 1st Ed.
		C22.2 No. 60950-1-03


Package Style and Pinning (mm)

24 PIN DIP Package - Available with /H2 and /H3 Options

3rd angle projection 



Recommended Footprint Details



Pin Connections DIP24



Pin #	Single	Dual
1	CTRL	CTRL
2	-Vin	-Vin
3	-Vin	-Vin
9	NC	Com
11	NC	-Vout
14	+Vout	+Vout
16	-Vout	Com
22	+Vin	+Vin
23	+Vin	+Vin

NC = No Connection



XX.X ± 0.5 mm

XX.XX ± 0.25 mm

24 PIN SMD Package- Only available with /H2 Option



Recommended Footprint Details



Pin Connections DIP24 SMD

Pin #	Single	Dual
1	CTRL	CTRL
2	-Vin	-Vin
3	-Vin	-Vin
9	NC	Com
11	NC	-Vout
14	+Vout	+Vout
16	-Vout	Com
22	+Vin	+Vin
23	+Vin	+Vin
4,5,10,12		NC
13,15,20,21,24		NC

NC = No Connection

XX.X ± 0.5 mm

XX.XX ± 0.25 mm