

PS2633, PS2634, PS2633L, PS2634L

**HIGH ISOLATION VOLTAGE
HIGH COLLECTOR TO EMITTER VOLTAGE
DARLINGTON TYPE 6 PIN PHOTOCOUPLER**

— NEPOC Series —

DESCRIPTION

PS2633, PS2634 and PS2633L, PS2634L are optically coupled isolators containing a GaAs light emitting diode and an NPN silicon darlington-connected phototransistor.

PS2633, PS2634 are in a plastic DIP (Dual In-line Package).

PS2633L, PS2634L are lead bending type (Gull-wing) for surface mount.

PS2633, PS2633L have base pin and PS2634, PS2634L have no base pin.

FEATURES

- High isolation voltage (BV: 5 kV_{r.m.s.} MIN.)
- High collector to emitter voltage (V_{CEO}: 300 V MIN.)
- Ultra High current transfer ratio (CTR: 1 000 % MIN.)
- High speed switching (t_r , t_f = 100 μ s TYP.)
- UL recognized [File No. E72422(S)]
- Taping product name (PS2633L-E3, E4, PS2634L-E3, E4)


APPLICATIONS

- Telephone/Telegraph line receiver
- Power Supply


PACKAGE DIMENSIONS (Unit: mm)

DIP (Dual In-line Package)

Lead Bending type (Gull-wing)



PIN CONNECTION (Top View)



ABSOLUTE MAXIMUM RATINGS ($T_A = 25\text{ }^{\circ}\text{C}$)**Diode**

Reverse Voltage	V_R	6	V
Forward Current (DC)	I_F	80	mA
Power Dissipation Derating	$\Delta P_D/^{\circ}\text{C}$	1.5	mW/ $^{\circ}\text{C}$
Power Dissipation	P_D	150	mW
Peak Forward Current	$I_{F(\text{Peak})}$	1	A
(PW = 100 μs , Duty Cycle 1 %)			

Transistor

Collector to Emitter Voltage	V_{CEO}	300	V
Emitter to Collector Voltage	V_{ECO}	0.6	V
Collector Current	I_C	150	mA
Power Dissipation Derating	$\Delta P_C/^{\circ}\text{C}$	3.0	mW/ $^{\circ}\text{C}$
Power Dissipation	P_C	300	mW


Coupled

Isolation Voltage *1)	BV	5 000	$V_{r.m.s.}$
Storage Temperature	T_{stg}	-55 to +150	$^{\circ}\text{C}$
Operating Temperature	T_{opt}	-55 to +100	$^{\circ}\text{C}$







*1) AC voltage for 1 minute at $T_A = 25\text{ }^{\circ}\text{C}$, RH = 60 % between input (Pin No. 1, 2, 3, Common) and output (Pin No. 4, 5, 6 Common).






ELECTRICAL CHARACTERISTICS ($T_A = 25\text{ }^{\circ}\text{C}$)

CHARACTERISTIC		SYMBOL	MIN.	TYP.	MAX.	UNIT	TEST CONDITIONS
Diode	Forward Voltage	V_F		1.15	1.4	V	$I_F = 10\text{ mA}$
	Reverse Current	I_R			5	μA	$V_R = 5\text{ V}$
	Junction Capacitance	C_t		30		pF	$V = 0$, $f = 1.0\text{ MHz}$
Transistor	Collector to Emitter Dark Current	I_{CEO}			400	nA	$V_{CE} = 300\text{ V}$, $I_F = 0$
Coupled	Current Transfer Ratio	CTR	1 000	4 000	15 000	%	$I_F = 1\text{ mA}$, $V_{CE} = 2\text{ V}$
	Collector Saturation Voltage	$V_{CE(\text{sat})}$			1.0	V	$I_F = 1\text{ mA}$, $I_C = 2\text{ mA}$
	Isolation Resistance	R_{1-2}	10^{11}			Ω	$V_{in-out} = 1.0\text{ kV}_{DC}$
	Isolation Capacitance	C_{1-2}		0.6		pF	$V = 0$, $f = 1.0\text{ MHz}$
	Rise Time*2)	t_r		100		μs	$V_{CC} = 5\text{ V}$, $I_C = 10\text{ mA}$, $R_L = 100\text{ }\Omega$
	Fall Time*2)	t_f		100		μs	$V_{CC} = 5\text{ V}$, $I_C = 10\text{ mA}$, $R_L = 100\text{ }\Omega$

***2) Test Circuit for Switching Time**

TYPICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$)







★ The measurement of TYPICAL CHARACTERISTICS are only for reference, not guaranteed.

SOLDERING PRECAUTION

(1) Infrared reflow soldering

- Peak reflow temperature : 235 °C or below (Plastic surface temperature)
- Reflow time : 30 seconds or less
(Time period during which the plastic surface temperature is 210 °C)
- Number of reflow processes : Three
- Flux : Rosin flux containing small amount of chlorine
(The flux with a maximum chlorine content of 0.2 Wt % is recommended.)

INFRARED RAY REFLOW TEMPERATURE PROFILE




(2) Dip soldering

- Peak temperature : 260 °C or lower
- Time : 10 s or less
- Flux : Rosin-base flux

APPLICATIONS OF PHOTO COUPLERS

TELEPHONE



Caution

The Great Care must be taken in dealing with the devices in this guide.

The reason is that the material of the devices is GaAs (Gallium Arsenide), which is designated as harmful substance according to the law concerned.

Keep the law concerned and so on, especially in case of removal.

No part of this document may be copied or reproduced in any form or by any means without the prior written consent of NEC Corporation. NEC Corporation assumes no responsibility for any errors which may appear in this document.

NEC Corporation does not assume any liability for infringement of patents, copyrights or other intellectual property rights of third parties by or arising from use of a device described herein or any other liability arising from use of such device. No license, either express, implied or otherwise, is granted under any patents, copyrights or other intellectual property rights of NEC Corporation or others.

While NEC Corporation has been making continuous effort to enhance the reliability of its semiconductor devices, the possibility of defects cannot be eliminated entirely. To minimize risks of damage or injury to persons or property arising from a defect in an NEC semiconductor device, customer must incorporate sufficient safety measures in its design, such as redundancy, fire-containment, and anti-failure features.

NEC devices are classified into the following three quality grades:

"Standard", "Special", and "Specific". The Specific quality grade applies only to devices developed based on a customer designated "quality assurance program" for a specific application. The recommended applications of a device depend on its quality grade, as indicated below. Customers must check the quality grade of each device before using it in a particular application.

Standard: Computers, office equipment, communications equipment, test and measurement equipment, audio and visual equipment, home electronic appliances, machine tools, personal electronic equipment and industrial robots

Special: Transportation equipment (automobiles, trains, ships, etc.), traffic control systems, anti-disaster systems, anti-crime systems, safety equipment and medical equipment (not specifically designed for life support)

Specific: Aircrafts, aerospace equipment, submersible repeaters, nuclear reactor control systems, life support systems or medical equipment for life support, etc.

The quality grade of NEC devices in "Standard" unless otherwise specified in NEC's Data Sheets or Data Books. If customers intend to use NEC devices for applications other than those specified for Standard quality grade, they should contact NEC Sales Representative in advance.

Anti-radioactive design is not implemented in this product.