





REV.	DATE	DESCRIPTION
A	06/15/99	MODIFY DESCRIPTION
B	11/14/00	UPDATE PART DIMENSIONS
C	02/19/07	UPDATE DRAWING FORMAT



RECOMMENDED CABLE STRIPPING DIMENSIONS



NOTES:

- CONSULT AMPEHNOL CONNEX FOR CRIMP TOOL INFORMATION.

8				<small>UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.</small> <small>UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE:</small> 0.5 - 8mm \pm 0.20mm 8 - 30mm \pm 0.40mm 30 - 120mm \pm 0.50mm <small>UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE:</small> .020 - .315 \pm 0.007" .315 - 1.180 \pm 0.015" 1.180 - 4.724 \pm 0.020" DO NOT SCALE DRAWING	APPROVALS	DATE	<h1 style="color: blue;">Amphenol Connex</h1> <p>TNC CRIMP JACK – REVERSE POLARIZED (FOR LMR 600 CABLE)</p> <p>PART NO. 122418RP</p>	
7					DRAWN	G.R.S.		02/19/07
6					CHECKED			
5					ISSUED			
4	FERRULE	COPPER	NICKEL		1	SHEET		1 OF 1
3	CONTACT PIN	BRASS	GOLD	1	CAD FILE	C:/122/122418RP.DWG	DWG. NO. 122418RP.DWG	
2	INSULATOR	TEFLON	NATURAL	1	REV.	C	SIZE A	
1	BODY	BRASS	NICKEL	1	SCALE	NA		
	DESCRIPTION	MATERIAL	FINISH	QTY				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[122418RP](#)